

## General Information

<b>Extended Product Type:</b>	ZS50-PE
<b>Product ID:</b>	1SNK516151R0000
<b>EAN:</b>	3472595161515
<b>Catalog Description:</b>	ZS50-PE Screw Clamp Terminal Block - Ground - Green/Yellow
<b>Long Description:</b>	- Reliable electrical and mechanical contact with the rail that exceeds the requirements of the IEC 60947-7-2 terminal block standard.

## Ordering

<b>Color:</b>	Green-Yellow
---------------	--------------

<b>Minimum Order Quantity:</b>	20 piece
--------------------------------	----------

<b>Customs Tariff Number:</b>	85369010
-------------------------------	----------

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK161071D0201
---	-----------------

<b>Instructions and Manuals:</b>	1SNK160027C0201
----------------------------------	-----------------

## Dimensions

<b>Product Net Width:</b>	16 mm
---------------------------	-------

<b>Product Net Height:</b>	63.6 mm
----------------------------	---------

<b>Product Net Depth / Length:</b>	61.2 mm
------------------------------------	---------

<b>Product Net Weight:</b>	83 g
----------------------------	------

## Technical

<b>Rated Cross-Section:</b>	50 mm <sup>2</sup>
-----------------------------	--------------------

<b>Spacing:</b>	16 mm
-----------------	-------

<b>Connection Type:</b>	Screw clamp
-------------------------	-------------

<b>Function:</b>	Ground
------------------	--------

<b>Number of Levels:</b>	1
--------------------------	---

<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 1 ... 50 mm <sup>2</sup>
	Screw Clamp / Flexible 2x 1 ... 25 mm <sup>2</sup>
	Screw Clamp / Rigid 1x 1 ... 50 mm <sup>2</sup>
	Screw Clamp / Rigid 2x 1 ... 25 mm <sup>2</sup>
	Screw Clamp / With Insulated Ferrule 1x 1 ... 50 mm <sup>2</sup>
	Screw Clamp / Without Insulated Ferrule 1x 1 ... 50 mm <sup>2</sup>
	Screw Clamp / With Twin Ferrule 2x 1 ... 16 mm <sup>2</sup>

<b>Gauge Type:</b>	Dia.11
--------------------	--------

<b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b>	for 1 s 6000 A
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	8000 V
<b>Dielectric Test Voltage:</b>	2200 V
<b>Pollution Degree:</b>	3
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	17.0 mm

## Technical UL/CSA

<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 18 ... 0 AWG Screw Clamp / Rigid 2x 18 ... 4 AWG Screw Clamp / With Insulated Ferrule 1x 18 ... 0 AWG Screw Clamp / Without Insulated Ferrule 1x 18 ... 0 AWG Screw Clamp / With Twin Ferrule 2x 18 ... 4 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 0 AWG
<b>Flammability According to UL94:</b>	V0
<b>Short-Circuit Current Rating (SCCR):</b>	100 kA

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant

## Certificates and Declarations (Document Number)

<b>ATEX Certificate:</b>	1SND162004A1708
<b>BV Certificate:</b>	1SND161073A0204
<b>CB Certificate:</b>	1SND161104A0200
<b>CSA Certificate:</b>	1SND161070A0209
<b>cUL Certificate:</b>	1SND161041A0210
<b>Declaration of Conformity - CE:</b>	1SND225112U1004
<b>DNV Certificate:</b>	1SND161087A0202
<b>EAC Certificate:</b>	1SND161010A1100
<b>Environmental Information:</b>	1SND220072E1002
<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RMRS Certificate:</b>	1SND161008A1101

RoHS Information:

1SND230491F0207

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000901 - Ground terminal block
<b>ETIM 5:</b>	EC000901 - Ground terminal block
<b>ETIM 6:</b>	EC000901 - Ground terminal block

## Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	82 mm
<b>Package Level 1 Depth / Length:</b>	265 mm
<b>Package Level 1 Height:</b>	65 mm
<b>Package Level 1 Gross Weight:</b>	1.728 kg
<b>Package Level 1 EAN:</b>	3472595161515
<b>Package Level 2 Units:</b>	80 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Depth / Length:</b>	400 mm
<b>Package Level 2 Height:</b>	200 mm
<b>Package Level 2 Gross Weight:</b>	6.912 kg
<b>Package Level 3 Units:</b>	7680 piece
<b>Product Packing Type:</b>	Box

