

General Information

Extended Product Type:	ZK6-YL
Product ID:	1SNK708060R0000
EAN:	3472599001978
Catalog Description:	ZK6-YL PI-Spring clamp Terminal Block - Feed-through - Yellow
Long Description:	Combine high performance with compact dimensions: - 1000 V AC / DC IE C 600 V UL, - Opt for the best marking visibility thanks to the up-front, flat marker zone, which lets you mark up to eight digits or increase the font size.

Ordering

Color:	Yellow
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK162029D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	8 mm
Product Net Height:	57.5 mm
Product Net Depth / Length:	41.9 mm
Product Net Weight:	11.8 g

Technical

Rated Cross-Section:	6 mm ²
Spacing:	8 mm
Connection Type:	PI Spring
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.5 ... 6 mm ² Spring Clamp / Rigid 1x 0.5 ... 10 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 6 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 6 mm ² Spring Clamp / With Twin Ferrule 2x 0.5 ... 1.5 mm ²
Gauge Type:	A5 & 3.9 mm Dia.

Rated Current (I_n):	Main Circuit 41 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1.3 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Rigid 1x 24 ... 8 AWG Spring Clamp / With Insulated Ferrule 1x 24 ... 10 AWG Spring Clamp / Without Insulated Ferrule 1x 24 ... 10 AWG
Connecting Capacity UL/CSA:	Stranded 8 AWG
Flammability According to UL94:	V0
Short-Circuit Current Rating (SCCR):	100 kA

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225112U1004
Instructions and Manuals:	1SNK160027C0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 119 mm

Package Level 1 Depth / Length: 201 mm

Package Level 1 Height: 46 mm

Package Level 1 Gross Weight: 0.64 kg

Package Level 1 EAN: 3472599001978

Package Level 2 Units: 450 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 5.76 kg

Package Level 3 Units: 21600 piece

Product Packing Type: Box

