



VMx24493RSM-xxx

Vehicular MIMO Antenna

2.4-2.5 AND 4.9-5.85 GHZ VEHICULAR MIMO ANTENNA

The Laird Technologies vehicular MIMO antenna covers the 2.4 to 2.5 GHz and 4.9 to 5.85 GHz frequency ranges, as well as GPS (1575 MHz). Multiple configurations are available from three-port, dual-band elements to one-port, single-band at 4.9 GHz with integrated GPS. Cable options include low-loss cables (LMR195 and LMR240) or RG58 cables. The housing incorporates a low-profile, rugged design that conforms to IP67 standards. The antenna also features high impact, UV-resistant polycarbonate plastic available in black or white..

SPECIFICATIONS	
Frequency	2.4 to 2.5 GHz and 4.9 to 5.9 GHz
Gain	4 dBi peak
VSWR	<2.0:1
Nominal Impedance	50 Ω
Polarization	Vertical
Pattern	Omnidirectional
Max Power	25 Watts
Size	127 mm (5 inches) OD x 31.75 mm (1.25 inches)
Radom Material	High impact PC UV stabilized
Color	Black or white
Termination	LMR195, LMR240, LMR100 or RG58 Cables 1 - 20 ft with Optional Connectors (subject to configuration & performance requirement limitations)
Mounting Require- ments	5/8" and 3/4" prep holes (dependent on chosen configuration)

PART NUMBERS	
VMD24493RSM-366	MIMO,2-Port,802.11N,3dBi,12ft,RP-SMA
VMD24493RSM-518	MIMO,2-Port,802.11N,3dBi,17ft,RP-SMA
VMD24493RSM-610	MIMO,2-Port,802.11N,3dBi,20ft,RP-SMA
VMT24493RSM-366	MIMO,3-Port,802.11N,3dBi,12ft,RP-SMA
VMT24493RSM-518	MIMO,3-Port,802.11N,3dBi,17ft,RP-SMA
VMT24493RSM-610	MIMO,3-Port,802.11N,3dBi,20ft,RP-SMA
VMG24493RSM-366	MIMO,2-Port w/GPS,802.11N,3dBi,12ft,RP-SMA
VMG24493RSM-518	MIMO,2-Port w/GPS,802.11N,3dBi,17ft,RP-SMA
VMG24493RSM-610	MIMO,2-Port w/GPS,802.11N,3dBi,20ft,RP-SMA

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

12/21 Original