

YS4303

Directional Yagi Antenna 430-450 MHz

Directional gamma matched Yagi antennas are focused on economy and high performance. This UHF Yagi series has a 9.1 dBi antenna gain and operates on the 430-450 MHz frequency range. It is manufactured using high strength 6061-T6 aluminum to withstand heavy ice, high wind, and other harsh conditions.

FEATURES AND BENEFITS

- Every Yagi is tuned on a network analyzer for best power match and lowest VSWR.
- All Yagi antennas ship complete with a high-quality cast aluminum mounting kit that includes stainless steel hardware and allows vertical or horizontal orientation during installation (VHF models require light assembly).

APPLICATIONS

- Point-to-point directional and multiple point to omnidirectional outdoor antenna applications used by private organizations and government agencies around the globe.
- Typical applications include transportation such as railroad switching, remote locations reporting examples that include oil fields and weather conditions and meter data transmissions for utilities.

ELECTRICAL SPECIFICATION

Model Name	YS4303
Operating Frequency (MHz)	430-450
VSWR	< 2:1
Return Loss - Max (dB)	-10
Gain (dBi)	9.1
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	300
Polarization	Vertical or horizontal
Pattern	Directional
Vertical Plane 3 dB Beamwidth	114°
Horizontal Plane 3 dB Beamwidth	115°
Tuning	Fixed tune
Transmitting/Receiving	Both
Front-to-Back Ratio (dB)	17

MECHANICAL SPECIFICATION

Dimensions - L x H - cm (inches)	51.4 x 34.6 (20.3 x 13.6)
Boom Diameter - cm (inches)	2.22 (0.875)
Material	Aluminum
Color	Silver
Lightning Protection	Lightning arrester - LABH350NN (sold separately)
Mounting	Yagi mounting kit

ENVIRONMENTAL SPECIFICATION


Operating Environment (Indoor or Outdoor)	Outdoor
Operating Temperature - °C (°F)	-30 to +70°C (-22 to +158°F)
Storage Temperature - °C (°F)	-30 to +70°C (-22 to +158°F)
Rated Wind Velocity - km/hr (mph)	241 (150)
Equivalent Flat Area - sq. m (sq. ft.)	0.04470 (0.48115)

CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR
YS4303	N/A	N-Female

RADITION PATTERNS

**Vertical-to-Vertical Polarization
Azimuth (X, Y, or E-plane)**



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2023 TE Connectivity. All Rights Reserved.

09/23 Original