

KEM SERIES

THREE PHASE HIGH PERFORMANCE EMI FILTER

SINGLE STAGE DELTA CONFIGURATION

INTRODUCTION

Provides high performance when used in applications with low Impedance load controlling pulsed, continuous and intermittent interference noise and where high levels of mains borne interference are present.

APPLICATION

- CNC Machines
- HVAC
- Rectifier
- AC/DC Converters

FEATURES

- Compact
- High Performance
- Chassis mounting


APPROVALS AND COMPLIANCE

- UL Recognised
- CSA Certified



STANDARD

NEW DIN RAIL



SCHEMATIC

Specifications

Electrical Characteristics	
Maximum Continuous Operating Voltage	440/520VAC
Current Ratings	6A to 250A @40°C, Din Mount 6A to 50A @40°C
Operating Frequency	50/60Hz
High Potential Test Voltage -440VAC	Line to Ground 2632VDC for 1 Minute
	Line to Line 1892VDC for 1 Minute
High Potential Test Voltage -520VAC	Line to Ground 2856VDC for 1 Minute
	Line to Line 2236VDC for 1 Minute
Overload Capability	135% of Rated current for 15 minutes

KEM Series



Three Phase High Performance EMI Filter

Functional Characteristics	
Operating Temperature Range	-25°C to +85°C
Climatic Category	25/85/21
Termination (Depends on Current Rating)	Shock Proof (6-100A), Nut & Bolt (150-250A)
Flammability Corresponding to	UL 94 V-0

Reference Standards	
Design Corresponding to	UL 60939-3 and CSA 22.2 No.8-13



Selection Table - Standard Version



TE Part Number	Catalog Number	Rated Current @40°C	Rated Voltage @40°C	Leakage Current (mA)	Weight (Kgs)	Termination	
							
1-1609967-0	6KEMS10AFPD	6A	440 VAC	18	0.7	4	
1-1609967-1	8KEMS10AFPD	8A	440 VAC	18	2	4	
1-1609967-2	10KEMS10AFPD	10A	440 VAC	18	2	4	
1-1609967-3	16KEMS10AFPD	16A	440 VAC	18	3	4	
1-1609967-4	20KEMS10AFPD	20A	440 VAC	18	3	4	
1-1609967-5	25KEMS10AFPD	25A	440 VAC	18	3	4	
1-1609967-6	36KEMS10AFPD	36A	440 VAC	18	3	10	
1-1609967-7	50KEMS10AFPD	50A	440 VAC	18	3	10	
2-1609967-0	60KEMS10AFPD	60A	440 VAC	18	8	16	
2-1609967-1	75KEMS10AFPD	75A	440 VAC	20	8	16	
2-1609967-2	100KEMS10AFPD	100A	440 VAC	20	8	25	
2-1609967-3	125KEMS6AFPD	125A	440 VAC	20	8		M10
2-1609967-4	150KEMS6AFPD	150A	440 VAC	20	8		M10
2-1609967-5	200KEMS6AFPD	200A	440 VAC	20	10		M10
2-1609967-6	250KEMS6AFPD	250A	440 VAC	20	10		M10
4-1609967-0	6KEMS10BFPD	6A	520 VAC	18	0.7	4	
4-1609967-1	8KEMS10BFPD	8A	520 VAC	18	2	4	
4-1609967-2	10KEMS10BFPD	10A	520 VAC	18	2	4	
4-1609967-3	16KEMS10BFPD	16A	520 VAC	18	3	4	
4-1609967-4	20KEMS10BFPD	20A	520 VAC	18	3	4	

KEM Series


Three Phase High Performance EMI Filter

TE Ordering Number	Catalog Number	Rated Current @40°C	Rated Voltage @40°C	Leakage Current (mA)	Weight (Kgs)	Termination	
							
4-1609967-5	25KEMS10BFPD	25A	520 VAC	18	3	4	
4-1609967-6	36KEMS10BFPD	36A	520 VAC	18	3	10	
4-1609967-7	50KEMS10BFPD	50A	520 VAC	18	3	10	
5-1609967-0	60KEMS10BFPD	60A	520 VAC	18	8	16	
5-1609967-1	75KEMS10BFPD	75A	520 VAC	20	8	16	
5-1609967-2	100KEMS10BFPD	100A	520 VAC	20	8	25	
5-1609967-3	125KEMS6BFPD	125A	520 VAC	20	8		M10
5-1609967-4	150KEMS6BFPD	150A	520 VAC	20	8		M10
5-1609967-5	200KEMS6BFPD	200A	520 VAC	20	10		M10
5-1609967-6	250KEMS6BFPD	250A	520 VAC	20	10		M10

Selection Table - Din Rail Mount




NEW




VERTICAL MOUNT

Note: Din Rail not supplied




HORIZONTAL MOUNT

TE Part Number	Catalog Number	Din Type	Rated Current @40°C	Rated Voltage @40°C	Leakage Current (mA)	Weight (Kgs)	Termination 
7-1609967-0	6KEMS10AFPDHM	HORIZONTAL	6A	440 VAC	18	41	0.8
7-1609967-1	8KEMS10AFPDHM	HORIZONTAL	8A	440 VAC	18	41	2.1
7-1609967-2	10KEMS10AFPDHM	HORIZONTAL	10A	440 VAC	18	41	2.1
7-1609967-3	6KEMS10AFPDVM	VERTICAL	6A	440 VAC	18	41	0.9
7-1609967-4	8KEMS10AFPDVM	VERTICAL	8A	440 VAC	18	41	2.2
7-1609967-5	10KEMS10AFPDVM	VERTICAL	10A	440 VAC	18	41	2.2
7-1609967-6	16KEMS10AFPDHM	HORIZONTAL	16A	440 VAC	18	41	3.2
7-1609967-7	20KEMS10AFPDHM	HORIZONTAL	20A	440 VAC	18	41	3.2
7-1609967-8	25KEMS10AFPDHM	HORIZONTAL	25A	440 VAC	18	41	3.2
7-1609967-9	36KEMS10AFPDHM	HORIZONTAL	36A	440 VAC	18	10	3.2
8-1609967-0	50KEMS10AFPDHM	HORIZONTAL	50A	440 VAC	18	10	3.2
9-1609967-1	6KEMS10BFPDHM	HORIZONTAL	6A	520 VAC	18	41	0.8
9-1609967-2	8KEMS10BFPDHM	HORIZONTAL	8A	520 VAC	18	41	2.1
9-1609967-3	10KEMS10BFPDHM	HORIZONTAL	10A	520 VAC	18	41	2.1
9-1609967-4	6KEMS10BFPDVM	VERTICAL	6A	520 VAC	18	41	0.9
9-1609967-5	8KEMS10BFPDVM	VERTICAL	8A	520 VAC	18	41	2.2

KEM Series

Three Phase High Performance EMI Filter

TE Part Number	Catalog Number	Din Type	Rated Current @40°C	Rated Voltage @40°C	Leakage Current (mA)	Weight (Kgs)	Termination 
9-1609967-6	10KEMS10BFPDVM	VERTICAL	10A	520 VAC	18	2.2	4
9-1609967-7	16KEMS10BFPDHM	HORIZONTAL	16A	520 VAC	18	3.2	4
9-1609967-8	20KEMS10BFPDHM	HORIZONTAL	20A	520 VAC	18	3.2	4
9-1609967-9	25KEMS10BFPDHM	HORIZONTAL	25A	520 VAC	18	3.2	4
7-1609968-0	36KEMS10BFPDHM	HORIZONTAL	36A	520 VAC	18	3.2	10
7-1609968-1	50KEMS10BFPDHM	HORIZONTAL	50A	520 VAC	18	3.2	10

Connectors Cross Section

	4	10	16	25	50
Wire Section (mm ²)	4mm ²	10 mm ²	16 mm ²	25 mm ²	50 mm ²
Wire Section (AWG)	12AWG	8 AWG	6 AWG	4 AWG	1/0 AWG
Wire Stripping	max 10mm	max 13.5 mm	max 17 mm	max 17 mm	max 20 mm
Max Recommended Torque	0.5 Nm/4.5 in.lbs	1.2 Nm/10.8 in.lbs	2-2.2 Nm / 18-19.8 in.lbs	2 Nm/18 in.lbs	6 Nm/54 in.lbs

Insertion Loss (Typical) - Measured in Closed 50Ω System

		Common Mode 50Ω/50Ω								
		Frequency in MHz								
		0.01	0.05	0.15	0.5	1	3	5	10	30
Current Rating	6A	60	64	64	57	51	44	40	34	30
	8A	56	60	62	54	50	42	40	34	32
	10A	65	64	61	55	51	42	38	33	27
	16A	57	55	56	54	49	41	37	32	29
	20A	56	54	56	53	49	45	38	32	24
	25A	54	52	50	48	46	39	34	32	24
	36A	60	55	48	38	32	30	28	44	35
	50A	58	54	45	34	31	32	29	42	36
	60A	54	51	47	36	39	29	32	38	44
	75A	44	46	51	55	50	54	44	33	36
	100A	36	40	46	48	52	49	40	34	27
	125A	34	40	48	44	50	48	38	32	28
	150A	34	36	42	44	51	47	40	34	30
	200A	32	36	51	50	47	40	35	30	26
	250A	32	35	51	51	47	39	35	29	26

KEM Series

Three Phase High Performance EMI Filter


		Differential Mode 50Ω/50Ω								
		Frequency in MHz								
		0.01	0.05	0.15	0.5	1	3	5	10	30
Current Rating	6A	20	22	35	62	49	39	36	30	26
	8A	20	24	35	60	46	39	36	30	26
	10A	20	23	36	61	49	38	34	29	25
	16A	35	37	46	55	48	38	35	29	26
	20A	31	32	35	55	72	64	60	51	54
	25A	32	34	34	50	68	62	59	50	52
	36A	54	50	46	40	35	42	29	40	50
	50A	56	51	48	42	40	48	46	52	54
	60A	50	49	50	42	45	48	49	53	58
	75A	48	51	54	49	52	49	46	32	28
	100A	37	41	50	55	60	58	56	55	40
	125A	32	38	51	57	61	56	58	58	46
	150A	32	38	51	57	61	54	58	57	44
	200A	34	38	52	52	46	37	38	31	25
	250A	33	36	52	52	47	40	37	31	25

KEM Series


Three Phase High Performance EMI Filter

Common Mode Insertion Loss (Typical in dB - Refer to table above)


3A




6A




8A




10A



16A



20A




KEM Series


Three Phase High Performance EMI Filter

Common Mode Insertion Loss (Typical in dB - Refer to table above)


25A




36A




50A




60A



75A



100A




KEM Series


Three Phase High Performance EMI Filter

Common Mode Insertion Loss (Typical in dB - Refer to table above)


125A




150A



200A



250A



KEM Series

Three Phase High Performance EMI Filter

Case Dimensions - Standard Version

6A Shock Proof Type	8A to 10A Shock Proof Types
15A to 50A Shock Proof Types	60A to 100A Shock Proof Types
125A to 150A Nut & Bolt Types	150A to 250A Nut & Bolt Types


KEM Series

Three Phase High Performance EMI Filter

Case Dimensions - Din Rail Mount


6A Shock Proof Type - Horizontal Mount

Note: Din Rail not supplied



6A Shock Proof Type - Vertical Mount

Note: Din Rail not supplied




KEM Series

Three Phase High Performance EMI Filter

Case Dimensions - Din Rail Mount


8A to 10A Shock Proof Types - Vertical Mount

Note: Din Rail not supplied



8A to 10A Shock Proof Types - Vertical Mount

Note: Din Rail not supplied




KEM Series

Three Phase High Performance EMI Filter

Case Dimensions - Din Rail Mount


16A to 50A Shock Proof Types - Horizontal Mount

Note: Din Rail not supplied



All dimensions in mm; Tolerances according: ISO2768-m

HOW TO ORDER



te.com

©2022 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

12/22 ED