


REV. 0
DCO 143675

COIL: @ 25°C	
RESISTANCE	44 OHMS ±10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.4 VDC
MUST RELEASE	1.45 VDC MAX, 0.26 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	100 g's 11 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES: OPERATE & RELEASE 4 MS MAX.	
BOUNCE 1.5 MS MAX.	
DIELECTRIC 500 VAC - ALL POINTS	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	2A 28VDC RES.,
	0.5A 28VDC IND. L/R .008 MAX., 0.5A
	115VAC CASE UNGROUNDED, .125A 115VAC
	CASE GROUNDED RES., 100,000 OPS

DR. ASB 16 OCT 02

CK. *[Signature]*

CII Technologies
advanced control electronic solutions

CUST. C.I.I. STD.
CUST. NO. REV.

"3SBC" RELAY

3SBC5004A1