

WIREWOUND ANTI-SURGE RESISTORS


TYPE EP SERIES

INTRODUCTION

TE Connectivity (TE) is pleased to offer this wire wound axial leaded resistor. Robustly manufactured with high quality materials this resistor offers flame proof coating and is designed and tested to withstand power surges of up to 12KV. In line with our commitment to increasing power to size ratio we are now also able to offer this series in extra-small size.

FEATURES

- Power up to 10W in Extra Small Size
- 22 Size/Power Options
- Specially Designed and Tested for Surge Immunity
- RoHS Compliant with no exemptions



CHARACTERISTICS - ELECTRICAL

| Size | Type | Rated Power at 70° C | Maximum Working Voltage | Maximum Overload Voltage | Dielectric Withstanding Voltage | Resistance Range | Operating Temperature Range |
|-------------|-------|----------------------|-------------------------|--------------------------|---------------------------------|------------------|-----------------------------|
| Normal size | EP05W | 1/2W (0.50W) | 500 V | 1,000 V | 350 V | 10Ω - 560Ω | -55°C ~ +155°C |
| | EPIW | 1W | 500 V | 1,000 V | 500 V | 10Ω- 1KΩ | |
| | EP2W | 2W | 500 V | 1,000 V | 500 V | 10Ω - 2KΩ | |
| | EP3W | 3W | 500 V | 1,000 V | 500 V | 10Ω - 3KΩ | |
| | EP5W | 5W | 500 V | 1,000 V | 500 V | 10Ω - 5KΩ | |
| | EP7W | 7W | 500 V | 1,000 V | 500 V | 10Ω - 6KΩ | |
| | EP8W | 8W | 500 V | 1,000 V | 500 V | 10Ω - 10KΩ | |
| | EP9W | 9W | 500 V | 1,000 V | 500 V | 10Ω - 15KΩ | |

Wirewound Anti-Surge Resistors

Type EP Series

CHARACTERISTICS - ELECTRICAL

| Size | Type | Rated Power at 70° C | Maximum Working Voltage | Maximum Overload Voltage | Dielectric Withstanding Voltage | Resistance Range | Operating Temperature Range |
|------------------|---------|----------------------|-------------------------|--------------------------|---------------------------------|------------------|-----------------------------|
| Small size | EP1WS | 1W | 500 V | 1,000 V | 350 V | 10Ω - 560Ω | -55°C to +155°C |
| | EP2WS | 2W | 500 V | 1,000 V | 500 V | 10Ω - 1KΩ | |
| | EP3WS | 3W | 500 V | 1,000 V | 500 V | 10Ω - 2KΩ | |
| | EP5WS | 5W | 500 V | 1,000 V | 500 V | 10Ω - 3KΩ | |
| | EP7WS | 7W | 500 V | 1,000 V | 500 V | 10Ω - 5KΩ | |
| | EP8WS | 8W | 500 V | 1,000 V | 500 V | 10Ω - 6KΩ | |
| | EP9WS | 9W | 500 V | 1,000 V | 500 V | 10Ω - 10KΩ | |
| | EP10WS | 10W | 500 V | 1,000 V | 500 V | 10Ω - 15KΩ | |
| Extra small size | EP1WSSS | 1W | 500 V | 1,000 V | 350 V | 1Ω - 560Ω | -55°C to +155°C |
| | EP1WSS | 1W | 500 V | 1,000 V | 350 V | 1Ω - 750Ω | |
| | EP2WSS | 2W | 500 V | 1,000 V | 350 V | 1Ω - 910Ω | |
| | EP3WSS | 3W | 500 V | 1,000 V | 500 V | 1Ω - 2.2KΩ | |
| | EP4WSS | 4W | 500 V | 1,000 V | 500 V | 1Ω - 2.2KΩ | |
| | EP10WSS | 10W | 500 V | 1,000 V | 500 V | 1Ω - 10KΩ | |

*Maximum working voltage: 500V

Maximum overload voltage: 1,000V

Dielectric withstanding voltage: Dimension: ≤3.5x10 : 350V
>3.5x10 : 500V

Voltage rating:

Resistor shall have a rated Directed-Current (DC) continuous working voltage or an appropriate sine-wave root-mean-square (RMS) alternating-current (AC) Continuous working voltage at commercial line frequency and waveform corresponding to the power rating, as determined from the following formula:

$$RCWV = \sqrt{PxR}$$

Note:

Maximum Working Voltage or \sqrt{PxR} whichever is lesser.

Maximum Overload Voltage or $2.5\sqrt{PxR}$ whichever is lesser.

Were:

RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (Volt)

P = Power Rating (watt)


R = Nominal Resistance (ohm)

In no case shall the rated DC or RMS AC continuous working voltage be greater than the applicable maximum value

Wirewound Anti-Surge Resistors

Type EP Series

DERATING CURVE



For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with this curve.

SURGE RATING

| Type | Low Resistance Range | Maximum Surge Voltage | Medium Resistance Range | Maximum Surge Voltage | High Resistance Range | Maximum Surge Voltage |
|-------------------|----------------------|-----------------------|-------------------------|-----------------------|-----------------------|-----------------------|
| EP05W | 10Ω - 40Ω | 3KV | 43Ω - 240Ω | 4KV | 270Ω - 560Ω | 4KV |
| EP1W | 10Ω - 50Ω | 4KV | 51Ω - 240 Ω | 5KV | 270Ω - 1kΩ | 5KV |
| EP2W | 10Ω - 100Ω | 5KV | 110Ω - 240Ω | 6KV | 270Ω - 2kΩ | 6KV |
| EP3W | 10Ω - 100Ω | 7KV | 110Ω - 680Ω | 8KV | 750Ω - 3kΩ | 8KV |
| EP5W | 10Ω - 160Ω | 8KV | 180Ω - 680Ω | 9KV | 750Ω - 5kΩ | 9KV |
| EP7W | 10Ω - 160Ω | 9KV | 180Ω - 680Ω | 10KV | 750Ω - 6kΩ | 10KV |
| EP8W | 10Ω - 160Ω | 10KV | 180Ω - 680Ω | 11KV | 750Ω - 10kΩ | 11KV |
| EP9W | 10Ω - 160Ω | 10KV | 180Ω - 680Ω | 11KV | 750Ω - 15kΩ | 12KV |
| Small Size | | | | | | |
| EP1WS | 10Ω - 40Ω | 3KV | 43Ω - 240Ω | 4KV | 270Ω - 560Ω | 4KV |
| EP2WS | 10Ω - 50Ω | 4KV | 51Ω - 240 Ω | 5KV | 270Ω - 1kΩ | 5KV |
| EP3WS | 10Ω - 100Ω | 5KV | 110Ω - 240Ω | 6KV | 270Ω - 2kΩ | 6KV |
| EP5WS | 10Ω - 100Ω | 7KV | 110Ω - 680Ω | 8KV | 750Ω - 3kΩ | 8KV |
| EP7WS | 10Ω - 160Ω | 8KV | 180Ω - 680Ω | 9KV | 750Ω - 5kΩ | 9KV |
| EP8WS | 10Ω - 160Ω | 9KV | 180Ω - 680Ω | 10KV | 750Ω - 6kΩ | 10KV |
| EP9WS | 10Ω - 160Ω | 10KV | 180Ω - 680Ω | 11KV | 750Ω - 10kΩ | 11KV |
| EP10WS | 10Ω - 160Ω | 10KV | 180Ω - 680Ω | 11KV | 750Ω - 15kΩ | 12KV |


Wirewound Anti-Surge Resistors

Type EP Series


SURGE RATING

| Type | Low Resistance Range | Maximum Surge Voltage | Medium Resistance Range | Maximum Surge Voltage | High Resistance Range | Maximum Surge Voltage |
|-------------------------|----------------------|-----------------------|-------------------------|-----------------------|-----------------------|-----------------------|
| Extra Small Size | | | | | | |
| EP1WSSS | 1Ω - 40Ω | 1.5KV | 43Ω - 240Ω | 2KV | 270Ω - 560Ω | 2.5KV |
| EP1WSS | 1Ω - 40Ω | 1.8KV | 43Ω - 240Ω | 3KV | 270Ω - 750Ω | 4KV |
| EP2WSS | 1Ω - 40Ω | 2KV | 43Ω - 240Ω | 3KV | 270Ω - 910Ω | 4KV |
| EP3WSS | 1Ω - 100Ω | 3KV | 110Ω - 240Ω | 4KV | 270Ω - 2k2Ω | 5KV |
| EP4WSS | 1Ω - 100Ω | 4KV | 110Ω - 240Ω | 5KV | 270Ω - 2k2Ω | 6KV |
| EP10WSS | 1Ω - 160Ω | 9KV | 180Ω - 680Ω | 10KV | 750Ω - 10kΩ | 10KV |

Surge Waveform (1.2 / 50 μs)




1.2 / 50 μs Voltage Capability



Wirewound Anti-Surge Resistors


Type EP Series

CONSTRUCTION



| No. | Name | Material |
|-----|-----------------|---|
| 1 | Basic Body | Rod Type Ceramics |
| 2 | Resistance Wire | Resistance Wire Alloy |
| 3 | End Cap | Steel (Tin plated iron surface) |
| 4 | Lead Wire | Annealed copper wire coated with tin |
| 5 | Joint | By welding |
| 6 | Coating | Insulated & Non-Flame paint (colour: Light Green) |
| 7 | Colour Code | Non-Flame epoxy resin |

DIMENSIONS AND RESISTANCE RANGE



| Type | Power Rating at 70 °C | Dimensions (mm) | | | |
|---------|-----------------------|-----------------|-------|----------|-------|
| | | D ± 1 | L ± 1 | d ± 0.05 | H ± 3 |
| EP05W | 1/2W (0.50W) | 3.5 | 10.0 | 0.54 | 28 |
| EP1W | 1W | 5.0 | 12.0 | 0.70 | 28 |
| EP2W | 2W | 5.5 | 16.0 | 0.70 | 28 |
| EP3W | 3W | 6.5 | 17.5 | 0.75 | 28 |
| EP5W | 5W | 8.5 | 25.0 | 0.75 | 38 |
| EP7W | 7W | 8.5 | 30.0 | 0.75 | 38 |
| EP8W | 8W | 8.5 | 40.0 | 0.75 | 38 |
| EP9W | 9W | 8.5 | 53.0 | 0.75 | 38 |
| EP1WS | 1W-S | 3.5 | 10.0 | 0.54 | 28 |
| EP2WS | 2W-S | 5.0 | 12.0 | 0.70 | 28 |
| EP3WS | 3W-S | 5.5 | 16.0 | 0.70 | 28 |
| EP5WS | 5W-S | 6.5 | 17.5 | 0.75 | 28 |
| EP7WS | 7W-S | 8.5 | 25.0 | 0.75 | 38 |
| EP8WS | 8W-S | 8.5 | 30.0 | 0.75 | 38 |
| EP9WS | 9W-S | 8.5 | 40.0 | 0.75 | 38 |
| EP10WS | 10W-S | 8.5 | 53.0 | 0.75 | 38 |
| EP1WSSS | 1W-SSS | 2.5 | 6.8 | 0.54 | 28 |
| EP1WSS | 1W-SS | 3.0 | 9.0 | 0.54 | 28 |
| EP2WSS | 2W-SS | 3.5 | 10.0 | 0.54 | 28 |
| EP3WSS | 3W-SS | 5.5 | 13.5 | 0.70 | 28 |
| EP4WSS | 4W-SS | 5.5 | 16.0 | 0.70 | 28 |
| EP10WSS | 10W-SS | 8.5 | 40.0 | 0.75 | 38 |

Wirewound Anti-Surge Resistors


Type EP Series

PERFORMANCE SPECIFICATION


| Characteristics | Limits | Test Methods (JIS C 5201-1) | | | | | | | | | | | | | | | |
|---------------------------------|---|--|------|-------------|------|---|-----------------|---------|---|------------------|------------|---|------------------|--------|---|------------------|------------|
| DC. resistance | Must be within the specified tolerance | The limit of error of measuring apparatus shall not exceed allowable range or 5% of resistance tolerance. (Sub-clause 4.5) | | | | | | | | | | | | | | | |
| Temperature coefficient | $<20\Omega : \pm 400 \text{ PPM}/^\circ\text{C}$ $\geq 20\Omega : \pm 300 \text{ PPM}/^\circ\text{C}$ | Natural resistance change per temperature degree centigrade. $\frac{R2-R1}{R1} \times 10^6 \text{ (PPM}/^\circ\text{C)}$ $R1(t2-t1)$ R1: Resistance value at room temperature (t1) R2: Resistance value at room temperature plus 100°C (t2) (Sub-clause 4.8) | | | | | | | | | | | | | | | |
| Short time overload | Resistance change rate is $\pm (2\% + 0.05\Omega)$ Maximum with no evidence of mechanical damage | Permanent resistance change after application of a potential of 2.5 times RCWV for 5 seconds. (Sub-clause 4.13) | | | | | | | | | | | | | | | |
| Terminal Strength | No evidence of mechanical damage | Direct load: Resistance to a 2.5 kgs direct load for 10 secs. In the direction of the axis of the terminal leads Twist test: Terminal leads shall be bent through 90° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations (Sub-clause 4.16) | | | | | | | | | | | | | | | |
| Solderability | 95% coverage Minimum | The area covered with a new, smooth, clean, shiny and continuous surface free from concentrated pinholes. Test temperature of solder 245 °C ± 3 °C Dwell time in solder : 2 ~ 3 seconds (Sub-clause 4.17) | | | | | | | | | | | | | | | |
| Soldering temperature reference | Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95% coverage Minimum) | The leads immersed into solder bath to 3.2 to 4.8 mm. from the body. Permanent resistance change shall be checked. <u>Wave soldering conditions: (2 cycles Maximum)</u> Pre-heat : 100 ~ 120°C, 30 \pm 5 sec. Suggestion solder temperature: 235 ~ 255 °C, 10 sec. (Maximum) Peak temperature: 260 °C <u>Hand soldering condition:</u> Hand soldering bit temperature: 380 °C \pm 10°C Dwell time in solder : 3 +1/-0 sec. | | | | | | | | | | | | | | | |
| Resistance to soldering heat | Resistance change rate is $\pm (1\% + 0.05\Omega)$ Maximum with no evidence of mechanical damage. | Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C \pm 10°C solder for 3 \pm 0.5 seconds. (Sub-clause 4.18) | | | | | | | | | | | | | | | |
| Temperature cycling | Resistance change rate is $\pm (2\% + 0.05\Omega)$ Maximum with no evidence of mechanical damage | Resistance change after continuous 100 cycles for duty shown below: <table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55°C \pm 3°C</td> <td>30 mins</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>10-15 mins</td> </tr> <tr> <td>3</td> <td>+155°C \pm 2°C</td> <td>30mins</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>10-15 mins</td> </tr> </tbody> </table> (Sub-clause 4.19) | Step | Temperature | Time | 1 | -55°C \pm 3°C | 30 mins | 2 | Room temperature | 10-15 mins | 3 | +155°C \pm 2°C | 30mins | 4 | Room temperature | 10-15 mins |
| Step | Temperature | Time | | | | | | | | | | | | | | | |
| 1 | -55°C \pm 3°C | 30 mins | | | | | | | | | | | | | | | |
| 2 | Room temperature | 10-15 mins | | | | | | | | | | | | | | | |
| 3 | +155°C \pm 2°C | 30mins | | | | | | | | | | | | | | | |
| 4 | Room temperature | 10-15 mins | | | | | | | | | | | | | | | |
| Vibration | Resistance change rate is $\pm (1\% + 0.05\Omega)$ Max. | 55Hz, 3 planes 2hrs each Total amplitude = 1.5mm (Sub-clause 4.22) | | | | | | | | | | | | | | | |

Wirewound Anti-Surge Resistors

Type EP Series

| Characteristics | Limits | Test Methods (JIS C 5201-1) | |
|---|---|---|------------------------------|
| Load life in humidity | Resistance change rate is $\pm(5\% + 0.05\Omega)$ Maximum with no evidence of mechanical damage | Resistance change after 1000 hrs (1.5 hrs "on", 0.5 hr "off") at RCWV in a humidity test chamber controlled at $40^{\circ}\text{C} \pm 2^{\circ}\text{C}$ and 90 to 95% relative humidity (Sub-clause 4.24.2.1) | |
| Load life | Resistance change rate is $\pm(5\% + 0.05\Omega)$ Maximum with no evidence of mechanical damage | Permanent resistance change after 1000 hrs operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at $70^{\circ}\text{C} \pm 2^{\circ}\text{C}$ ambient (Sub-clause 4.25.1) | |
| Resistance to solvent | No deterioration of protective coatings and markings | Specimens shall be immersed in a bath of Isopropyl alcohol completely for 3 minutes with ultrasonic (Sub-clause 4.30) | |
| Surge immunity test (Resistor stand alone-Not sync to phase angle and polarity) | Resistance change rate is $\pm(5\% + 0.05\Omega)$ Maximum | Refer to IEC61000-4-5 | Max Surge Voltage |
| | |  <p>1.2μsec rising time and 50μsec discharge; 10 cycles every 1 minute</p> | Refer to surge rating chart. |


PAINTING METHOD



Welding point, terminal, and lead wire is permissible to be exposed without the outer coated cover. The extent should be within $\frac{1}{2}$ of the angle.


MARKING

For EP Normal Size 1/2W, 1W, 2W, 3W and EP Small Size 1WS, 2WS, 3WS, 5WS and EP Extra Small Size 1WSS, 1WSS, 2WSS, 3WSS. Resistors shall be marked with colour coding in accordance with JIS C 0802.



For EP Normal Size 5W, 7W, 8W 9W and EP Small Size 7WS, 8WS, 9WS, 10WS and EP Extra Small Size 10WSS. Resistors will be marked with:

- 1.Power Rating,
2. Nominal Resistance
3. Resistance Tolerance Code.



Wirewound Anti-Surge Resistors


Type EP Series

LABEL

Label shall be marked with the following items:


1. Type and style
2. Resistance Tolerance
3. Nominal Resistance
4. Quantity
5. PPM
6. Lot Number

Example:

| | | | |
|--|------------------------|-------------|-----------------|
| TYCO Pn | 2176082-7 | | |
| DESC | EP 3W(S) | ± 5% | 100R |
| QTY | 1,000 | Pcs. | PPM: 300 |
| LOT | SAMPLE | | |
| REF | RoHS 2011/65/EU | | |
|  | | | |

PACKAGING

TAPE DIMENSIONS (mm)




| | Style | O ± 1 | P | L1-L2 Maximum | T ± 1 | Z Maximum | R | T ± 1 | S Maximum |
|-------------------------|-------|-------|----------|---------------|-------|-----------|---|-------|-----------|
| EP05W | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EPIW | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2W | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP3W | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |
| Small Size | | | | | | | | | |
| EPIWS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2WS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP3WS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP5WS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |
| Extra Small Size | | | | | | | | | |
| EPIWSSS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EPIWSS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2WSS | PT-52 | 52 | 5 ± 0.5 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP3WSS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP4WSS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |

Wirewound Anti-Surge Resistors


Type EP Series

TAPE IN BOX PACKAGING (mm)



| | Style | O ± 1 | P | L1-L2 Maximum | T ± 1 | Z Maximum | R | T ± 1 | S Maximum |
|-------------------------|-------|-------|----------|------------------|-------|--------------|---|-------|--------------|
| EP05W | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP1W | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2W | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP3W | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |
| Small Size | | | | | | | | | |
| EP1WS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2WS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP3WS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP5WS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |
| Extra Small Size | | | | | | | | | |
| EPIWSSS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP1WSS | PT-52 | 52 | 5 ± 0.3 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP2WSS | PT-52 | 52 | 5 ± 0.5 | 1 | 6 | 1 | 0 | 4 | 0.5 |
| EP3WSS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 5 | 0.5 |
| EP4WSS | PT-64 | 64 | 10 ± 0.5 | 1 | 6 | 1 | 0 | 6 | 0.5 |

TAPE IN BOX PACKAGING (mm)




Wirewound Anti-Surge Resistors

Type EP Series

| | Style | C ± 5 | A ± 5 | B ± 5 | Quantity Per Box (pcs.) |
|-------------------------|-------|-------|-------|-------|-------------------------|
| EP05W | PT-52 | 260 | 85 | 70 | 1000 |
| EPIW | PT-52 | 262 | 86 | 80 | 1000 |
| EP2W | PT-64 | 262 | 92 | 108 | 1000 |
| EP3W | PT-64 | 256 | 92 | 80 | 500 |
| Small Size | | | | | |
| EPIWS | PT-52 | 260 | 85 | 70 | 1000 |
| EP2WS | PT-52 | 262 | 86 | 80 | 1000 |
| EP3WS | PT-64 | 262 | 92 | 108 | 1000 |
| EP5WS | PT-64 | 256 | 92 | 80 | 500 |
| Extra Small Size | | | | | |
| EPIWSSS | PT-52 | 260 | 85 | 70 | 1000 |
| EPIWSS | PT-52 | 260 | 85 | 70 | 1000 |
| EP2WSS | PT-52 | 262 | 86 | 80 | 1000 |
| EP3WSS | PT-64 | 262 | 86 | 80 | 1000 |
| EP4WSS | PT-64 | 262 | 86 | 80 | 1000 |

TAPE ON REEL PACKAGING (mm)




| | Style | A (Across Flanges) | Quantity Per Reel |
|-------------------------|-------|--------------------|-------------------|
| EP05W | PT-52 | 73 ± 2 | 2500 |
| EPIW | PT-52 | 73 ± 2 | 2500 |
| EP2W | PT-64 | 81 ± 5 | 1000 |
| EP3W | PT-64 | 81 ± 5 | 500 |
| Small Size | | | |
| EPIWS | PT-52 | 73 ± 2 | 2500 |
| EP2WS | PT-52 | 73 ± 2 | 2500 |
| EP3WS | PT-64 | 81 ± 5 | 1000 |
| EP5WS | PT-64 | 81 ± 5 | 500 |
| Extra Small Size | | | |
| EPIWSSS | PT-52 | 73 ± 2 | 2500 |
| EPIWSS | PT-52 | 73 ± 2 | 2500 |
| EP2WSS | PT-52 | 73 ± 2 | 2500 |
| EP3WSS | PT-64 | 81 ± 5 | 1000 |
| EP4WSS | PT-64 | 81 ± 5 | 1000 |

Wirewound Anti-Surge Resistors


Type EP Series

BULK IN BOX (IN PLASTIC BAG) (mm)



| | Style | $C \pm 5$ | $A \pm 5$ | $B \pm 5$ |
|-------------------------|-------|-----------|-----------|------------|
| EPO5W | 155 | 95 | 53 | 100 / 1000 |
| EPIW | 155 | 95 | 53 | 100 / 500 |
| EP2W | 155 | 95 | 53 | 100 / 500 |
| EP3W | 155 | 95 | 53 | 100 / 400 |
| Small Size | | | | |
| EPIWS | 155 | 95 | 53 | 100 / 1000 |
| EP2WS | 155 | 95 | 53 | 100 / 500 |
| EP3WS | 155 | 95 | 53 | 100 / 500 |
| EP5WS | 155 | 95 | 53 | 100 / 400 |
| Extra Small Size | | | | |
| EPIWSSS | 155 | 95 | 53 | 100 / 1000 |
| EPIWSS | 155 | 95 | 53 | 100 / 1000 |
| EP2WSS | 155 | 95 | 53 | 100 / 1000 |
| EP3WSS | 155 | 95 | 53 | 100 / 1000 |
| EP4WSS | 155 | 95 | 53 | 100 / 500 |

BULK IN PLASTIC CASE PACKAGING (mm)




| | $C \pm 5$ | $A \pm 5$ | $B \pm 5$ | Quantity Per Case/Box (pcs.) |
|-------------------|-----------|-----------|-----------|------------------------------|
| EP5W | 36 | 20 | 8 | 100 / 1000 |
| Small Size | | | | |
| EP7WS | 36 | 20 | 8 | 100 / 1000 |

Wirewound Anti-Surge Resistors

Type EP Series

BULK IN INNER BOX PACKAGING (IN PLASTIC BAG) (mm)



| | Quantity / Bag (pcs.) | Quantity Inner Box (pcs.) | Quantity Carton (pcs.) | Carton Box Size L x W x H (± 5) |
|-------------------------|-----------------------|---------------------------|------------------------|---------------------------------------|
| EP7W | 10 | 250 | 1000 | 520 x 220 x 250 |
| EP8W | 10 | 250 | 1000 | 520 x 220 x 250 |
| EP9W | 10 | 250 | 1000 | 520 x 220 x 250 |
| Small Size | | | | |
| EP8WS | 10 | 250 | 1000 | 520 x 220 x 250 |
| EP9WS | 10 | 250 | 1000 | 520 x 220 x 250 |
| EP10WS | 10 | 250 | 1000 | 520 x 220 x 250 |
| Extra Small Size | | | | |
| EP10WSS | 10 | 250 | 1000 | 215 x 520 x 250 |

ENVIRONMENTAL RELATED SUBSTANCE

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and halogen free.

Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFGs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

STORAGE CONDITIONS (MSL1)


The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of $25^{\circ}\text{C} \pm 10^{\circ}\text{C}$ and a relative humidity of $60\%RH \pm 10\%RH$, chemical and dust free atmosphere.

Even within the above guarantee periods, do not store these products in the following conditions.

Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as Cl_2 , H_2S , NH_3 , SO_2 , or NO_2
2. In direct sunlight

HOW TO ORDER



*Preferred range is E24 resistances at 5% Tolerance with Tape/Box packaging.

te.com

©2024 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

02/24 9-1773463-6 ED