



# 623 Extension

**speedtec** - ready

**12-pin  
insulation insert uncoded  
housing code 1**

**EMC - Shielding**

**central mount /lock nut M25x1.5 variable end stop  
Anti-vibration o-ring**

## Technical Data

number of pins 12  
temperature range -20 °C to 130 °C  
clamping range Ø 6.0 mm to Ø 10.0 mm  
protection type when connected IP 66/67

## Electrical Data

rated current max. 7 A\*  
rated voltage 160 V (AC/DC)  
rated insulation voltage (L-L) 2500 V

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3  
over voltage category III  
max. height for operation 2000 m

## Material

housing zinc diecast / nickel plated  
insulation insert PBT, UL 94 / V0  
seals FKM  
clamp ring brass / nickel plated

**Contacts** (not part of product contents)

**Tools** (not part of product contents)

**A KU A 021 NN 00 41 0240 000**  
**A K A 021 N 00 41 0240 000**



**Contact Arrangement**  
mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH  
Bernrieder Straße 15  
94559 Niederwinkling, Deutschland  
Tel.: +49 9962 2002-0  
Fax: +49 9962 2002-70  
E-Mail: intercontec@te.com  
Web: www.intercontec.biz



**Main Dimensions**  
Extension

\*for max. wire cross-section  
pay attention to the  
cross-section of used contacts