

Y(B)1505

Directional Yagi Antenna

GOLD ANODIZED YAGI ANTENNAS SURE LONG-TERM PERFORMANCE

Laird's premium series Directional Yagi antennas are fully gold anodized for corrosion resistance. Our engineering staff has also optimized the product family for forward gain by computer analysis and then field-tested each for conformance.

FEATURES AND BENEFITS

- Every Yagi is tuned on a network analyzer for best power match and lowest VSWR.
- All Yagi antennas ship complete with a high quality cast aluminum mounting kit that includes stainless steel hardware and allows vertical or horizontal orientation during installation. (VHF models require light assembly)
- Available in gold or black (B) anodized finish

APPLICATIONS

- Point to point directional and multiple point to omnidirectional outdoor antennas applications used by private organizations and government agencies around the globe
- Typical applications include transportation such as railroad switching, remote locations reporting examples that include oil fields and weather conditions and meter data transmissions for utilities

MECHANICAL SPECIFICATION


Material	Aluminum
Length	72"
Height	39.5"
Boom Diameter	1.25"
Weight	6 lbs
Rated Wind Velocity	150mph (241kph)
Equivalent Flat Area	0.9102 sq. ft.
Cable	None
Termination	N-Female connector
Color	Gold or Black Anodized
Lightning Protection	Lightning Arrestor LABH350NN (Sold Separately)
Mounting	Heavy duty gold cast (Kit included as shown)

ELECTRICAL SPECIFICATION


Frequency Range	150 - 174 MHz (Tunable)
VSWR	< 2:1
Return Loss	-10dB max
Nominal Gain	9.2 dBd
Front to Back Ratio	20 dB
Maximum Power	300 W
Nominal Impedance	$\Omega 50$
Polarization	Vertical or Horizontal
Pattern	Directional
Horizontal Beamwidth (For Horizontal Polarization)	60°
Vertical Beamwidth (For Vertical Polarization)	54°
Tuning	See cut chart
Transmitting/Receiving	Both



Heavy-Duty Mounting Kit Included



Vertical-to-Vertical Polarization
Azimuthal Pattern (Y, Z, or E-plane)



Horizontal-to-Horizontal Polarization
Azimuthal Pattern (Y, Z, or H-plane)

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

11/21 Original