



# 958 Extension

**8-pin**  
**EMC - Shielding**  
**Earth-to-Housing Connection according to VDE 0627**

## Technical Data

number of pins	8
power	4 (3+PE)
signal	4
temperature range	-20 °C to 130 °C
clamping range	Ø 17.0 mm to Ø 36.0 mm
protection type	when connected IP 66/67

## Electrical Data

	<b>power</b>	<b>signal</b>
rated current	max. 150 A*	max. 12 A*
rated voltage	630V (AC/DC)	250 V (AC/DC)
rated insulation voltage (L-L)	6000 V	4000 V

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree	3
over voltage category	III
max. height for operation	2000 m

## Material

housing	zinc diecast / nickel plated
insulation insert	PBT, UL 94 / V0
seals	FKM
contacts	brass / silver plated
contacts	brass / gold plated
clamp ring	aluminium / nickel plated

## Contacts

Item / TCPN:	61.114.23 / 61-0114-023-000
type	Contact Pin ø10.0 mm
cross section	crimp/ 25.00mm <sup>2</sup>
contact resistance	< 90 µOhm

Item / TCPN:	61.117.11 / 61-0117-011-000
type	Contact Pin ø1.6 mm
cross section	crimp/ 0.35 - 1.50 mm <sup>2</sup>
contact resistance	< 5 mOhm

## Tools (not part of product contents)

Battery crimp tool  
Item / TCPN: C0.207.00 / C0-0207-000-000

Crimping Inserts  
Item / TCPN: C0.210.00 / C0-0210-000-000

analog crimping tool for 1 mm-/2 mm- contacts  
Item / TCPN: C0.201.00 / C0-0201-000-000

**D KU A 002 MR 03 74 0001 000**  
**D K A 002 M 03 74 0001 000**



## Contact Arrangement

mating view



**Contact Pin ø10.0 mm**  
crimp/ 25.00mm<sup>2</sup>  
Item: 61.114.23  
TCPN: 61-0114-023-000



**Contact Pin ø1.6 mm**  
crimp/ 0.35 - 1.50 mm<sup>2</sup>  
Item: 61.117.11  
TCPN: 61-0117-011-000




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH  
Bernrieder Straße 15  
94559 Niederwinkling, Deutschland  
Tel.: +49 9962 2002-0  
Fax: +49 9962 2002-70  
E-Mail: intercontec@te.com  
Web: www.intercontec.biz



**Main Dimensions**  
Extension

\*for max. wire cross-section  
pay attention to the  
cross-section of used contacts