



Pin, Spool & Strain Insulators



PIN, SPOOL, STRAIN INSULATORS

TE Energy rounds out the insulator offering to include spool, pin and strain insulators.

TE’s porcelain insulators were sold in the past with brand names of Morlynn, Dulmison and Zibo, and have 95 years of service experience in electric power supply and rail applications. Manufactured from high-quality non-porous electrical porcelain, they provide long life and cost-effective solutions for a majority of applications.

Contact your TE Energy sales representative for more information and for other applications not found in this brochure.

PORCELAIN PIN TYPE INSULATORS

Description	Pin Type	Leakage Distance (in)	Critical Impulse Flashover Pos./Neg. (kV)	Low Frequency Flashover Wet/Dry (kV)	Cantilever Strength (lbs)	Dry Arc Distance	Puncture Voltage	Max. RIV	Diameter (in)	Height (in)
PI-55-1-PSG	55-1	4	50/70	20/35	3000	2.25	50	50	3.25	3.50
PI-55-2-PSG	55-2	5	70/85	25/45	2500	3.38	70	50	3.75	3.25
PI-55-3-PSG	55-3	7	90/110	30/55	2500	4.49	90	50	4.75	3.75
PI-55-4-PSG	55-4	9	105/130	35/65	3000	5.00	95	50	5.50	4.38
PI-55-5-PSG	55-5	12	130/150	45/80	3000	6.26	115	100	7.00	4.88
PI-55-6-PSG	55-6	12	150/170	50/100	3000	8.00	135	100	8.38	5.50

Above descriptions designate gray and semicon glaze. For other designs and custom-made products, please contact your TE Energy sales representative.




PORCELAIN PIN TYPE INSULATOR, F NECK

PORCELAIN PIN TYPE INSULATORS

Description	Pin Type	Leakage Distance (in)	Critical Impulse Flashover Pos./Neg. (kV)	Low Frequency Flashover Wet/Dry (kV)	Cantilever Strength (lbs)	Dry Arc Distance	Puncture Voltage	Max. RIV	Diameter (in)	Height (in)
PI-56-1-PSG	56-1	13	150/190	60/95	2500	7.0	130	100	7.50	5.75
PI-56-2-PSG	56-2	17	175/225	70/110	3000	8.3	145	100	9.00	6.50
PI-56-3-PSG	56-3	21	200/265	80/125	3000	9.5	165	200	10.5	7.50
PI-56-4-PSG	56-4	27	225/310	95/140	3000	11.3	185	200	12.0	9.50

“S” designates semicon glaze applied to upper side of the insulator. Above descriptions designate gray and semicon glaze. For other designs and custom-made products, please contact your TE Energy sales representative.




PORCELAIN PIN TYPE INSULATOR, J NECK



PORCELAIN STRAIN

Description	Low Frequency Flashover Dry (kV)	Low Frequency Flashover Wet (kV)	Leakage Distance (in)	Mechanical Failure Load (lbs)	Height (in)	Diameter (in)
MG-54-1-PG	25	12	41	10000	3.50	2.52
MG-54-2-PG	30	15	48	13000	4.25	2.87
MG-54-3-PG	35	18	57	20000	5.50	3.39
MG-54-4-PG	40	23	76	20000	6.75	3.50

For other designs and custom-made products, please contact your TE Energy sales representative.




PORCELAIN STRAIN

PORCELAIN SPOOL

Description	Low Frequency Flashover	Low Frequency Flashover Vertical\Horizontal	Height (in)	Transverse Strength (lbs)
	Dry (kV)	Wet (kV)		
MS-53-1-PG	20	8/10	2.13	2000
MS-53-2-PG	25	12/15	3.00	3000
MS-53-3-PG	25	12/15	3.19	4000
MS-53-4-PG	25	12/15	3.00	4500
MS-53-5-PG	35	18/25	4.13	6000

For other designs and custom-made products, please contact your TE Energy sales representative.



PORCELAIN SPOOL



FOR MORE INFORMATION

te.com/energy

TE Technical Support Center

USA: +1 (800) 327-6996
Canada: +1 (905) 475-6222
Mexico: +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
UK: +44 (0) 800-267666
France: +33 (0) 1-3420-8686
Netherlands: +31 (0) 73-6246-999
China: +86 (0) 400-820-6015

energy.te.com

© 2011 - 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.
8-1773462-9 E458 07/2012

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

