



TE'S RAYCHEM PLUG-IN TERMINATIONS RPIT INNER CONE SYSTEMS FOR SWITCHGEARS AND TRANSFORMERS UP TO 52 kV

KEY FEATURES

- Shielded inline connection for gas insulated switchgears and transformers up to 52 kV
- Metal-enclosed, hermetically insulated and suitable for outdoor use
- Designed to be used for different conductor types in accordance with IEC 60228
- Special designs for wind power stations and offshore applications with bronze protection cover
- Optional voltage detection point

TE Connectivity's (TE) Raychem Plug-In Terminations RPIT separable connectors are designed for both aluminum or copper conductors in accordance with IEC 60228 and are compatible with inner cone bushings size 2 (800 A) and size 3 (1250 A) as per EN 50180/EN 50181. TE's Raychem RPIT are available for system voltages from 12 kV up to 52 kV for any type of cable and are compliant with CENELEC HD 629.1.S2:2006- A1:2008 (up to 42 kV) and IEC 60840 (52 kV). In addition, TE's Raychem RPIT can be customized with an optional voltage detection point and a special material composition for harsh environments.

The inner cone terminations incorporate a high-quality contact system which ensures reliable current transmission from the cable conductors to the busbars. The electrical interfaces between the silicone stress relief cone to the cable and the bushing are kept permanently sealed using a pressure component. This element is housed in the protection cover, which is sealed with heat shrink tubing.

The installation and plug-in of inner cone terminations is simple by using silicone component and offering an easy-to-handle installation tool, which is compatible with industry-wide standards. In addition to TE's Raychem RPIT inner cone terminations, TE offers a full line of other RPIT accessories such as bushings, insulating caps and current testing tools to meet any needs and support our customers.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



TE Connectivity has decades of experience in the field of hermetically-insulated termination systems for medium voltage networks and offers an inner cone termination product series that ensure reliable cable connection for switchgears and transformers up to 52 kV.

TECHNICAL DATA - TESTING ACCORDING TO CENELEC HD629.1.S2			
Item	Size 2	Size 3	Requirement
U_0 / U	20.8/36	20.8/36	n.a.
U_m	42	42	n.a.
DC withstand voltage 15 min (kV)	125	125	no breakdown or flashover
AC withstand voltage 5 min (kV)	93.5	93.5	no breakdown or flashover
PD at ambient temp (kV)	< 2 pC	< 2 pC	max 10 pC at 2 U_0
Impulse voltage at elevated temp (kV)	200	200	10 impulses of each polarity; no breakdown
Heating cycle voltage in air (kV)	52	52	63 cycles at 2.5 U_0 ; no breakdown
Heating cycle voltage in water (kV)	52	52	63 cycles at 2.5 U_0 ; no breakdown
Thermal short circuit conductor (kA)	31.8/2.93 sec	34.93/4.75 sec	2 short circuits to raise conductor to 250°C; no breakdown
Dynamic short circuit (kA)	125	125	1 short circuit at I_d ; no breakdown
Disconnection/Connection	5 x pass	5 x pass	5 complete operations; no visible damage to contact
Partial discharge at elevated and ambient temp (kV)	< 2 pC	< 2 pC	max 10 pC at 2 U_0
Impulse voltage at ambient temp (kV)	200	200	10 impulses of each polarity; no breakdown
AC withstand voltage 15 min (kV)	52	52	no breakdown or flashover

PRODUCT SELECTION INFORMATION						
Description	Size	Nominal Current (A)	System Voltage (kV)	Cross Section (mm ²)	Diameter over conductor (mm)	Diameter over insulation (mm)
RPIT - 321x	2	800	12	120 - 400	12.0 - 24.6	21.0 - 33.0
RPIT - 521x	2	800	24	50 - 400	7.6 - 24.6	21.0 - 39.0
RPIT - 621x	2	800	36/42	50 - 400	7.6 - 24.6	23.5 - 42.0
RPIT - 331x	3	1250	12	240 - 630	17.0 - 32.5	26.0 - 40.0
RPIT - 531x	3	1250	24	150 - 630	13.0 - 32.5	26.0 - 42.5
RPIT - 631x	3	1250	36/42	70 - 630	7.6 - 32.5	26.0 - 50.0
RPIT - 831x*	3	1250	52	50 - 500	7.6 - 27.6	26.0 - 55.0

TE's Raychem RPIT are available with and without test point. One kit contains a set of 3 plug-in terminations.

* 52 kV product tested according to IEC 60840.

TEST REPORT
Size 2: PPR - 2940
Size 3: PPR - 3037

te.com/energy

© 2018 TE Connectivity. All Rights Reserved. EPP-2342-11/18-EN

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

**FOR MORE INFORMATION:
TE Technical Support Centers**

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+32 16 508 695
Russia:	+7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015