



## TE CONNECTIVITY'S (TE) RAYCHEM LOW VOLTAGE JOINT FOR CLASS 5 CABLES (LJC5)

### KEY FEATURES

- Specially designed to meet the requirements of flexible class 5 cables
- Meets the CENELEC 50393 specifications
- Uses mechanical connectors to ensure good connection of class 5 cables
- Easy and fast installation
- Reliable moisture seal due to pre-coated adhesive

TE Connectivity's (TE) Raychem Low Voltage Joint for class 5 cables (LJC5) is part of the innovative solutions product portfolio, which includes products for various cable types and applications that excel in harsh environments. TE's Raychem LJC5 is designed to meet the requirement of flexible class 5 cables and also meets CENELEC 50393 specifications.

TE's Raychem LJC5 offers a reliable jointing system to maintain high network reliability and the use of mechanical connectors to ensure that the fine wires in the class 5 cables are not damaged. The design of the joint is staggered in order to ensure that it remains compact after installation.

TE's Raychem LJC5 is designed to cover a wide variety of class 5 cables used in the industrial network.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**

## LJC5 - Low Voltage Joint for Class 5 cables



### Selection Table for 4-core Polymeric Cables

Part Number	Product Description	Application Range (mm <sup>2</sup> )	Cable Shield Type
EJ2719-000	LJC5-4,5x25-70	25-70	Copper wire Shielded
EJ2720-000	LJC5-4,5x95-150	95-150	
EJ2721-002	LJC5-4,5x240	240	

Should be used only with the connectors included in the kit.

A full selection table is available on request.

For further details on this or any other TE products please contact your local sales representative.

[te.com/energy](http://te.com/energy)

©2018 TE Connectivity. All Rights Reserved. EPP-2843-DDS-02/18

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

#### FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015