

ELECTRO-TAP CABLE CONNECTOR & SPLICES

DUAL BARRIER TERMINAL BLOCKS

KEY FEATURES

- Eliminates junction boxes and wire nuts
- No wire stripping or cutting of run wires
- Permanent lock
- Built-in wire stop
- Tap pre-assembly possible
- Isolated metal contacts
- Polarized for proper mating
- Tap wire installed separately



Raychem AMP ELECTRO-TAP connector utilizes insulation displacement type self-stripping contacts which provide faster, easier tapping than the conventional twist or other type splices. After four simple steps you have a fast, reliable connection on solid or stranded wires 20-10 AWG (.160-.195 max. insulation diameter). There is no special tooling required--ordinary pliers are all that are needed.

Each AMP ELECTRO-TAP connector is constructed of durable nylon with self-stripping, tin-plated brass contacts.

These connectors have a wide range of wiring applications in both low- and high-voltage usage.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

ELECTRO-TAP Cable Connector & SPLICES



PRODUCT SELECTION			
Part Number	Wire Range	Description	Std. Pack
CPGI-1116377-2	12-14 AWG	Splice Kit for 2 -conductor	5
CPGI-1116377-2-Bulk	12-14 AWG	Splice Kit for 2 -conductor	100
CPGI-208169-2	12-14 AWG	Splice Kit for 3-conductor	5
CPGI-208169-2-Bulk	12-14 AWG	Splice Kit for 3-conductor	100
CPGI-1116415-2	12-14 AWG	Tap & Splice Kit for 2 -conductor	5
CPGI-1116415-2-Bulk	12-14 AWG	Tap & Splice Kit for 2 -conductor	100

te.com/energy

© 2019 TE Connectivity. All Rights Reserved. EPP-3385-DDS-6/19-ELECTRO-TAP-AMP

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION:
TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015

