

EKM-2050F-2D1-5S-6-E1-B
Art.Nr.: CS0553-000 (JOR-88541)



Fuse box for lighting application EKM 2050
according to DIN / VDE 0660 T. 505 - with VDE-Symbol

explanation SKF (for installation in lighting columns and outdoor application)

- protection class II
- ingress protection IP 54
- minimum diameter 89 mm
- door opening minimum 85 x 270 mm
- l x w x h: 257 x 82 x 63 mm
- grey cover with screws
- protection cover
- compact- terminal block comprising:
 - 2 fuse bases 16 A / D01-E14
 - 2 fuses 6 A / E14
 - 2 screw caps E 14
 - 5 sliding terminals
- rail connection (brass rails, nickel-plated)
- fully insulated PE- and N- output terminals
- type of mains: (N), L1, L2, <L3>, PE(N), for all net configurations
- enclosed earthing cable, 10 mm², green / yellow, 400 mm long, with ring cable lug and captive screw M 8- enclosed
- extension of cable break out area (80 mm)
- cable entry: cable clamp for 3 cables to 5 x 16 mm²
- output: 2 cable glands

Two additional luminaire cables can be routed towards the bottom of the box.
Sales unit= 28 pieces in a carton

Schaltbild:

