


# RNF-3000



## PRODUCT BENEFITS

- 3:1 shrink ratio easily accommodates awkward, irregular shapes
- Few sizes cover a wide range of diameters, allowing reduced inventory
- Excellent physical, chemical, and electrical properties meet industry standards for highly reliable, general purpose tubing
- Flame-retardant (colors only)
- RoHS compliant

## FLEXIBLE, HIGH-SHRINK-RATIO, FLAME-RETARDANT, GENERAL PURPOSE, POLYOLEFIN TUBING

Used for insulation and strain relief of wire terminations and electrical connections. Also suitable for light-duty harnessing, jacketing, and identification of wires, cables, and electrical and electronic components.

### TEMPERATURE RATING

- Continuous operating temperature from **-55°C up to +135°C**
- Minimum shrink temperature: **+80°C**
- Minimum full recovery temperature: **+120°C**


### SPECIFICATIONS

- TE: **Specification RW-2053**
- UL: **E35586, 600 V, 125°C**
- Military: **Def. Stan. 59-97 Type 2B, VG 95343 Pt 5 Type A (color), VG 95343 Pt 5 Type B (clear)**
- Industry: **VDE 0341 Pt 9005, Type A and B**
- CSA: **LR31929, 600 V, 125°C**
- Flammability Rating: **UL 224/CSA All Tubing Flame Test (Colors only)**

### TYPICAL APPLICATION

- Insulation and strain relief of wire terminations and connections.
- Jacketing wire bundles and harnesses where superior abrasion resistance is a plus. Color-coding and identification. Protection of wire markers (clear).

## DIMENSIONS (MILLIMETERS/INCHES)



## RNF-3000 3:1 RATIO STANDARD SIZES

SIZE	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D (D)		MINIMUM RECOVERED I.D (d)		WALL THICKNESS AFTER RECOVERY (W)	
	mm	in	mm	in	mm	in
1.5/0.5	1.50	0.059	0.50	0.020	0.45±0.10	0.018±0.004
3/1	3.00	0.118	1.00	0.039	0.55±0.10	0.022±0.004
4.5/1.5	4.50	0.177	1.50	0.059	0.55±0.10	0.022±0.004
6/2	6.00	0.236	2.00	0.079	0.65±0.10	0.026±0.004
9/3	9.00	0.354	3.00	0.118	0.75±0.12	0.030±0.005
12/4	12.00	0.472	4.00	0.157	0.75±0.12	0.030±0.005
18/6	18.00	0.709	6.00	0.236	0.85±0.12	0.033±0.005
24/8	24.00	0.945	8.00	0.315	1.00±0.18	0.039±0.007
39/13	39.00	1.535	13.00	0.512	1.15±0.20	0.045±0.008

### ORDERING INFORMATION

Colour	Standard**: Black (-0), white (-9), red (-2), blue (-6), yellow (-4), clear (-X) Nonstandard: Brown (-1), orange (-3), green (-5), violet (-7), gray (-8)
Size selection	Always order the largest size that will shrink snugly over the component to be covered. Special order sizes are available upon request.
Standard packaging***	On spools or in 1.2-meter [4-foot] lengths.
Ordering Description	Specify product family, size/range, color, and package. <b>RNF-3000-X/X-X-X</b> 

#### Note

\*\*Black is the only standard color in the Americas. All other colors are nonstandard.

\*\*\*Only spools are standard in the Americas. 1.2 meter [4-foot] lengths are nonstandard.

\*\*\*\*Europe only. For supply to Def Stan and BS add -DS or -BS to ordering description.

Are you looking to seal out moisture, offer enhanced strain relief, or provide rigorous mechanical protection?

Do you need a flame retardant product? Leverage TE Connectivity's (TE) comprehensive portfolio of heat shrink tubing products in a wide range of applications.

## Learn more: [TE.com/heatshrinktubing](https://www.te-connectivity.com/heatshrinktubing)

© 2024 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo), TE and Raychem are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

07/24