



MESH SERIES™

Omnidirectional Antennas 2400 MHz - 5850 MHz

The Mesh Series™ omnidirectional antenna systems offered by Laird are designed with mesh networking in mind. With their waterproof N male connector they can be easily mounted to an enclosure like the die- cast enclosure (DCE-7x6x2) to give total wireless coverage. Various gains and frequencies are available. They are constructed of UV resistant materials and are waterproof for a long service life.

FEATURES AND BENEFITS

- Mesh networking vertically polarized omni-directionals
- Various gains available: 5dBi to 12dBi
- Various frequencies available: 2.4GHz 3.5GHz, 4.9GHz, 5GHz, also tri-band model
- Type N male integrated connector Rugged, lightweight, and waterproof


ELECTRICAL SPECIFICATIONS	OD24M-5	OD24M-7	OD24M-9	OD24M-12	OD35M-10	OD49M-6	OD49M-11	OD5WM6	OD58M-12
Operating Frequency (MHz)	2400-2485	2400-2485	2400-2485	2400-2485	3400-3600	4940-4990	4940-4990	5150-5850	5400-5850
Gain (dBi)	5	7	9	12	10	6	11	6	12
Vertical Bandwidth (°)	25	18	14	7	14	30	5	8.5	7
VSWR	1.5:1								
Impedance (Ohms)	50								
Input Power	10								
Rate wind velocity m/sec (mph)	56 (125)								
Operating temperature (°C)	-40 - +70								

MECHANICAL SPECIFICATIONS	OD24M-5	OD24M-7	OD24M-9	OD24M-12	OD35M-10	OD49M-6	OD49M-11	OD5WM6	OD58M-12
Dimensions – diameter x height – mm (inches)	15 x 355 (0.6 x 12)	15 x 540 (0.6 x 21)	15 x 690 (0.6 x 27)	15 x 1220 (0.6 x 48)	15 x 690 (0.6 x 27)	13 x 175 (0.5 x 7)	15 x 787	15 x 483	15 x 700
Weight – kg (lbs.)	.2 (.5)	.3 (.6)	.4 (.8)	.6 (1.4)	.5 (1.1)	.043 (1.5)	.5 (1.1)	.14 (.3125)	.5 (.65)

CONFIGURATION

PART NUMBER	CONNECTOR
OD24M-5	2400-2485 MHz Omnidirectional Antenna
OD24M-7	2400-2485 MHz Omnidirectional Antenna
OD24M-9	2400-2485 MHz Omnidirectional Antenna
OD24M-12	2400-2485 MHz Omnidirectional Antenna
OD35M-10	3400-3600 MHz Omnidirectional Antenna
OD49M-6	4940-4990 MHz Omnidirectional Antenna
OD49M-11	4940-4990 MHz Omnidirectional Antenna
OD5WM6	5150-5850 MHz Omnidirectional Antenna
OD58M-12	5400-5850 MHz Omnidirectional Antenna

ANTENNA PATTERN



SYSTEM ORDERING

OD ___ M- ___

24 = 2400 to 2485 MHz 35
= 3400 to 3600 MHz 49 =
4940 to 4990 MHz 58 =
5400 to 5858 MHz 5W =
5150 to 5850 MHz

Gain
5 = 5dBi
12 = 12dBi

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

12/21 Original