



## LIVE END SEAL (HVES)

FOR 1/C PILC AND POLY OR 3/C PILC CABLE (15-25 kV)

### KEY FEATURES

- Provides excellent insulation
- For use on polymeric and PILC cables


TE Connectivity's (TE) Raychem HVES heat-shrinkable live end seals insulate and seal the ends of polymeric and PILC cables. These kits consist of heat-shrinkable tubings and a high-dielectric strength, polymeric plug, which overlap the conductor to provide excellent insulation. The outer adhesive-lined re-jacketing sleeve is designed to provide a positive environmental seal.

Once the HVES kit is installed, the cable can be re-energized. Typical applications include the live ending of spare cables for future use, isolating a failed cable length, and sectionalizing a cable circuit during system maintenance and repair, expansion, or testing.


**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**



HVES



HVES-3



**PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (mm)**

Description	PILC/Poly Conductor Size (AWG/kcmil)	Insulation Diameter (min - max)		Kit Installed Length
		PILC	POLY	
<b>HVES-1520D (1/C PILC/VCLC and 1/C Poly) 15 kV</b>				
		<b>A</b>	<b>A</b>	<b>L</b>
HVES-1521D	#4 - 4/0	0.60 - 0.90 (15 - 23)	0.65 - 1.05 (17 - 27)	12 (305)
HVES-1522D	250 - 350	0.85 - 1.10 (22 - 28)	0.90 - 1.30 (23 - 33)	12 (305)
HVES-1523D	500 - 750	1.05 - 1.30 (27 - 33)	1.10 - 1.60 (28 - 41)	12 (305)
HVES-1524D	750 - 1000	1.20 - 1.50 (30 - 38)	1.25 - 1.80 (32 - 46)	12 (305)
<b>HVES-2520D (1/C PILC/VCLC and 1/C Poly) 25 kV</b>				
HVES-2521D	#1 - 250	0.85 - 1.25 (22 - 32)	0.85 - 1.25 (22 - 32)	21 (533)
HVES-2522D	350 - 500	1.15 - 1.50 (29 - 38)	1.15 - 1.50 (29 - 38)	23 (584)
HVES-2523D	750 - 1000	1.50 - 1.90 (38 - 48)	1.50 - 1.90 (38 - 48)	25 (635)
<b>HVES-3-1590 (3/C PILC/VCLC) 15 kV</b>				
HVES-3-1591	#4 - 4/0	0.60 - 1.00 (15 - 25)	-	27 (686)
HVES-3-1592	250 - 350	0.85 - 1.10 (22 - 28)	-	27 (686)
HVES-3-1593	500 - 750	1.05 - 1.50 (27 - 38)	-	27 (686)
HVES-3-1594	750 - 1000	1.15 - 1.75 (29 - 44)	-	27 (686)
<b>HVES-3-2590E (3/C PILC/VCLC) 25 kV</b>				
HVES-3-2591E	#1 - 250	0.85 - 1.20 (22 - 30)	-	28 (711)
HVES-3-2592E	350 - 500	1.15 - 1.40 (28 - 36)	-	31 (787)
HVES-3-2593E	750 - 1000	1.50 - 1.70 (38 - 43)	-	32 (813)

**ORDERING INFORMATION**

1. Select the appropriate catalog number. All selections are based on the typical dimensions of 100% insulated and 133% insulated poly cables manufactured in accordance with AEIC standard Nominal insulation thickness (100%): 15 kV: 165 mils (PILC/VCLC) 175 mils (poly) 25 kV: 225 mils (PILC/VCLC) 260 mils (poly) Nominal insulation thickness (133%): 15 kV: 220 mils (poly)
2. For cables manufactured to other specifications, confirm selection with cable dimensions
3. Standard package: HVES-1520D,-2520D = One kit/box, HVES-3-1590,-2590E = One 3/C kit/box

**TEST REPORT**

15 kV: EDR-5146  
25 kV: EDR-5273

te.com/energy

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved. E604 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

**FOR MORE INFORMATION: TE Technical Support Centers**

USA: +1 800 327 6996  
 France: +33 380 583 200  
 UK: +44 0870 870 7500  
 Germany: +49 896 089 903  
 Spain: +34 916 630 400  
 Benelux: +32 16 351 731  
 Canada: +1 (905) 475-6222  
 Mexico: +52 (0) 55-1106-0800  
 Latin/S. America: +54 (0) 11-4733-2200  
 China: +86 (0) 400-820-6015