



## RAYCHEM RAYVOLVE RVS SPLICE COVERS

### ROLL-ON SPLICES FOR FOR 1/C POWER CABLE (1000V)

#### KEY FEATURES

- Easy connection
- Water resistant seal
- Fast installation
- CSA certified

TE Connectivity's (TE) Raychem RVS splice cover kits are the easy "roll-on" way to insulate and seal cable connections up to 1000 V. The gripping force of the specially formulated EPDM elastomer combines with the high performance sealant to form a water-resistant, insulating sleeve that is CSA certified for direct burial application over in-line compression connectors.

RVS splice cover sleeves feature a dual-wall design with an entrapped lubricant, making installation fast and simple. The cable can also be energized immediately and is ideal to be used where gas or electric heating devices are not approved.

The elastomeric sleeve rolls onto the cable with minimal effort, even at temperatures below -15°F (-25°C).

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**

## RAYCHEM RAYVOLVE RVS SPLICE COVERS



Bulk options are also available. Consult your TE Connectivity representative. Each kit contains one Rayvolve RVS splice cover sleeve and sealant strips. Kit does not contain connectors.

PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (mm)				
Description	Conductor Size (AWG/kcmil)	Cable OD (min. - max.)	Sleeve Length	Max Collector Length
RVS-11	#8 - 2/0	0.22 - 0.68 (6 - 17)	8.0 (205)	5.00 (127)
RVS-12	1/0 - 250	0.50 - 0.90 (13 - 23)	9.5 (241)	4.50 (114)
RVS-13	250 - 600	0.70 - 1.20 (18 - 30)	12.0 (305)	7.00 (178)
RVS-14	600 - 1000	0.95 - 1.50 (24 - 38)	14.0 (356)	9.00 (229)

\*Dimension values provided are typical.

TEST REPORT
Standard test reports: EDR-5167

Learn more: [TE.com/energy](https://www.te-connectivity.com/energy)

© 2024 TE Connectivity. All Rights Reserved. EPP-2729-DDS-EN-AMS-06/24

TE, TE Connectivity, TE connectivity (logo), EVERY CONNECTION COUNTS, Raychem and Rayvolve are trademarks owned or licensed by TE Connectivity. Other logos, product and company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions, specifications, and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications, and/or information. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

Connect with us:  
[TE.com/energy-contact](https://www.te-connectivity.com/energy-contact)