


COIL: @ 25°C	
RESISTANCE	140 OHMS ± 10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.3 VDC
MUST RELEASE	.75 VDC

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6 ± 1	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: \_\_\_\_\_  
 \_\_\_\_\_  
 \_\_\_\_\_

**CUSTOMER DATA SHEET**



CONTACT RATING: 5 AMPS 30 VDC  
 RESISTIVE 100,000 OPERATIONS

DR. R.B. 1/27/92 CK. 1/27/92 gms



CUST. HI-G  
 CUST. NO. 2BN-2A-112

TYPE "FW" RELAY

FW5A1201S07