



## GA30K6A1i SERIES II THERMISTORS

Thermally Conductive Epoxy Coating

Ø 2.4 mm Maximum Diameter

32 AWG Solid Silver-Plated Copper Leads  
with White PTFE Insulation

Four Temperature Tolerance Classifications Available

RoHS Compliant

BetaCURVE series II thermistors are small epoxy coated devices with solid tin-plated lead wires. The series II offers insulated lead wires for added protection, the PTFE insulation also enhances bonding for applications that require mounting or potting the thermistor with epoxies or adhesives. This series also offers a choice of precision temperature tolerance classifications for a wide variety of applications.


### FEATURES

- Interchangeability
- Proven stability and reliability
- Rapid time response
- PTFE insulated lead wires
- Thermally conductive epoxy coating
- Temperature range -40°C to +125°C
- Custom probe assemblies available

### APPLICATIONS

- Temperature sensing, control and compensation
- Tight tolerance instrumentation
- General instrumentation applications

**MECHANICAL DETAILS**



**DIMENSIONS**

A	B	C
10 ±2 mm	76 ±2 mm	2.4 mm max.

**Note 1:** 30AWG Solid Silver-Plated Copper Leads with White PTFE Insulation

**Note 2:** Green Stycast 2850ft Epoxy

**PERFORMANCE SPECS**

Parameters	Units	Value
Nominal Resistance at +25°C	Ohms	30,000
GA30K6A1iA Resistance Tolerance from 0°C to +70°C	°C	±0.1
GA30K6A1iB Resistance Tolerance from 0°C to +70°C	°C	±0.2
GA30K6A1iC Resistance Tolerance from 0°C to +70°C	°C	±0.5
GA30K6A1iD Resistance Tolerance from 0°C to +70°C	°C	±1.0
Alpha Value at +25°C	%/°C	4.68
Beta Value 25/85	K	4261
Tolerance on Beta Value 25/85	%	±0.5
Time Response in Liquids	Seconds	<1
Dissipation Constant in Still Air	mW/°C	0.85

**RESISTANCE V TEMPERATURE TABLE**

Temp. °C	Ohms
-40	1219114
-39	1137677
-38	1062161
-37	992104
-36	927079
-35	866698
-34	810604
-33	758469
-32	709991
-31	664894
-30	622924
-29	583847
-28	547448
-27	513528
-26	481906
-25	452413
-24	424895
-23	399208
-22	375221
-21	352813
-20	331871
-19	312291
-18	293977
-17	276841
-16	260801
-15	245781
-14	231711
-13	218526
-12	206164
-11	194572
-10	183696
-9	173489
-8	163905
-7	154905
-6	146449
-5	138501
-4	131028
-3	124000
-2	117388
-1	111164
0	105305
1	99787

Temp. °C	Ohms
2	94588
3	89688
4	85069
5	80712
6	76603
7	72725
8	69064
9	65608
10	62343
11	59258
12	56342
13	53585
14	50978
15	48512
16	46178
17	43969
18	41877
19	39896
20	38019
21	36240
22	34554
23	32955
24	31439
25	30000
26	28635
27	27339
28	26108
29	24939
30	23828
31	22773
32	21770
33	20816
34	19909
35	19047
36	18225
37	17444
38	16700
39	15992
40	15317
41	14674
42	14062
43	13478

Temp. °C	Ohms
44	12921
45	12390
46	11884
47	11400
48	10939
49	10499
50	10079
51	9678
52	9294
53	8928
54	8578
55	8244
56	7924
57	7618
58	7325
59	7046
60	6778
61	6521
62	6276
63	6041
64	5816
65	5601
66	5394
67	5196
68	5007
69	4825
70	4651
71	4483
72	4323
73	4169
74	4022
75	3880
76	3744
77	3613
78	3488
79	3367
80	3251
81	3140
82	3033
83	2930
84	2832
85	2737

Temp. °C	Ohms
86	2645
87	2557
88	2473
89	2392
90	2313
91	2238
92	2165
93	2095
94	2028
95	1963
96	1901
97	1841
98	1783
99	1727
100	1673
101	1621
102	1571
103	1522
104	1476
105	1431
106	1387
107	1345
108	1305
109	1266
110	1228
111	1192
112	1156
113	1123
114	1090
115	1058
116	1027
117	998
118	969
119	941
120	915
121	889
122	864
123	839
124	816
125	793

**ORDERING INFORMATION**

<b>Part Number</b>	<b>Description</b>	<b><math>\Omega</math> @25°C</b>	<b>MOQ*</b>
GA30K6A1iA	Series II thermistor	30,000	1,000
GA30K6A1iB	Series II thermistor	30,000	1,000
GA30K6A1iC	Series II thermistor	30,000	1,000
GA30K6A1iD	Series II thermistor	30,000	1,000

\* For quantities less than MOQ (Minimum Order Quantity) contact distribution

**NORTH AMERICA**  
Tel +1 800 522 6752  
[customercare.ando@te.com](mailto:customercare.ando@te.com)

**EUROPE**  
Tel +31 73 624 6999  
[customercare.glwy@te.com](mailto:customercare.glwy@te.com)

**ASIA**  
Tel +86 0400 820 6015  
[customercare.chdu@te.com](mailto:customercare.chdu@te.com)

**[te.com/sensorsolutions](http://te.com/sensorsolutions)**

BetaCurve, TE Connectivity, TE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, products and/or company names referred to herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.