



OC80271

806-960 MHz/1710-2700 MHz Direct Mount Omnidirectional Antenna

MULTI-BAND DIRECT MOUNT OMNIDIRECTIONAL ANTENNA

The OC80271 antenna is a wide band omnidirectional antenna covering the domestic Cellular/PCS/AWS/MDS, WiMax 2300/2500 and global GSM900/GSM1800/UMTS/LTE2600 bands. The antenna can be used in both indoor and outdoor applications complete with mast mounting hardware and includes a UV stable radome enclosure that provides years of use without degradation to either mechanical properties or aesthetics.

FEATURES

- Applicable for both 3G and 4G solutions
- Global LTE 2600 band
- Domestic Cellular and Global GSM
- WiMax 2300/2500/2600
- Weatherproof UV stable radome
- Mast mounting hardware included
- Conformance to RoHS

MARKETS

- Broadband wireless access service provider
- Campus, healthcare, or transportation terminals
- Stadium, industrial plants, and processing stations
- Low-to-medium density, tower mounted rural locations
- Public Safety Radio

PARAMETER	SPECIFICATIONS
Frequency	806 to 824 MHz, 824 to 960 MHz, 1710 to 1900 MHz, 1920 to 2170 MHz, 2300 to 2500 MHz, 2500 to 2690 MHz
Max Gain	806 to 960 MHz - 1.0 dBi, 1710 to 2700 MHz - 5.0 dBi
Average Efficiency	806 to 960 MHz - 72%, 1710 to 2700 MHz - 79%
3 dB Beamwidth (E-plane)	806 to 960 MHz - 93°, 1700 - 2200 MHz - 75°, 2500 - 2700 MHz - 95°
3 dB Beamwidth (H-plane)	360°, Omnidirectional
Polarization	Linear, Vertical
Nominal Impedance	50 Ohms
VSWR	806 to 960 MHz - < 2.5:1, 1710 to 2700 MHz - < 2.0:1
Power	20 watts
RF Connector	N- Type (M)
Mount Style	Mast/pole mount (Upright position only)
Radome	Polycarbonate, UV, White


PARAMETER	SPECIFICATIONS
Material Substance Compliance	ROHS Compliant
Operating Temperature	-30°C to +70°C
Storage Temperature	-40°C to +85°C
Dimensional (Ht x OD)	196 x 24.5 mm (7.7" x 1")
Weight	120g

CONNECTORS


MODEL NUMBER	CONNECTOR
OC80271-FNM	Type N male
OC80271-FNF	Type N female

TYPICAL RADIATION PATTERNS


806 MHZ Band



Azimuth Plane




Phi 0° Plane




Phi 90° Plane


960 MHZ Band



Azimuth Plane




Phi 0° Plane




Phi 90° Plane


1710 MHZ Band



Azimuth Plane




Phi 0° Plane




Phi 90° Plane


2500 MHZ Band



Azimuth Plane



Phi 0° Plane



Phi 90° Plane

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

11/21 Original

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015