


REV. 0
DCO 143507

COIL: @ 25°C	
RESISTANCE	200 OHMS ±10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.4 VDC
MUST RELEASE	2.0 VDC MAX., 0.28 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 4.0 MS MAX.
	RELEASE TIME 7.5 MS MAX.
	CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 18 APR 02 *CK* *4/19/02*



CUST. GPL
CUST. NO. M39016/16-018M REV. _____

"JMSD" RELAY

JMSWD-6XM