

MEAS MS5611 PERIPHERAL MODULE

Digital Pressure Temperature Sensor

The MS5611 peripheral module provides the necessary hardware to interface the MS5611 digital barometric pressure and temperature sensor to any system that utilizes a Digilent Pmod™ compatible expansion ports configurable for I²C communication. The MS5611 sensor is a self-contained pressure and temperature sensor that is fully calibrated during manufacture. The sensor can operate from 1.5V to 3.6V. The sensor module includes a high-linearity pressure sensor and an ultra-low power 24-bits $\Delta\Sigma$ ADC with internal factory-calibrated coefficients.

Performance

- 300 to 1200mbar pressure range
- -40°C to 85°C temperature range
- Very low power consumption
- Operates from 1.5V to 3.6V
- Altitude resolution at sea level is 20 cm of air
- Fast conversion time – 0.5 ms typical

Specifications

- Measures pressure from 300mbar to 1200mbar
- Measures temperature from -40°C to 125°C
- I²C communication
- Fully calibrated
- Fast response time
- Very low power consumption


Features

- 12-pin connector compatible with Digilent Pmod™
- I²C interface
- Secondary 12-pin connector allows daisy chain
- FPGA bare metal drivers available for download
- μ C C code drivers available for download
- 24-bits resolution for pressure
- 24-bits resolution for temperature
- Parameters stored on chip

MS5611 PERIPHERAL MODULE

Digital Pressure Sensor

Schematic



Connector Pin Assignments (I²C Communications)


System Plug (Table 1)

| Connector J1 | | |
|--------------|--------|-------------------------------|
| Pin No. | Signal | Description |
| 1 | N/C | Not Connected |
| 2 | N/C | Not Connected |
| 3 | SCL | I ² C Serial Clock |
| 4 | SDA | I ² C Serial Data |
| 5 | GND | Ground |
| 6 | Vdd | Power Supply |
| 7 | N/C | Not Connected |
| 8 | N/C | Not Connected |
| 9 | SCL | I ² C Serial Clock |
| 10 | SDA | I ² C Serial Data |
| 11 | GND | Ground |
| 12 | Vdd | Power Supply |

Expansion Socket (Table 2)

| Connector J2 | | |
|--------------|--------|-------------------------------|
| Pin No. | Signal | Description |
| 1 | N/C | Not Connected |
| 2 | N/C | Not Connected |
| 3 | SCL | I ² C Serial Clock |
| 4 | SDA | I ² C Serial Data |
| 5 | GND | Ground |
| 6 | Vdd | Power Supply |
| 7 | N/C | Not Connected |
| 8 | N/C | Not Connected |
| 9 | N/C | Not Connected |
| 10 | N/C | Not Connected |
| 11 | N/C | Not Connected |
| 12 | N/C | Not Connected |

Dimensions(mm)



MS5611 PERIPHERAL MODULE

Digital Pressure Sensor

Detailed Description

I²C Interface

The peripheral module can interface to the host in one of two ways. It can plug directly into a Digilent Pmod™ compatible port (configured for I²C) through connector J1, or to other I²C boards that have a Digilent Pmod™ compatible expansion connector.

I²C Interface (Daisy Chaining Modules)

Connector J1 provides connection of the module to the Digilent Pmod™ host. The pin assignments and functions adhere to the Digilent Pmod™ standard as shown in Table 1. The J2 connector allows additional Digilent Pmod™ modules to be connected in a daisy-chain fashion. See Table 2.

External Control Signals

The module operates as an I²C slave using the standard 2 wire I²C connection scheme. The module is controlled by the host (through the Digilent Pmod™ connector). In cases where one or more of the SCL and SDA signals are driven from an external source, resistors R1, R2 provide pull-up. However, this also increases the apparent load to the external driving source. If the external source is incapable of driving these loads, they could be removed from the board.

Reference Material

Detailed information regarding operation of the IC:

[MEAS MS5611 Datasheet](#)

Ordering Information

| Description | Part Number |
|--------------------------|-------------|
| MS5611 PERIPHERAL MODULE | DPP102Z000 |

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Phone: +1-800-522-6752
customercare.hmp1@te.com

EUROPE

MEAS France(Europe)
a TE Connectivity Company
Phone: +31 73 624 6999
customercare.tise@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Phone: +86-400-820-6015
customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. family of companies All Rights Reserved.