

REV. 1 9/9/98


COIL: @ 25°C	
RESISTANCE	50 OHMS \pm 10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.7 VDC
MUST RELEASE	1.4 VDC MAX, 0.22 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.
RELEASE TIME 1.5 MS MAX.
CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/3/98 *[Signature]* 9/9/98

 COMMUNICATIONS
INSTRUMENTS, INC.

CUST. TELEDYNE
 CUST. NO. ER412X-5B

TYPE PRMA RELAY

PRMACF-5Y