

PS13-6B TO

Description

Blue-green enhanced square active area PIN photodiode with 13 mm² active area. Metal can type hermetic TO5 package with UV clear glass window.

Features

- 13 mm² PIN detector
- High sensitivity
- High shunt resistance
- Blue-green enhanced

Applications


- Precision photometry
- Analytical instruments
- Medical equipment
- Fluorescence detector

RoHS

2011/65/EU

2015/863/EU


[CLICK HERE >](#)
CONNECT WITH A SPECIALIST




Absolute maximum ratings

Symbol	Parameter	Min	Max	Unit
T _{STG}	Storage temp	-55	125	°C
T _{OP}	Operating temp	-40	100	°C
V _{max}	Max reverse voltage		20	V
I _{PEAK}	Peak DC current		10	mA

Spectral response (23 °C)




Schematic




Electro-optical characteristics @ 23 °C

Symbol	Characteristic	Test	Min	Typ	Max	Unit
	Active area		3504 x 3504			µm
	Active area		13			mm ²
I _D	Dark current	V _R = 5 V		0.25	10	nA
C	Capacitance	V _R = 0 V		180		pF
		V _R = 5 V		50		pF
	Responsivity	λ = 410 nm		0.22		A/W
		λ = 550 nm		0.37		A/W
t _R	Rise time	V _R = 0 V; λ = 410 nm; R _L = 50 Ω		140		ns
		V _R = 5 V; λ = 410 nm; R _L = 50 Ω		70		ns
	Shunt Resistance	V _R = 5 mV		200		MΩ
	N.E.P.	V _R = 5 V; λ = 410 nm		4 E-14		W/√Hz
V _{BR}	Breakdown voltage	I _R = 2 µA	20	30		V


Quantum efficiency (23 °C)



Capacitance as fct of reverse bias (23 °C)



Dark current as fct of bias (23 °C)



Optical inspection

Optical inspection according to failure catalogue for optical sensors FK INS 201.

Package dimension:

Small quantities: Foam pad, boxed (12 cm x 16.5 cm)

Handling:

Please refer to document "Instructions for handling and processing"

Disclaimer: Due to our strive for continuous improvement, specifications are subject to change within our PCN policy according to JESD46C.

Ordering information (standard configurations)

Description	TE Part Number	MPQ
PS13-6b TO (TO5)	3001225-F	1000 pcs

CLICK HERE >
CONNECT WITH A SPECIALIST

NORTH AMERICA
Tel +1 800 522 6752

EUROPE
Tel +31 73 624 6999

ASIA
Tel +86 0400 820 6015

te.com/sensors

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Corporation. All Rights Reserved.

Version # 07/2022

