

SGJ

Cable Actuated Sensor Industrial | CAN bus J1939

Two Available Stroke Ranges: 0-80 in & 0-120 in.

Rugged Polycarbonate Enclosure | Simple Installation

Compact Design | Built for IP67 environments

Specifications

Stroke Range Options	80 in. (2032 mm), 120 in. (3048 mm)
Accuracy	.5% FS
Repeatability	.05% FS
Resolution	12-bit
Input Voltage	10-36 VDC
Input Current (max.)	100 mA

Measuring Cable

0.19-inch dia. nylon-coated stainless steel

Measuring Cable Tension

80-inch	14 oz. (3,9 N) ±30%
12-inch	9 oz. (2,5 N) ±30%

Maximum Acceleration

10 g

Sensor

Plastic-hybrid precision potentiometer

Cycle Life

≥ 250,000

Electrical Connection

M12 connector (mating plug included)

Enclosure

glass-filled polycarbonate

Environmental

IP 67

Operating Temperature

-40° to 185° F (-40° to 85° C)

Weight, 80-inch (w/o bracket)

0.6 lbs. (272 g)

Weight, 12-inch (w/o bracket)


1 lb. (454 g)

The economically priced SGJ provides linear position sensing over J1939 CANbus for OEM, mobile equipment, and factory automation applications. Designed to withstand IP67 environments, the SGJ is constructed with a rugged polycarbonate body, an extremely durable spring-loaded stainless steel measuring cable and a stainless steel mounting bracket. For the OEM, customized options are available.



CANbus SPECIFICATIONS

Communication Profile	CANbus SAE J1939
Protocol	Proprietary B
Node ID	Adjustable via dipswitch (O-63), default set to 0
Baud Rate Options	125K (default), 250K, 500K, 1M
Date Rate Options	5ms (default), 20ms, 50ms, 100ms
Termination Resistor	See ordering information


Electrical Connection:



signal	pin	pin-colorcode
n/c	1	1 - brown
10...36 Vdc	2	2 - white
common	3	3 - blue
CAN high	4	4 - black
CAN Low	5	5 - green/yellow



Position Data Overview:



Baud, Node ID and Data Rate:

Baud Rate, Node ID and Data Rate settings are set via dip switch found on the internal controller board. To gain access to the controller board, remove the 4 cover attaching screws and carefully separate the sensor cover from the main body. Be careful not to damage the small gauge wires that connect the potentiometer to the controller board mounted directly to the rear cover.


Follow the instructions below for desired settings and reinstall sensor cover.

BAUD rate options	baud rate	SW7	SW8
}	125 kbps	off	off
	250 kbps	on	off
	500 kbps	off	on


Data Rate options	Data Rate	SW9	SW10
}	5 ms	off	off
	20 ms	on	off
	50 ms	off	on
	100 ms	on	on

node ID options (0x00-0x3F)	node ID Dec. Hex	SW1 (2 ¹)	SW2 (2 ²)	SW3 (2 ³)	SW4 (2 ⁴)	SW5 (2 ⁵)	SW6 (2 ⁶)
}	0 0x00	off	off	off	off	off	off
	1 0x01	on	off	off	off	off	off
	2 0x02	off	on	off	off	off	off
	3 0x03	on	on	off	off	off	off
...
62 0x3E	off	on	on	on	on	on	on
63 0x3F	on	on	on	on	on	on	on

I/O Format:



Position Data Overview



Identifier:



	Message Priority				Future Use		J1939 Reference Proprietary B								Data Field Type*				Not Used		Node ID**									
Example -	1	0	0	0	0	0	1	1	1	1	1	1	1	1	0	1	0	1	0	0	1	1	0	0	1	1	1	1	1	1
Identifier Bit No. -	28	27	26	25	24	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
Hex Value -	0						F								5				3		F									

*Sensor field data can be factory set to customer specific value. **Customer defined, set via Dips 1-6. Bit values shown for example only, see Address Setting below.

Data Field:

- B₀ - LSB current measurement count byte
- B₁ - MSB current measurement count byte
- B₂ - not used
- B₃ - not used

- B₄ - error flag
- B₅ - error flag
- B₆ - LSB velocity data byte
- B₇ - MSB velocity data byte



Current Measurement Count

The Current Measurement Count (CMC) is the output data that indicates the present position of the measuring cable. The CMC is a 12-bit value that occupies bytes B₀ and B₁ of the data field. B₀ is the LSB (least significant byte) and B₁ is the MSB (most significant byte).

The CMC starts at 0x006 with the measuring cable fully retracted and continues upward to the end of the stroke range stopping at 0xFE5. This holds true for all ranges.

Converting CMC to Linear Measurement

To convert the current measurement count to inches or millimeters, simply divide the count by 4061 (total counts over the range) and then multiply that value by the full stroke range:


$$\left(\frac{\text{CMC} - 6}{4063} \right) \times \text{full stroke range}$$

Sample Conversion:

If the full stroke range is 125 inches and the current position is 0x4FF (1279 Decimal) then,


$$\left(\frac{1279 - 6}{4061} \right) \times 125 = 39.2 \text{ inches}$$

Error Flags




0x00 (GREEN - ON, RED - OFF) indicates the sensor is operating within normal calibrated limits.

0x33, 0x55, 0xAA, 0xCC (RED or GREEN - FLASHING) indicates sensor is at or beyond its calibrated measurement range. Should any of these conditions occur within calibrated range, return unit to factory for evaluation or service.



Velocity

Data in bytes B₇ - B₆ is the change in the CMC (current measurement count) over a 100 msec time period. This data can then be used to calculate velocity in a post processing operation.



Velocity Calculation

$$\left(\frac{\text{count change} - 2047}{.1 \text{ sec. time period}} \right) \times \left(\frac{\text{full stroke range}}{4063} \right)$$

Sample Calculations

Cable Extension (positive direction):

B₇..B₆ = 0x8D3 (2259Dec), full stroke = 125 in.


$$\left(\frac{2259 - 2047}{.1 \text{ sec}} \right) \times \left(\frac{125 \text{ in.}}{4063} \right) = 65.22 \text{ in. / sec.}$$

Cable Retraction (negative direction):


B₇..B₆ = 0x7D0 (2000Dec), full stroke = 125 in.

$$\left(\frac{2000 - 2047}{.1 \text{ sec}} \right) \times \left(\frac{125 \text{ in.}}{4063} \right) = -14.46 \text{ in. / sec.}$$

80-inch SGJ-80-4 w/ Mounting Bracket:



120-inch SGJ-120-4 w/ Mounting Bracket:




Mounting Options:

Changing Measuring Cable Exit and Electrical Connector Direction:


For the ultimate in flexibility, the measuring cable exit direction and the direction of the electrical connector can be rotated around in 90° increments to accommodate just about any installation requirement.

To change the measuring cable exit direction, remove the 4 mounting bracket screws, rotate the bracket to the desired position and replace the screws.


To change the direction of the electrical connector, remove the 4 sensor cover screws and carefully remove the sensor cover just far enough to separate the cover from the main body. Be careful of the three small gauge wires that attach the internal controller board to the potentiometer.



Mounting Option Mounting Dimensions • 80-inch (SGJ-80-4):



Mounting Option Mounting Option Dimensions • 120-inch (SGJ-120-4):



Ordering Information:

w/o terminating resistor

	Part No. SGJ-80-4 80-inch stroke range, no terminating resistor, 5-pin M12 mating plug, mounting bracket included	Part No. SGJ-120-4 120-inch stroke range, no terminating resistor, 5-pin M12 mating plug, mounting bracket included
---	---	---

w/ terminating resistor

	Part No. SGJ-80-4-TR 80-inch stroke range, with terminating resistor, 5-pin M12 mating plug, mounting bracket.	Part No. SGJ-120-4-TR 80-inch stroke range, with terminating resistor, 5-pin M12 mating plug, mounting bracket.
---	--	---

 5-pin M12 connector 16 ft (5 m) 22 AWG (.50mm ²)	Optional Cordset for short-run connections, a convenient optional 16-ft. cordset with a 5-pin M12 connector.	Part No. 9036810-0030
--	--	---------------------------------

 5-pin, field installable M12 connector	Field Installable Connector While every SGJ ships with a field installable 5-pin M12 mating plug, additional connectors are available.	Part No. 9036810-0032
--	--	---------------------------------

[CLICK HERE >](#)
CONNECT WITH A SPECIALIST

NORTH AMERICA
 Tel +1 800 522 6752

EUROPE
 Tel +31 73 624 6999

ASIA
 Tel +86 0400 820 6015

te.com/sensors

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2021 TE Connectivity Corporation. All Rights Reserved.

Version # 08/2023

