

POWER PCB RELAY T9F SERIES

INTRODUCTION

TE Connectivity (TE) introduces the T9F series 32Amp miniature relays designed for generating control in the latest energy and power supply applications. The T9F series product line is a noteworthy and reliable solution for EV charging, power supply, solar inverters, and battery energy storage system applications. It has 32Amp current capability and is suitable for 105°C environments. More importantly, its size is significantly minimized to create space saving for the customer.

FEATURES

- 1 pole 32A, 1 form A (NO) contact
- Ambient temperature up to 105°C at 32A
- Small size and footprint
- Compliant with AEC-Q200

APPLICATION

- On board chargers
- Power supply / UPS
- EV charging stations
- Photovoltaic inverters
- Battery energy storage systems



APPROVALS

- UL

CONTACT DATA

Characteristic	Specification
Contact arrangement	1 form A (NO)
Rated voltage	277VAC
Max. switching voltage	277VAC
Max. switching current	32A
Breaking capacity max.	8864KVA
Contact material	AgSnO ₂
Initial contact resistance	Max.100mΩ (100mA 6VDC)
Frequency of operation, with/without load	6 cycles / min (with load) 300 cycles / min (without load)
Operation/release time max., including bounce time	15ms/10ms

Power PCB Relay T9F Series

Power PCB Relays

CONTACT RATINGS

Contact	Load	Cycles
Normally open	Making 16A, carrying 32A, breaking 16A, 277VAC, 105C, resistive	10x10 ³
Normally open	32A 277VAC, 85C, resistive	10x10 ³
Mechanical endurance		1x10 ⁶

COIL DATA

Coil voltage range	9 VDC ~ 48 VDC
Coil insulation system according to UL	Class F

COIL VERSIONS, DC COIL (only for coil power D)

Coil code	Rated voltage VDC ¹⁾	Operation voltage VDC	Release voltage VDC	Coil resistance Ω±10%	Rated coil power W	Hold power W
9	9	7.2	0.45	67.5	1.2	min. 0.192
12	12	9.6	0.6	120	1.2	min. 0.192
24	24	19.2	1.2	480	1.2	min. 0.192
48	48	38.4	2.4	1920	1.2	min. 0.192

Notes:

- All figures above are given for coil without pre-energization at ambient temperature +23°C. Under this condition, after the energization time of 200ms with the rated voltage, the coil requires a reduction of the coil voltage to -30%-80% of the rated voltage.
- Under 105 ° C ambient temperature, after the energization time of 200ms with the rated voltage, the coil requires a reduction of the coil voltage to -40%-45% of the rated voltage. (Eg: 12VDC rated coil need to be reduced to the hold voltage of 4.8VDC-5.4VDC).
- Under 85°C ambient temperature, after the energization time of 200ms with the rated voltage, the coil requires a reduction of the coil voltage to -45%-50% of the rated voltage. (Eg: 12VDC rated coil need to be reduced to the hold voltage of 5.4VDC-6.0VDC).
- Only typical voltages listed, other coil voltages on request.

INSULATION DATA

Initial dielectric strength	
between open contacts	2,000Vrms
between contact and coil	4,000Vrms
Initial insulation resistance	
Initial insulation resistance	1000MΩ min.
Clearance/creepage	
between contact and coil	≥3/5mm
Flame resistance of plastic parts	UL94 V-0

OTHER DATA

Material compliance	For Eu RoHS/ELV, China RoHS, REACH, Halogen content refer to the product compliance support center at www.te.com/customer-support/rohssupportcenter
Ambient temperature	- 40 to +105°C
Temperature cycling (Shock)	1000cycles, -40/+105°C
Cold storage	240h, -40°C
Dry heat	240h, +105°C
Category of environmental protection IEC61810	RTII - flux resistant
Shock (functional, 11ms)	30g
Shock (destructive, 6ms)	100g
Vibration	10Hz - 55Hz, 1.5mm double amplitude
Terminal type	THT PCB type
Terminal strength (lead)	1.2kg
Weight	16 grams
Resistance to soldering heat THT	Tb, method 1A, hot dip 10s, 260°C with thermal screen
Package unit	100pcs/tray, 1000pcs/ carton box


Note:

The relay connections and wiring have to be designed with an adequate cross sections to help ensure the current flow and heat dissipation as well as contact ratings with relay properly vented.

Power PCB Relay T9F Series


Power PCB Relays

DIMENSIONS (Unit:mm)




PCB LAYOUT / TERMINAL ASSIGNMENT (Unit:mm)

Bottom view of solder pins



WIRING DIAGRAM




GENERAL TOLERANCE

Diagram Dimension	Tolerance
≤1mm	±0.2mm
1mm - 5mm	±0.3mm
≥5mm	±0.4mm

PART NUMBER LIST

Product Code	Version	Contact Arrangement	Contact Material	Coil	Part Number
T9FVID112,00000	PCB, flux-resistant	1 form A (NO) contact	AgSnO ₂	12VDC	2071581-1
T9FVID124,00000		1 form A (NO) contact	AgSnO ₂	24VDC	2071581-2
T9FVID148,00000		1 form A (NO) contact	AgSnO ₂	48VDC	2071581-3
T9FVID19,00000		1 form A (NO) contact	AgSnO ₂	9VDC	2071581-4

ORDERING INFORMATION



te.com

©2023 TE Connectivity. All Rights Reserved.

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

09/23 ED