# RCPT. ASS'Y, RIGHT ANGLE, CENTRONICS.

#### 1. SCOPE

### 1.1. CONTENTS

This specification covers performance, tests and quality requirements for RCPT. ASS'Y, RIGHT ANGLE, CENTRONICS connector.

#### APPLICABLE DOCUMENT 2.

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

Test Report: 501-57055

#### 3. **REQUIREMENTS**

## 3.1. DESIGN AND CONSTRUCTION

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

### 3.2. MATERIALS

- Α. Housing: Thermoplastic, UL 94V-0, Color: Black.
- Contact: Copper Alloy, Gold plating on contact area, Tin-lead or Tin B. plated on soldertails, Nickel underplated all over.

## 3.3. SOLDERTAILS, NICKEL UNDERPLATED ALL OVER.RATINGS

- Temperature range: -55°C to +125°C Α.
- Current rating: 5 Amperes Max. В.
- C. Humidity range: 25% to 85%.

# 3.4. PERFORMANCE AND TEST DESCRIPTION

The product is designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1.

DR	DATE	APVD	DATE
Oblic Hu	29-Jan-2004	Ted Ke	29-Jan-2004
			FZ00-0007-04





# 3.5. TEST REQUIREMENTS AND PROCEDURES SUMMARY

Figure 1

	T	Da su insura surta	D							
┝	Test Item	Requirements	Procedure							
1	Examination of Product	No Physical damage.	Visual.							
	Electrical Test									
2	Termination Resistance	Initial: 30 m $\Omega$ Max.	20 mV, 100 mA Max.							
	(Low Level)	Final: 40 m $\Omega$ Max.	MIL-STD-1344A							
3	Insulation Resistance	1000 MΩ Min.	500 V DC 2 minute							
			Adjacent circuits of							
			unmated connectors.							
4	Dielectric Withstanding	No creeping discharge nor flash	1200 V ac 1 min.							
	Voltage	over.	Current leakage :0.5 mA							
	Mechanical Test									
5	Connector Mating Force	Initial: 10.5 Kgf Max.	Operation speed: 25.4							
		Finial: 10.5 Kgf Max.	mm/min.							
6	Connector Unmating	Initial: 2.7 Kgf Min.	Operation speed: 25.4							
	Force	Finial: 2.7 Kgf Min.	mm/min.							
7	Durability	T/R: 40 m $\Omega$ Max.	Operation speed: 25.4							
		See note (a).	mm/min. Number of cycles:							
			500 cycles 20 mV, 100 mA							
			Max.							
	Environmental Test									
8	Humidity	T/P: 40 m Ω Max.	Mated connector. 40±2℃							
		See note (a).	90~95%R.H.for 96 Hours.							
9	Thermal Shock	T/P: 40 m $\Omega$ Max.	Mated connector55℃							
		See note (a).	/30min., 85°C/30min.							
		, .	5 cycles.							
10	Salt Spray	T/P: 40 mΩ Max.	Mated connectors. 5%,							
		See note (a).	35℃ for 6 hours							
I										

<sup>(</sup>a) Shall meet visual requirements, show no physical damage, and shall meet requirements of additional test as specified in the Test Sequence in Figure 2.

Rev A 2 of 3



# 3.6. PRODUCT QUALIFICATION AND REQUALIFICATION TEST SEQUENCE

Test or Examination		Test Group				
		1	2	3	4	
		Test Sequence				
1	Examination of Product	1,9	1,7	1,6	1,3	
2	Termination Resistance (Low Level)	2,6	3,6			
3	Insulation Resistance		2,5	2,5		
4	Dielectric Withstanding Voltage			3		
5	Connector Mating Force	3,7				
6	Connector Unmating Force	4,8				
7	Durability	5				
8	Humidity			4		
9	Thermal Shock		4			
10	Salt Spray				2	
	Sample Quantity (Connector)	5	5	5	5	

Figure 2(end)

Rev A 3 of 3