


## EVC 250-800 Main Contactor

- Limiting continuous current 250A at 85°C
- Suitable for voltage levels up to 900VDC
- High peak current carrying capability up to 6000A<sup>1)</sup>

### Typical applications

- DC high voltage high current applications
- Main contactors for hybrid, full battery electric vehicles and fuel-cell cars
- Battery charging systems



Contact Data	
Contact arrangement	1 form X (SPST NO DM)
Rated voltage	800VDC
Maximum switching voltage	900VDC, dep. on load characteristics <sup>1)</sup>
Rated current	load cable 50mm <sup>2</sup>
Forward load current direction	250A
Limiting continuous current	load cable 50mm <sup>2</sup>
85°C	250A
Limiting short time current	load cable 50mm <sup>2</sup>
85°C	400A 5min 600A 1min 6000A 20ms
Limiting make current	5x10 <sup>4</sup> x250A at 50VDC

Contact Data (continued)	
Limiting break current	1x650A at 800VDC
Forward load current direction	5000x100A at 800VDC
altitude max 5500m	5x10 <sup>4</sup> x50A at 800VDC
Limiting break current	1x415A at 300VDC
Reverse load current direction	20x50A at 800VDC
altitude max 5500m	1x10 <sup>4</sup> x20A at 800VDC
Voltage drop (initial) at 100A	max. 40mV after 60s <sup>2)</sup>
Voltage drop (over lifetime) at 250A	typ. 50mV after 60s <sup>3)</sup>
Operate time <sup>4)</sup>	max. 25ms
Release time <sup>4)</sup>	max. 10ms <sup>5)</sup>
Mechanical endurance	>2x10 <sup>5</sup> ops.

1) Please contact TE Connectivity for details.

2) Measurement condition: 370A for 2s followed by 100A for 60s.


3) Max. 600mV with current >1A.

4) At rated coil voltage.


5) Without arc duration (only mechanical contact opening considered).

## EVC 250-800 Main Contactor (Continued)


Coil operating range (12V single coil version)



Coil operating range (12V dual coil version)



Coil operating range (24V dual coil version)



### Coil Data<sup>6)</sup>

#### Un-economized: single coil version for external economization<sup>7)</sup>

Coil code	Rated voltage [VDC]	Operate voltage [VDC]	Max. cont. voltage [VDC]	Non-release voltage [VDC]	Coil resistance [Ω]
0101	12	6.0	5.0	2.0	±10% 3.9

#### Recommended parameters for external economization with PWM<sup>7)</sup>

Min. frequency [kHz]	Controlled current Max. current [A]	PWM Min. current [A]	Controlled voltage Max. voltage [V]	equivalent Min. voltage [V]
15	1.0	0.5	5.9	2.6

#### Economized: dual coil version with internal switch<sup>9)</sup>

Coil code	Rated voltage [VDC]	Operate voltage <sup>10)</sup> [VDC]	Nominal inrush current [ADC]	Non-release voltage [VDC]	Max. voltage [VDC]	Coil resistance [Ω]
0102	12	7.6	4.7	4.0	16.0	±10% 2.6/26 <sup>11)</sup>
0112	24	15.2	4.8	8.0	32.0	±10% 5.0/79 <sup>11)</sup>

### Insulation Data

Initial dielectric strength	
between open contacts	4000VDC / 3mA
between contact and coil	4000VDC / 3mA
Insulation resistance after abuse test	
between open contacts	>200MΩ
between contact and coil	>200MΩ
Clearance/creepage	
acc. IEC 60664-1 (2007) for	over voltage category I, pollution degree 2
Max. altitude	5500m

### Other Data

Ambient temperature	-40°C to +85°C
Degree of protection	IEC 60529 (2000-09) IP54 <sup>12)</sup>
Vibration resistance (functional)	
IEC 60068-2-6 (2007-12) sine sweep	10 to 500Hz, min. 10g No change of switching state >10μs.
Shock resistance (functional)	
IEC 60068-2-27(2008-02) half sine	closed: 11ms, min. 40g open: 11ms, min. 20g No change of switching state >10μs.
Terminal type	connector (coil) and screw (load)
Weight	approx. 525 / 580g (18.5 / 20.5oz), depending on version
Packaging unit	20 pcs.

- 6) All values valid for 23°C ambient temperature with no pre-energization if not noted otherwise. Refer to diagram for values at other temperatures.
- 7) Requires external coil economization that must start 100-300ms after coil activation. Avoid repetitive switching. Minimum clamp voltage 60V (see circuit recommendation).
- 8) Demagnetization voltage is clamped at ~70V. External coil suppression is not necessary and could reduce switching capability. Contact TE Connectivity for details.
- 9) Max. duty cycle 0.5Hz.
- 10) Max. rise time 100ms.
- 11) 2.6Ω coil / 5.0Ω coil is switched off internally max. 250ms after pull-in
- 12) Protection class applicable for all mounting orientations except load terminals upwards.



