



# Current Capacity

TE Connectivity Rail Thin Wall Signal Wire Products

WTDS-025

Issue 1

22.04.2020

Page 1 of 5

## Current Rating of Rail Thin Wall Signal Wire

Table 1

Nominal conductor cross sectional area (mm <sup>2</sup> )	Current Carrying Capacity I <sub>Cable</sub> (A)
0.25	9.5
0.40	12.9
0.50	14.9
0.60	16.8
0.75	19.4
1.00	23.4
1.20	26.3
1.50	30.4
2.00	36.7
2.50	42.4
3.00	47.7
4.00	57.5

Current Carrying Capacity as calculated by TE Connectivity using EN 50343:2014

45°C Ambient temperature (TCRefAmb)

120°C maximum conductor operating temperature (TCRefMax)

In free air.

For conditions other than the above, the following equation should be used;

$$I_{Corr} = I_{Cable} \times K^* \times K_1 \times K_2 \times K_3 \times K_4 \times K_5$$

Where:

K\* is a correction factor for the expected maximum temperature

K<sub>1</sub> is a correction factor for the expected ambient temperature.

K<sub>2</sub> is a correction factor for installation type

K<sub>3</sub> is a correction factor to allow for a decrease in the expected cable lifetime

K<sub>4</sub> is a correction factor to take into account the short time current when operation is not continuous.

K<sub>5</sub> is a correction factor for multi-core cables

Correction factors K<sub>3</sub> and K<sub>4</sub> are assumed to 1.0 unless stated otherwise.

Author

P. Watson

Prod. Development Engineer

TE Connectivity

Approver

P. Crofts

Product Manager

TE Connectivity

## Modification Factor K\*

Calculating current ratings for temperature classes other than 120°C

Table 2

TC <sub>Max</sub> (°C)	Factor K*
90	0.808
105	0.913
120	1.000
140	1.096
150	1.138

For temperature classes other than 120°C, the values in Table 1 shall be multiplied by the values in Table 2.

For other maximum temperatures not listed in Table 2, use the following equation;

$$K_* = \sqrt{\frac{(TC_{Max} - TC_{RefAmb}) * (1 + (0.004 * TC_{RefMax}))}{(TC_{RefMax} - TC_{RefAmb}) * (1 + (0.004 * TC_{Max}))}}$$

$$K_* = \sqrt{\frac{(TC_{Max} - 45) * (1 + (0.004 * 120))}{(120 - 45) * (1 + (0.004 * TC_{Max}))}}$$

Where:

**TC<sub>RefAmb</sub>** The ambient temperature in °C for which I<sub>Cable</sub> is correct.

**TC<sub>Max</sub>** The Maximum cable/conductor temperature in °C for which we want the current capacity.

**TC<sub>RefMax</sub>** The maximum cable/conductor temperature in °C for which I<sub>Cable</sub> is correct.

Author

P. Watson

Prod. Development Engineer

TE Connectivity

Approver

P. Crofts

Product Manager

TE Connectivity



# Current Capacity

TE Connectivity Rail Thin Wall Signal Wire Products

WTDS-025

Issue 1

22.04.2020

Page 3 of 5

## Modification Factor $K_1$

Derating factor for ambient temperatures other than 45°C

Table 3

Expected Ambient Temperature - $TC_{Amb}$ (°C)	Factor (Maximum conductor Temperature of 90°C)	Factor (Maximum conductor Temperature of 120°C)
35	1.11	1.07
45	1.00	1.00
55	0.88	0.93
65	0.75	0.85
75	0.58	0.76
85	0.33	0.68

For other maximum temperatures not listed in Table 3, use the following equation:

$$K_1 = \sqrt{\frac{(TC_{Max} - TC_{Amb})}{(TC_{Max} - TC_{RefAmb})}}$$

Where:

$TC_{Amb}$  The ambient temperature in °C which we want the current capacity for.

$TC_{RefAmb}$  The ambient temperature in °C for which  $I_{Cable}$  is correct.

$TC_{Max}$  The Maximum cable/conductor temperature in °C for which we want the current capacity.

Author	P. Watson	Prod. Development Engineer	TE Connectivity
Approver	P. Crofts	Product Manager	TE Connectivity

## Modification Factor $K_2$

Derating factor  $K_2$  for installation type (grouping and installation conditions)

Table 4

Number of cables being simultaneously loaded	Installation Type			
	Cable in free air	Cables on trays, in one layer	Cables on trays, in two layers	Cables on trays, in several layers
	Type (a)	Type (b)		Type (c)
1 single cable	1.00	1.00	1.00	1.00
2 cables together	-	0.87	0.87	0.87
3 cables together	-	0.83	0.83	0.78
4 cables together	-	0.78	0.71	0.71
up to 8 cables together	-	0.74	0.59	0.52
up to 12 cables together	-	0.73	0.54	0.45
up to 16 cables together	-	0.72	0.51	0.41
17 cables and above together	-	0.71	0.47	0.38

  

Number of cables being simultaneously loaded	Installation Type			
	Cables on the floor or on a wall	Cables on a ceiling or under floor	Cables in a closed tube, conduit or tray	Cables in a closed tube or conduit, thermally insulated
	Type (d)	Type (e)	Type (f)	Type (g)
1 single cable	1.00	0.95	0.95	0.76
2 cables together	0.85	0.81	0.80	0.61
3 cables together	0.79	0.72	0.70	0.53
4 cables together	0.75	0.68	0.65	0.49
up to 8 cables together	0.75	0.62	0.52	0.40
up to 12 cables together	0.75	0.61	0.45	0.34
up to 16 cables together	0.75	0.61	0.41	0.31
17 cables and above together	0.75	0.61	0.38	0.29

Author

P. Watson

Prod. Development Engineer

TE Connectivity

Approver

P. Crofts

Product Manager

TE Connectivity



# Current Capacity

TE Connectivity Rail Thin Wall Signal Wire Products

WTDS-025

Issue 1

22.04.2020

Page 5 of 5

## Modification Factor $K_5$

Derating factor  $K_5$  for installation type (grouping and installation conditions)

Table 5

Number of Loaded Cores	2	3	4	5	7	9	12	19
Correction Factor $K_5$	0.91	0.78	0.63	0.59	0.51	0.46	0.41	0.38

The information contained in this document is for reference only and may be subject to change.

Current carrying capacity of TE Connectivity products should be calculated in conjunction with TE Connectivity.

Using thermal ageing data, TE Connectivity can help to ensure that the current capacity values used are not only safe and suitable for the required application, but also that the life expectancy of the cable is acceptable.

The information contained in this document relates to TE Connectivity's *100G CK0226, 100E, 100RL, RL and EN50306-2-RAIL* product lines.