



## DEUTSCH AUTOSPORT INTERCONNECTION SOUTIONS FOR PROFESSIONAL MOTORSPORTS

HIGH-PERFORMANCE CONNECTORS DESIGNED FOR HARSH-ENVIRONMENT MOTORSPORT

## **DEUTSCH Autosport Interconnection Solutions**



#### **DEDICATED INDUSTRIAL ENGINEERING & MANUFACTURING SITES**

- Bydgoszcz, Poland
- Christchurch, New Zealand
- Hermosillo, Mexico
- Landisville, USA
- Trutnov, Czech Republic
- Tokyo, Japan
- Shanghai, China
- Darmstadt, Germany
- Harrisburg, USA
- Hastings, UK

India

Italy

• Japan

Latvia

Ireland

#### **PRODUCT INFORMATION CENTERS (PIC)**

• Denmark

• Estonia

• Finland

France

• Germany

- Austria
- Australia
- Belgium
- Brazil
- China
- Czech Republic Greece

- Lithuania

- Poland
- Portugal
- Russia Slovakia
- Slovenia
- South Africa
- South Korea
- Spain
- Sweden
- Switzerland
- Taiwan
- Turkey
- United Kingdom
- United States



- - Netherlands
  - Norway

  - Luxembourg

- Hungary

## **DEUTSCH Autosport Interconnection Solutions**



# **DEUTSCH AUTOSPORT** INTERCONNECTION SOLUTIONS

CONSISTENTLY LEADING THE WAY IN RESEARCH, DEVELOPMENT, INNOVATION, RELIABILITY & SERVICE

TE Connectivity (TE) with its DEUTSCH Autosport connection systems offers unrivalled expertise in the design and manufacture of interconnection solutions for harsh environments. With over 40-years of international experience, DEUTSCH products are well proven in the Aerospace, Defence, Industrial Transportation and Autosport markets.

In the early 1990's DEUTSCH products were the first to pioneer a range of interconnection solutions specifically for the Autosport industry, enabling them to reach their position as market leader. The AS Series and AS Micro Series radically changed the face of autosport connection technology. Following the success of these products, TE's DEUTSCH Autosport team was established to attend to the growing needs of the autosport teams and harness houses.

A knowledgeable and experienced team of experts, supported with considerable investment in research and backed by an international distribution network, ensures TE's DEUTSCH autosport range of connectors continue to meet the constantly evolving technical challenges faced in this dynamic and demanding industry.

Specified across the entire autosport industry, TE's DEUTSCH products dominance in the autosport industry has been proven many times, with world champions across practically every discipline choosing TE's DEUTSCH Autosport connectors as the most reliable, light weight and technologically advanced products available.

#### CONTENTS

4 Product Overview

6	AS Size 1 Micro XtraLITE HE 4 Way Connector
8	AS Micro XtraLITE HE 3 Way Connector
10	AS Micro XtraLITE HE 5 Way Connector
12	AS Micro XtraLITE HE 6 Way Connector
14	AS Ultra <sup>LITE</sup> HE and AS Micro Ultra <sup>LITE</sup> HE (ASU) Series Connectors
16	AS MicroLITE HE (ASL) Series Connectors
18	AS Rally Micro (ASR) Series Connectors
20	AS Composite (ASC) Series Connectors
22	AS Mini Series Connectors
24	AS Series Connectors
30	AS Double Density (ASDD) Series Connectors
32	AS Micro HE Hermetic Series Connectors
33	AS Micro Hermetic (Jam-Nut) Series Connectors
35	AS Hermetic Fuel Tank Series Connectors
36	AS Micro $^{\mbox{\tiny LTE}}$ HE Fuel Immersible Series Connectors
38	AS Heavy Duty (ASHD) Series Connectors
40	AS Co-ax Series Connectors
40	Portable Antenna
41	Special Contacts
42	AS4 Flangless Option
42	Clinchnut AS Series Connectors
43	Low Profile PCB Connectors
44	AS3 Through Bulkhead
45	Fibre Optics Series Connectors
45	Black Zinc Nickel Option
46	Termination Boots and Accessories
47	How to Order

48 Reference Guide

## **Product Overview**

The original autosport connector – the AS Series connector – continues to set the standard for the autosport industry. Invented by TE's DEUTSCH autosport engineers for the 93/94 season, the AS Series connector has been used by race winning teams throughout autosport ever since.

TE Connectivity (TE) with its DEUTSCH connectors continues to push the boundaries of technology and innovation, consistently driving the market forwards with new products that match the ever increasing demands of lower weight, smaller size and better performance. All DEUTSCH connectors are thermal cycle tested and environmentally sealed to IP67 when mated\*. All DEUTSCH autosport connectors also offer:

- Compact design/minimum space envelope
- Interfacial & wire sealing
- Boot termination feature
- PCB option
- Universal option available (not ASC)
- Standard crimp tooling
- Suitable for blind mating
- Visual indication of keyway orientation of connector

- Scoop-proof interface
- Shell-to-shell grounding (not ASC)
- Positive locking coupling mechanism
- No need for backshells o boot termination
- In-line and two hole mounting styles (not ASC)
- Surface finishing options
- Keyway options
- \*1 metre for 30 minutes minimur

#### MATERIALS

**Shell / coupling ring:** High strength aluminum alloy with a conductive black zinc finish\*\*

Contacts: Gold plated crimp contacts\*

Insulators: Thermoplastic

**Interface / wire seals:** Fluorinated silicone.

\*Except hermetic connectors \*\*Except hermetic and ASC connector

#### VIBRATION

All connectors undergo three rigorous tests for vibration and all exceed the following:

Dynamic test - random on random 60g RMS in 3 axis.

Endurance test - random 57g RMS in 2 axis for 8 hours each axis.

Sinusoidal resonance to over 75g.

#### **FLUID RESISTANCE**

All connectors show no damage when exposed to most fluids used n most autosport applications.

#### AS MICRO XTRALITE HE (ASX) SERIES CONNECTORS

The AS Micro Xtra<sup>Lite</sup> HE connectors offer teams the smallest, lightest package for three, four, five and six wires. The AS Micro Xtra<sup>Lite</sup> HE 6-way is the shortest, lightest AS connector for six wires, offering a solution where space is at its most restrictive. Refer to pages 6,8, 10 and 12 for technical specifications.

#### AS MICRO ULTRALITE HE (ASU) SERIES CONNECTORS

The AS Micro Ultra<sup>Lite</sup> HE connectors offer the teams a small and lightweight connector for 3 and 5 wires. The AS Micro Ultra<sup>Lite</sup> HE connectors are a perfect solution where space and weight are restricted. Refer to page 14 for technical specifications.

#### AS MICROLITE HE (ASL) SERIES CONNECTORS

The Micro<sup>Lite</sup> HE connector is in excess of 30% lighter than the original AS Micro HE connector and approximately 8mm shorter, whilst still retaining all the critical features including the renowned TE's DEUTSCH #23 contacts. The AS Micro<sup>Lite</sup> HE connector is fully intermateable with the AS Micro HE connector. Refer to page 16 for technical specifications.

#### AS RALLY MICRO (ASR) SERIES CONNECTORS

An evolution of the AS Micro<sup>Lite</sup> HE connector, the AS Rally Micro connector has been created with direct input from World Rally Teams. A wider coupling ring and more knurling enables mechanics wearing gloves to get a better grip when connecting and disconnecting in severe environments (snow, ice and mud). Refer to page 18 for technical specifications.

#### AS COMPOSITE (ASC) SERIES CONNECTORS

Made as one unit, in a military approved, rugged thermoplastic housing, the AS Composite connector is extremely resistant to vibration. Refer to page 20 for technical specifications.

#### AS MINI SERIES CONNECTORS

The AS Mini Series connector bridges the gap between the existing standard AS Series (Size 8) and the AS Micro range (Size 6), offering 6-way and 3-way connectors in three shell styles. Refer to page 22 for technical specifications.

## **Product Overview**

#### AS SERIES CONNECTORS

Developed by TE's DEUTSCH engineers from the MIL-C-38999 Series 1.5 (Eurofighter connector), the AS Series connector was the first range of high specification connectors designed by TE's DEUTSCH Autosport specifically for the autosport market. The AS Series connector offers weight and space saving over standard military designs and is available a wide variety of options, with medium and high density arrangements up to 128 ways with four shell styles, and five keyway orientations. Refer to page 24 for technical specifications.

#### AS DOUBLE DENSITY (ASDD) SERIES CONNECTORS

Next generation connector technology developed by TE's DEUTSCH Autosport, which brings together high density and high performance, inline with racing teams using smaller wire sizes. The AS Double Density range allows almost double the number of contacts to be packaged in the same shell as compared to the standard AS Series connectors. Refer to page 30 for technical specifications.

#### AS MICRO HE HERMETIC SERIES CONNECTORS

A unique hermetic receptacle developed by TE's DEUTSCH Autosport for transducers, sensors and instrumentation where space and performance is critical. The AS Micro HE Hermetic Series connector offers high density, harsh environment sealing as standard and is more compact than any other product currently available on the market. Mounting and ease of termination has also been a major consideration with PCB style contacts and weld mounting (316 St) offered as standard. Refer to page 32 for technical specifications.

#### AS MICRO HERMETIC (JAM-NUT) SERIES CONNECTORS

An evolution of the AS Micro HE Hermetic connectors featuring a jam-nut, this connector is ideally suited to fuel tank applications. Refer to page 33 for technical specifications.

#### AS HERMETIC FUEL TANK SERIES CONNECTORS

A range of hermetically sealed connectors designed specifically for autosport fuel tank applications. AS Hermetic Fuel Tank connector provides a high degree of performance where normal resilient connectors would fail, by using glass to metal sealing in place of traditional plastic and elastomer inserts. Connectors are supplied with a fuel immersible specification o-ring to provide a high standard of sealing between the connector and bulkhead. Refer to page 34 for technical specifications.

## AS MICRO<sup>LITE</sup> HE FUEL IMMERSIBLE SERIES CONNECTORS

An evolution of the AS Micro<sup>Lite</sup> connector, the AS Micro<sup>Lite</sup> Fuel Immersible connector contains a unique DEUTSCH designed fuel resistant elastomer insert which offers excellent resistance to racing fuel. An upgraded hermetic version, including an inline receptacle is also available. Refer to page 36 for technical specifications.

#### AS HEAVY DUTY (ASHD) SERIES CONNECTORS

A range of power connectors designed specifically for Autosport high current applications. The AS Heavy Duty connectors are ideally suited to battery, alternator, starter motor and energy recovery system applications. Specially designed low insertion / extraction force contacts ensure maximum performance in extreme conditions. Refer to page 38 for technical specifications.

#### FIBRE OPTICS SERIES CONNECTORS

TE's DEUTSCH Autosport connectors also offer Fiber Optic solutions. Refer to page 45 at the back of this brochure for more information.

## AS Size 1 Micro Xtraure HE 4 Way Connector

#### Ultra compact design (size 01 shell)

- Minimum space envelope
- 4 contacts Size #24
- PCB option
- Smaller and lighter than AS Ultraute (ASU) series connectors


#### **Easy installation**

- Positive locking coupling mechanism
- Suitable for blind mating

- Scoop proof interface
- Boot termination feature

#### Built to withstand harsh environments

- Conductive black zinc nickel finish
- Interfacial wire sealing
- Bonded and sealed insert to help prevent moisture ingress



## AS Size 1 Micro XtraLITE HE 4 Way Connector

#### **GENERAL SPECIFICATION**


No. of Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement & Disengagement)	Dielectric Withstanding Voltage (VAC)	No. of Keyway Orientations		ealing m) Max.	Tempe (° ( Min.	
4	24	01	3	500	1000	6	0.56	1.02	-55	+170

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current. Contact Technical Support for more detail of specific products to meet your sealed electrical connection requirements.


#### **CONTACTS & TOOLING PART NUMBERS**


Contact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
24	612879-99	612876-99	611292	611661	600300-24	605837	M22520/2-01	605840	605839

#### **ORDERING INFORMATION**




Pro Cap 4 Way Plug





Pro Cap 4 Way Receptacle



Part N	umber		Boot Inf	ormation		Pro	Сар
Nut Plate	Gasket		Straight 90 degree			Socket	Pin
ATM396-1	GV-1 Rayo		203W301-25-G02	223W601		611292	611661

## AS Micro XtraLITE HE 3 Way Connectors



#### Ultra compact design (Size 02 shell)


- Minimum space envelope
- 3 contacts Size #22
- PCB option
- Smaller and lighter than AS Ultra<sup>LITE</sup> (ASU) series connectors

#### **Easy installation**

- Positive locking coupling mechanism
- Suitable for blind mating
- Scoop proof interface
- Boot termination feature

#### Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress



## AS Micro XtraLITE HE 3 Way Connectors

1	GENERAL SPECIFICATION													
	No. of Wavs	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations		ealing m)	Temperature (°C)*				
	Way5	SILC	SILC	(////////	Disengagement)	Voltage (VAC)	onentations	Min.	Max.	Min.	Max.			
	3	22	02	3	500	1500	6	0.76	1.37	-55	+170			

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current. Contact Autosport Technical Support for more detail of specific products to meet your sealed electrical connection requirements.

CONTACTS & TOOLING PART NUMBERS

	ntact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
Ĩ	22	604984	604946-31	611282	611254-31	600300-22	M81969/14-01	M22520/2-01	605464	605463

#### ORDERING INFORMATION

	ASX	*	02	-	03	*	* - HE	****
Range Ref:								
<b>Style:</b> O = 2 Hole Flange Receptacle 1 = Inline Receptacle 2 = 2 Hole Flange Receptacle with 6 = Free Plug	PCB Contacts							
Shell Size:								
Contact Arrangement:								
Insert Type: P = Pin S = Socket								
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal for Test Harnesses - Plug Type 6 only)								
HE: Harsh Environment								
Modification Code:								

Part N	Part Number			Cap		Boot Info	ormation
Nut Plate	Gasket		Receptacle	Plug		Straight	90 Degree
ATM396-2	ATM396-2 GV-2		611545	611546	Raychem	203W301-25-G02	223W601
					Hellermann	1037-4-G	1182-4-G

## AS Micro XtraLITE HE 5 Way Connectors



#### Ultra compact design (size 02 shell)


- Minimum space envelope
- 5 contacts Size #24
- PCB option
- Smaller and lighter than AS UltraLITE (ASU) series connectors


#### **Easy installation**


- Positive locking coupling mechanism
- Suitable for blind mating
- Scoop proof interface
- Boot termination feature


#### Built to withstand harsh environments


- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress














## AS Micro XtraLITE HE 5 Way Connectors

#### **GENERAL SPECIFICATION**

No. of Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement & Disengagement)	Dielectric Withstanding Voltage (VAC)	No. of Keyway Orientations	(m	ealing m)	Temperature (°C)*	
				Diseligagement)	vollage (vAC)		Min.	Max.	Min.	Max.
5	24 02 3 500		1000	6	0.56	1.02	-55	+170		

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current. Contact Autosport Technical Support for more detail of specific products to meet your sealed electrical connection requirements.

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
24	605704	605705-31	611292	611661-31	600300-24	605837	M22520/2-01	605840	605839

#### **ORDERING INFORMATION**

	ASX	*	02	_	05	*	*	-HE	****
Range Ref:									
<b>Style:</b> O = 2 Hole Flange Receptacle 1 = Inline Receptacle 2 = 2 Hole Flange Receptacle with R 6 = Free Plug	PCB Contacts								
Shell Size:									
O5									
Insert Type: P = Pin S = Socket									
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal for Test Harnesses- Plug Type 6 only)									
HE: Harsh Environment									
Modification Code:									

Part Number				Boot Info	prmation	Pr	o Cap
Nut Plate	Gasket			Straight	90 Degree	Receptacle	Plug
ATM396-2	GV-2		Raychem	203W301-25-G02	223W601	611545	611546
			Hellermann	1037-4-G	1182-4-G		

## AS Micro XtraLITE HE 6 Way Connectors







#### Ultra compact design (size 02 shell)

- Minimum space envelope
- 6 contacts Size #24
- PCB option
- Smaller and lighter than AS Ultra<sup>LITE</sup> (ASU) series connectors


#### **Easy installation**


- Positive locking coupling mechanism
- Suitable for blind mating
- Scoop proof interface
- Boot termination feature

#### Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Gold-plated crimp contacts
- Bonded and sealed insert to prevent moisture ingress







18.40 MAX


ABBREVIATED PART No. AND BATCH No. BEHIND THE COLOUR BAND 10.25 MAX VER KNURL

12.10 MAX


0

 $\bigcirc$ 

COLOUR BAND







AEROSPACE, DEFENSE & MARINE / DEUTSCH AUTOSPORT INTERCONNECTION SOLUTIONS

MAX MAX

9.70 8.40

## AS Micro XtraLITE HE 6 Way Connectors

#### **GENERAL SPECIFICATION**

No. of Ways	Contact Size	Shell Size	Max. Current	Durability (Cycles of Engagement &	Dielectric Withstanding Voltage (VAC)**	No. of Keyway Orientations	Wire Sealing (mm)		Temperature (°C)*	
			(Amps)	Disengagement)	voltage (vac)		Min.	Max.	Min.	Max.
6	24	02	3	500	1000	6	0.56	1.02	-55	+170

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
24	605704	605705-31	611292	611661-31	600300-24	605837	M22520/2-01	605840	605839

#### ORDERING INFORMATION

	ASX	*	02	_	06	*	*	-HE	***	**
Range Ref:										
<b>Style:</b> O = 2 Hole Flange Receptacle 1 = Inline Receptacle 2 = 2 Hole Flange Receptacle with 6 = Free Plug	PCB Contacts									
Shell Size:										
Contact Arrangement:										
Insert Type: P = Pin S = Socket										
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal for Test Harnesses- Plug Type 6 only)										
HE: Harsh Environment										
Modification Code:										

Part N	lumber		Boot Info	ormation		Pro Cap
Nut Plate	Gasket		Straight	90 Degree	Receptacle	Plug
ATM396-2	GV-2	Raychem	203W301-25-G02	223W601	611636	611637
			1037-4-G	1182-4-G		

## AS UltraLITE HE & AS Micro UltraLITE HE (ASU) Series Connectors



#### **Unique DEUTSCH designed product**

- Smaller alternative to ASL range
- Cable accommodation 24-30 AWG (5 way), 22-28 AWG (3 way)
- 17% smaller coupling ring than ASL
- 30% lighter than ASL (mated pair)


#### 2 different contact options

- 5x AWG24 contacts
- 3x AWG22 contacts


## Built to withstand harsh environments


- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress

**INLINE RECEPTACLE - TYPE 1** 




**RECEPTACLE - TYPE 0** 





#### PANEL CUT-OUT DETAIL



All dimensions are in mm unless otherwise stated.

PLUG – TYPE 6

## AS UltraLITE HE & AS Micro UltraLITE HE (ASU) Series Connectors

#### **GENERAL SPECIFICATION**

	No. of Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement	Dielectric Withstanding	ing No. of Keyway Orientations		ealing m)	Tempe (°	
	mayo	0120	0120	(	& Disengagement)	Voltage (VAC)**	onentations	Min.	Max.	Min.	Max.
ĺ	3	22	03	5	500	1500	6	0.76	1.37	55	+170
	5	24	03	3	500	1000	0	0.56	1.02	-55	+1/0

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
22	604984	604946-31	605681	605679-31	600300-22	M81969/14-01	M22520/2-01	605464	605463
24	605704	605705-31	605902	605900-31	600300-24	605837	1122320/2-01	605840	605839

#### **ORDERING INFORMATION**

		A	SU	*	03	—	**	*	*	-HE	***
Range Ref: ⊢											
<b>Style:</b> O = 2 Hole Flar 1 = Inline Recep 2 = 2 Hole Flar 6 = Free Plug	otacle		B Contacts								
Shell Size: ⊢											
<b>Contact Arran</b> 03, 05	gement:										
Insert Type:P = PinS = Socket											
Shell Keyways N = Red (Stand A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal Plug Type	dard) for Test Ha	arnesses-									
HE: Harsh Env											
		-									

#### Modification Code:

Pro	Сар					Boot Info	ormation
Receptacle	Pluq	Nut Plate	Gasket			Straight	90 Degree
		171170.0 4			Raychem	204W221-25-G03	224W221-25-G03
605684	605687 ATM396-4		GV-3		Hellermann	1037-4-G	1182-4-G

## AS MicroLITE HE (ASL) Series Connectors







#### **Compact design (size 06 shell)**

- Designed for sensor applications
- 5 contacts Size #23
- PCB option


#### **Easy installation**

- Positive locking coupling mechanism
- Suitable for blind mating
- Scoop proof interface
- Boot termination feature


#### Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress


#### PLUG - TYPE 6




#### **INLINE RECEPTACLE - TYPE 1**




#### PANEL CUT-OUT DETAIL



#### **RECEPTACLE - TYPE 0**





## AS Micro<sup>LITE</sup> HE (ASL) Series Connectors

GLINE	SENERAL SPECIFICATION												
No. of Co Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations	Wire S (m	iealing m)	Temperature (°C)*				
mays	SILC	SILC	(11103)	Disengagement)	Voltage (VAC)**	onentations	Min.	Max.	Min.	Max.			
5	23	06	3	500	1000	6	0.60	1.37	-55	+170			

#### **GENERAL SPECIFICATION**

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	PCB Socket	PCB Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
23	604935	604927-31	604992-HE	604990-31	600300-22	M81969/14-01	M22520/2-01	604973	604972

#### **ORDERING INFORMATION**

	ASL	*	06 — 05	*	* _	HE	_ ***
Range Ref:							
<b>Style:</b> O = 2-Hole Flange Re 1 = Inline Receptacle 2 = 2-Hole Flange Re 6 = Free Plug	eceptacle eceptacle with PCB Contacts						
Shell Size:							
Contact Arrangeme	nt:						
<b>Insert Type:</b> P = Pin S = Socket							
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal for Test Plug Type 6 on							
Harsh Environment:							
Modification Code:							

Pro	Cap	Nut Plate	Gasket		Boot Info	ormation
Receptacle	Plug				Straight	90 Degree
604029	604027	ATM396-6	GV-6	Raychem	204W221	224W221
				Hellermann	1030-4-G	1181-4-G

## **AS Rally Micro (ASR) Series Connectors**



#### Compact design (size 06 shell)

- Specialised coupling ring for poor grip locations
- 5 contacts Size #23


#### **Easy installation**

- Positive locking coupling mechanism
- Suitable for blind mating
- Scoop proof interface
- Boot termination feature

# Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress

#### PLUG - TYPE 6



## **AS Rally Micro (ASR) Series Connectors**

GENER	GENERAL SPECIFICATION											
No. of Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations	Wire Sealing (mm)		Temperature (°C)*			
ind j 5	5120	5120	(//////////////////////////////////////	Disengagement) Voltage (VAC)**		orientations	Min.	Max.	Min.	Max.		
5	23	06	3	500	1000	6	0.60	1.37	-55	+170		

#### \* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
23	604935	604927-31	600300-22	M81969/14-01	M22520/2-01	604973	604972

#### **ORDERING INFORMATION**

	ASR	6	06 — 05	*	* _	HE	_ *	**
Range Ref:								
Style: 6 = Free Plug								
Shell Size:								
Contact Arrangement:								
Insert Type: P = Pin S = Socket								
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey U = Violet (U = Universal for Test Harnesses - Plug Type 6 only								
Harsh Environment:								
Modification Code:								

ASR = Enhanced Plug, for mating Receptacles see ASL page 16

Pro Cap		Boot Info	ormation
604027		Straight	90 Degree
	Raychem	204W221	224W221
	Hellermann	1030-4-G	1181-4-G

## **AS Composite (ASC) Series Connectors**




#### Extremely resistant to vibration


• Military approved rugged thermoplastic housing


#### **Unique installation options**

- Bondable with suitable adhesive in different configurations
- Cable-tie slot for security and mounting inline connections designed to fit Thomas & Betts part no. TY24 or equivalent
- Close stacking possible with locating sides and bottom


MATED PAIR










PLUG -TYPE 6








**RECEPTACLE - TYPE 1** 





## **AS Composite (ASC) Series Connectors**

OLIVE		LCIII	CAHON							
No. of Ways	Contact Size	Shell Size	Max. Current	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations	Wire S (m	m)	(	erature ° C)*
			(Amps)	Disengagement)	Voltage (VAC)**		Min.	Max.	Min.	Max.
6	22	06	5	300	1500	6	0.76	1.37	-55	+170

#### **GENERAL SPECIFICATION**

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
604984	604946-31	600300-22	M81969/14-01	M22520/2-01	605464	605463

#### **ORDERING INFORMATION**

	ASC	*	05 — 06	* *	* ***
Range Ref:					
<b>Style:</b> 1 = 1 Inline Receptacle 6 = Free Plug					
Shell Size:					
Contact Arrangemen	it:				
Insert Type: P = Pin S = Socket					
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey					
Modification Code:					

Part Numbers: Receptacle: ASC105-06SN Plug: ASC605-06PN

Please note: Plug only available in pin arrangement, Receptacle only available in socket arrangement.


	Boot Info	prmation
	Straight	90 Degree
Raychem	204W221	224W221
Hellermann	1030-4-G	1181-4-G


## **AS Mini Series Connectors**




- Size 07 shell Smaller option to Mil size 08
- 2 planform options 3 or 6 contact options
- Integral screen termination
   Ideal for braided cable installations
- Cable accommodation 20, 22, 24 and 26 AWG
- Offers size 8 insert arrangement in smaller shell

PLUG - TYPE 6







#### INLINE RECEPTACLE - TYPE 1




#### **RECEPTACLE - TYPE 0**




#### **INSERT ARRANGEMENTS**





#### PANEL CUT-OUT DETAIL



## **AS Mini Series Connectors**

No. of Ways	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations	Wire Sealing (mm)		Temperature (°C)*	
vvays	JILC	5120	(//////////////////////////////////////	Disengagement)	Voltage (VAC)**	onentations	Min.	Max.	Min.	Max.
6	22	07	5	500	1500	7	0.76	1.37	55	+170
3	20	07	7.5	000	1800		1.02	2.11	-55	+1/0

#### **GENERAL SPECIFICATION**

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
22	604887	38941-22	600300-22	M81969/14-01	M22520/2-01	605000	M22520/2-09
20	6862-201-20278	38941-20	20 600300-20 M81969/14-10		1122320/2-01	M22520/2-10	M22520/2-10

#### **ORDERING INFORMATION**

	AS	*	07 – **	* * -HE ***
Range Ref:				
Style:0 = 2-Hole Receptacle1 = 1 Inline Receptacle6 = Free Plug				
Shell Size:				
Contact Arrangement:				
Insert Type: P = Pin S = Socket				
Shell Keyways:N = Red (Standard)A = YellowB = Blue				
HE: Harsh Environment				
Modification Code:				

#### ACCESSORIES PART NUMBERS

Pro	Cap	Nut Plate	Gasket			Boot Info	ormation
Receptacle	Plug					Straight	
AS907	AS807	ATM396-7	GV-7		Raychem	202K121	
	1		1	1	Hellermann	152-42-G	

90 Degree 222K121 1152-4-G

## **AS Series Connectors**



#### Large application choices

- Filter, hermetic & fiber optic options available Shell sizes 08 - 24
- Intermateable with existing LN29729 (Mil-C 38999 Series 1.5) and Pan 6433-2 style connectors
- High density arrangements

# Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to prevent moisture ingress

Contact	Shell	Max. Current	Durability (Cycles of	No. of Keyway	Wire Seal	ing (mm)	Temperat	:ure ( ° C)*
Size	Size	(Amps)	Engagement & Disengagement)	Orientations	Min.	Max.	Min.	Max.
22	08 to 24	5		c.	0.76	1.37		
20	see below	7.5	500	only 3 for shell size 8	1.02	2.11	-55	+175
16		20			1.65	2.77		

\*The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

Shell Size	Contact	Nu	Imber of Conta	cts	Dating **	Shell Size	Contact	Nu	Imber of Conta	cts	Dating *
211611 2126	Arrangement	Size 22 D	Size 20	Size 16	Rating **	211611 2126	Arrangement	Size 22 D	Size 20	Size 16	- Rating *
08	-98		3			18	-32		32		
08	-35	6			М	18	-35	66			М
10	-98		6			20	-16			16	I
10	-35	13			М	20	-39		37	2	1
10	-02			2		20	-41		41		1
10	-03			3		20	-35	79			М
12	-04			4		22	-21			21	1
12	-98		10			22	-55		55		1
12	-35	22			М	22	-35	100			М
14	-97		8	4		24	-29			29	I
14	-19		19			24	-61		61		1
14	-35	37			М	24	-35	128			М
16	-08			8		**•••	C		<i>с</i> п		
16	-26		26			-	efine Dielectric Withsta	-	-	Amor	
16	-35	55			М	1500 VOILS	rms, I = 1800 volts rms	s, current leakage	e iess liidh z mill	ianips.	

Please note: The contact/insert arrangements shown above are standard layouts. Other combinations of shell sizes and insert arrangements may be available. For details contact the TE Technical Support.

#### **CONTACTS & TOOLING PART NUMBERS**


Contact Size	Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
22	38943-22	38941-22	600300-22	M81969/14-01	M22520/2-01	M22520/2-07	M22520/2-09
20	38943-20	38941-20	600300-20	M81969/14-10	M22520/2-01	M22520/2-10	M22520/2-10
16	38943-16	38941-16	600300-16	M81969/14-03	M22520/1-01	M22520/1-04	M22520/1-04

Please note: PCB versions are ordered with AS2 prefixes and come with contacts.

#### GENERAL SPECIFICATION


## **AS Series Connectors**


#### AS CONTACT / INSERT ARRANGEMENTS



AEROSPACE, DEFENSE & MARINE / DEUTSCH AUTOSPORT INTERCONNECTION SOLUTIONS


#### PLUG - TYPE 6






Shell Size	A Max.	B Max.	C Max.
08	17.70		
10	20.80		
12	25.20		
14	28.40		
16	31.50	33.50	15.00
18	34.80		
20	38.20		
22	41.30		
24	44.60		


**INLINE RECEPTACLE - TYPE 1** 






Shell Size	A Max.	D +0 -0.13	G Max.
08	17.70	12.00	
10	20.80	15.00	
12	25.20	19.05	
14	28.40	22.22	
16	31.50	25.40	33.50
18	34.80	28.57	
20	38.20	31.75	
22	41.30	34.92	
24	44.60	38.10	


#### **RECEPTACLE - TYPE 0**






Shell Size	A REF	B ± 0.2	C + 0.1 - 0	D + 0 - 0.13	E + 0.15 - 0	F + 0 - 0.13	G Max.	L Max.	P Max.
08	16.50	21.35		12.00		16.05	16.05	27.20	3.00
10	19.50	25.90		15.00	17.21			32.00	
12	24.00	29.10		19.05				35.20	
14	27.00	32.50	7 20	22.22				38.40	
16	30.30	34.80	3.20	25.40				41.00	
18	33.70	38.20		28.57				44.70	
20	37.00	41.60		31.75				47.90	
22	40.00	44.95		34.92		15.29		51.10	
24	43.30	49.35	3.70	38.10				55.80	2.26

#### PANEL CUT-OUT DETAIL



Shell	А	В	C
Size	±0.10	±0.20	±0.20
08	14.50	21.40	
10	17.40	25.90	
12	21.90	29.10	
14	25.00	32.50	3.6
16	28.20	34.80	5.0
18	31.40	38.20	
20	34.60	41.60	
22	37.80	44.90	
24	41.00	49.30	4.10

#### PCB BOX MOUNTING RECEPTACLE - TYPE 2



\*Dimensions for 20 and 22 contacts shown are for standard parts. Other PCB contacts are available.

Shell Size	A REF	B ± 0.2	C + 0.1 - 0	D + 0 - 0.13	E + 0.15 - 0	F + 0 - 0.13	G Max.	H Max.	L Max.	P Max.
08	16.50	21.40		12.00	17.21	16.05	ις	11.10	27.20	
10	19.50	25.90		15.00				14.27	32.00	
12	24.00	29.10		19.05				17.44	35.20	
14	27.00	32.50		22.22				20.60	38.40	3.00
16	30.30	34.80	3.7	25.40			27.65	23.77	41.00	5.00
18	33.70	38.20		28.57				26.94	44.70	
20	37.00	41.60		31.75				30.11	47.90	
22	40.00	44.95		34.92		15.29		33.29	51.10	
24	43.30	49.35		38.10				36.46	55.80	2.26


ORDERING IN	FORMATION							
	Α	S	*	** —	**	* *	* <u> </u>	***
Range Ref:								
1 = Inline Recept	e Box Mount PCB Rec Rear Fixing)							
Shell Size:								
Contact Arrange	ement:							
Insert Type:P = PinS = Socket								
Shell Keyways: N = Red (Standa A = Yellow D = Green B = Blue C = Orange U = Violet								
(U = Univers	al for Test Harnesses)							
<b>Modification Co</b>	de:							

#### Please note: The size 8 shell is only available in keyways A, D and N.

#### ACCESSORIES PART NUMBERS

Shell Size	Nut Plate	Gasket		
08	ATM396 -8	GV-08		
10	ATM396 -10	GV-10		
12	ATM396 -12	GV-12		
14	ATM396 -14	GV-14		
16	ATM396 -16	GV-16		
18	ATM396 -18	GV-18		
20	ATM396 -20	GV-20		
22	ATM396 -22	GV-22		
24	ATM396 -24	GV-24		

#### **BOOT TERMINATION DETAIL**



Shell Size	A ± 0.10	B ± 0.05
08	11.20	10.00
10	14.22	12.95
12	17.39	16.15
14	20.55	19.15
16	23.72	23.35
18	26.89	25.35
20	30.06	28.50
22	33.24	31.70
24	36.41	34.85

## **AS Double Density (ASDD) Series Connectors**




#### Next generation connector – high density and high performance 8 shell sizes

- Allows for a saving of 2 shell sizes relative to standard autosport planforms
- Very lightweight
- Almost double the number of contacts compared with the standard autosport range equivalent shell size
- Integral screen


# Built to withstand harsh environments

- Conductive black zinc finish
- Interfacial wire sealing
- Bonded and sealed insert to help prevent moisture ingress

#### 9-WAY CONNECTOR DIMENSIONS - For other dimensions, refer to pages 26 to 29



#### **INLINE RECEPTACLE - TYPE 1**



## **AS Double Density (ASDD) Series Connectors**

#### **GENERAL SPECIFICATION**

Connector	Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement	ement Withstanding Orientations (r		Wire S (m	ealing m)		erature C)*
			× 172	& Disengagement)	Voltage (VAC)**		Min.	Max.	Min.	Max.
06-09	06	06			750	6		1.02	-55	+170
07-11		07				3	0.56			
08-11		08				3				
10-23	24	10	7	500						
12-41	24	12	5	500		6				
14-64		14								
16-93		16								
18-118		18								

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current. \*\* Current leakage less than 2 milliAmps at (VAC)

#### **CONTACTS & TOOLING PART NUMBERS**

Connector	Socket	Pin	PCB Socket	PCB Pin	Ins/Ext Tool	Socket Positioner	Pin Positioner
06-09	605704	605705-31	610008	610006-31		605840	605839
07-11	612532	605719-31	612715-ZZ	612714-31		M22520/2-09	605839
08-11					1		
10-23			DCR versions	s are ordered	605837		
12-41	605721	605719-31			000007	610287	610286
14-64	003721	10-11-11	with AS2 prefixes and come			010207	010200
16-93				with contacts.			
18-118							

#### **ORDERING INFORMATION**

	ASDD	)	* *:	* _ **	*	* _ ***
Range Ref.:						
Style: O = 2-Hole Flange Recept 1 = Inline Receptacle 2 = 2-Hole Flange Recept 4 = Flangeless 6 = Free Plug		Contacts				
<b>Shell Size:</b> 06, 07, 08, 10, 12, 14, 16, 18	3					
<b>Contact Arrangement:</b> 09, 11, 23, 41, 64, 93, 118						
Insert Type: P = Pin S = Socket						
Shell Keyways: N = Red (Standard) A = Yellow D = Green B = Blue C = Orange E = Grey U = Violet						
Modification Code:						

#### Please note: 08-11 is only available in keyways N, A and D, and 06-09 is available in all keyways. 07-11 is only available in keyways N, A and B.

#### **ACCESSORIES PART NUMBERS**

For information on boots and nut plates please refer to AS series on pages 24 to 29 or contact TE Technical Support for further information.

## **AS Micro HE Hermetic Series Connectors**




# Hermetic weld mount connector intermateable with AS Micro and ASL connectors

• Filtered Hermetic option also available

#### **High performance materials**

- Stainless Steel (316) for ease of mounting and corrosion performance
- Titanium versions for light weight applications also available
- Glass seal can withstand pressure differentials of 1000 psi without loss of electrical performance or fluid leakage



#### **GENERAL SPECIFICATION**

Contact Size	Shell Size	Max. Current	Durability (Cycles of Engagement	Dielectric Withstanding	tanding No. of Keyway		ithstanding No. of Keyway		mp C)*	Mate	erials	Fin	ish
JIZC J	SILC	(Amps)	& Disengagement)	Voltage (VAC)**		Min.	Max.	Shell	Contacts	Shell	Contacts		
23	06	3	500	1000	5	-65	+200	Stainless Steel (316)***	Nickel Iron	Electro- polished	Gold Plated		

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliamps at (VAC)

\*\*\* Titanium Shell also available

#### **ORDERING INFORMATION**

AS Micro HE Hermetic Receptacle:	AS	4H	06	—	05	Ρ	Ν	—	HE
AS Micro HE Plug:	ASL	606	05S	*	-	HE			
Shell Orientation:									
N = Red (Standard)									

## **AS Micro Hermetic (Jam-Nut) Series Connectors**




### Unique product for sensor and fuel cell use


- Jam-nut fixing
- Enlarged backshell for easier contact soldering
- Fuel immersible specification O-ring for enhanced fluid resistance

#### **High performance materials**


• Glass seal can withstand pressure differentials of 1000 psi without loss of electrical performance or fluid leakage

#### Fully intermateable with AS Micro HE connector and MicroLITE connector






# REAR FACE



#### PANEL CUT-OUT DETAIL



#### **GENERAL SPECIFICATION**

Contact	Shell	Max. Current		Dielectric Withstanding	No. of Keyway	Temperature ( ° C)*		
Size	Size	(Amps)	Engagement & Disengagement)	Engagement & Disengagement) Voltage (VAC)**	Orientations	Min.	Max.	
23	06	3	500	1000	1	-65	+200	

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

#### **ORDERING INFORMATION**

Part No. AS7H06 - 05 PN-HE All dimensions are in mm unless otherwise stated.

## **AS Hermetic Fuel Tank Series Connectors**




# Range of connectors designed for fuel cell walls


Selection of contact arrangements to accommodate pumps and sensors

#### **High performance materials**

- Fuel immersible specification O-ring for enhanced fluid resistance
- Integral potting cup, rear accessory thread and external boot termination feature
- Glass seal can withstand pressure differentials of 1000 psi without loss of electrical performance or fluid leakage



Shell Size	Part No.	ØA Max.	B Max.	C TYP.	ØD TYP.	E THREAD	ØF Min.	G Max.
10	AS07PT-10-**PN	15.04	28.40	25.95	20.50	M18x1.0	17.70	17.00
12	AS07PT-12-**PN	19.09	33.00	30.75	23.67	M21x1.0	22.70	21.10
14	AS07PT-14-**PN	22.26	36.30	33.85	26.84	M24x1.0	25.70	24.30




## **AS Hermetic Fuel Tank Series Connectors**

Contact Size	Max. Current	Sealing	Pressure	Electrical	Materials		Finish	
JIZC	(Amps)				Shell	Contacts	Shell	Contacts
22	5		1,000 psi typ.	IR 5000 Mohms @ 500 volt DC				
20	7.5	1 x 10 <sup>-8</sup> cc/sec @ 15 PSI			Stainless Steel (303)	Nickel Iron	Electro- polished	Gold Plated
16	20				51661 (505)	lion	polisiicu	

#### **GENERAL SPECIFICATION**

#### **ORDERING INFORMATION**



For aluminum version, please contact our TE Technical Support on +44 (0) 1424 852722 or email autosport@te.com

#### **ACCESSORIES PART NUMBERS**

**O-Ring Table** 

Part Number	inch	mm	Connector
429320-17	0.676	17.17	Size 6
429320-18	0.739	18.77	Size 10
429320-21	0.926	23.52	Size 12
429320-23	1.051	26.70	Size 14


## **AS MicroLITE HE Fuel Immersible Series Connectors**





#### For in-tank connection applications


- Unique DEUTSCH designed fuel resistant elastomer insert
- Hermetic option with enlarged backshell for easy contact soldering and integrated potting cup available
- Cable accommodation 22, 24, 26 and 28 AWG
- Fully intermateable with AS Micro HE and AS Micro<sup>LITE</sup> connectors

PLUG - TYPE 6









19.76 2.15

M12-1.0

3.30


12.95

6.95


M15 - 1.0

2.40


#### HERMETIC RECEPTACLE




All dimensions are in mm unless otherwise stated.



#### PANEL CUT-OUT DETAIL



#### PANEL CUT-OUT DETAIL



### **AS Micro**<sup>LITE</sup> **HE Fuel Immersible Series Connectors**

GENER/	AL SPEC	IFICATION							
Contact Size		Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations	Wire Sealing (mm)		Temperature (°C)*	
SILC	SILC	(//////////////////////////////////////	Disengagement)	Voltage (VAC)**	orientations	Min.	Max.	Min.	Max.
23	06	3	500	1000	6	0.60	1.37	-55	+170

### \* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

For other sizes and arrangements, please call our TE Technical Support on +44 (0) 1424 852722 or email autosport@te.com

### **CONTACTS & TOOLING PART NUMBERS**

Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
604935	604927-31	600300-22	M81969/14-01	M22520/2-01	604973	604972

#### **ORDERING INFORMATION**

	ASL	*	06 —	05	*	* -	HE -	- 952K
Range Ref:   ASL (or AS for Hermetic)								
<b>Style:</b> O = 2-Hole Flanged Receptacle 1 = Inline Receptacle 7H = Hermetic Receptacle 6 = Free Plug								
Shell Size:								
Contact Arrangement:								
Insert Type: (AS7H Pin Insert only) P = Pin S = Socket								
Shell Keyways: (AS7H N only) N A B								
Harsh Environment:								
Modification Code:								

#### ACCESSORIES PART NUMBERS

Pro	Cap	Nut Plate	Gasket			Boot Info	ormation
Receptacle	Plug					Straight	90 Degree
604029	604027	ATM396-6	GV-6		Raychem	202A111	222A111
	1			1	Hellermann	113-4-G	1108-4-G

### **AS Heavy Duty (ASHD) Series Connectors**







# Autosport design for high current motorsport applications

- Early break / late mate on data contacts for safety
- Cable accommodation from 16mm<sup>2</sup> - 70mm<sup>2</sup>
- Positive locking coupling mechanism


### **High performance materials**

- Environmentally sealed
- Thermal cycle tested
- Heavy duty rated
- Crimp type solid and gold plated copper contacts



For parts dimensions, refer to pages 26 to 29





SuperASHD Single 70mm<sup>2</sup> contact

AS 22-24320 ( 2 x AWG 4 , 3 x AWG 20 )

AS 24-34220 ( 3 x AWG 4 , 2 x AWG 20 )

AS 24-44420 (4 x AWG 4 , 4 x AWG 20 )

All dimensions are in mm unless otherwise stated.

(1x AWG 4)

### **AS Heavy Duty (ASHD) Series Connectors**

#### **CONTACTS & TOOLING PART NUMBERS**

Contact Size	Socket	Pin	Filler Plug	Ins/Ext Tool	Crimp Tool	Socket Positioner	Pin Positioner
20	38943-20	38941-20	600300-20	M81969/14-10	M22520/2-01	M22520/2-10	M22520/2-10

Please note: PCB versions are ordered with AS2 prefixes and come with contacts.

Wire Size	Split-Finger Socket	Hyperboloid Socket	Pin	Ext Tool	Crimp Tool	Jaws	Contact	Max. Current
16mm	611103-016	605739	605734	610176		605774	20	7.5
25mm	611103-025	605654	605660	610136- Tool	605773	605775	4	200
35mm	611103-035	605740	605735	1.001		605776	0 **	300

\*For use with part numbers ASHD022-24320SN-S04 and ASHD622-24320PN-004 \*\* Super ASHD only

Application Note: Due to potential high current, we would recommend that the product be suitably insulated with the appropriate materials.

#### **ORDERING INFORMATION**

	ASHD	*	*	—	*	*	*	-	***	- ****
Range Ref.:										
Style:         0         1         2 (ASHD Size 14 only)         6										
Shell Size: 14 = ASHD 22 = ASHD 2-Way and SuperASHE 24 = ASHD 3 and 4-Way										
Contact Arrangement: 1 = (ASHD) 24320 = (Size 22) 34220 = (Size 24) 3-Way 44420 = (Size 24) 4-Way 1 = (Super ASHD)	1									
Insert Type: P = Pin S = Socket										
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D =Green E = Grey										
Harsh Environment: Contact Size Code *16 *25 *35 *With pin contacts, C for size 14 sh contacts for size 14 shell only / O fo										

#### Modification Code:

### **AS Co-ax Series Connectors**



#### Autosport designed co-axial cable solution

- Ultra compact and light weight design (size 3 shell)
- Single co-axial contact and gold-plated crimp contacts
- Positive locking coupling mechanism with 2 keyway orientations and boot termination feature
- Designed for RG316 cable

#### **GENERAL SPECIFICATION**

Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &		No. of Keyway Orientations		Wire Sealing (mm)		Temperature (°C)*	
SILC	5120	(rimps)	Disengagement)		onentations	Min.	Max.	Min.	Max.	
-	03	-	500	1000	2	-	-	-55	+175	

\* The upper limit is the maximum internal hot-spot temperature resulting

from the combination of the ambient temperature and heating due to current.

\*\* Current leakage less than 2 milliAmps at (VAC)

	<b>CONTACTS &amp; TOOLING PART NUMBERS</b>								
Contacts P	art Numbers	Connector Type	Part Number						
Pin	Socket	Plug	ASCX603-1SN-050						
610908	610872	Inline - receptacle	ASCX103-1PN-050						

All dimensions are in mm unless otherwise stated.

### **AS Co-ax Series Connectors**



#### Portable antenna

• Ultra compact and light weight design (size 3 shell)

Flanged - receptacle

ASCX003-1PN-050

- Single co-axial contact
- Conductive black zinc finish
- Can be cut to length for optimised frequency (supplied with cut chart)
- Designed for RG316 and RG178 cables

#### GENERAL SPECIFICATION

Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	5	No. of Keyway Orientations	Wire S (m	- J	Tempe (°	
5120	SILC	(//////////////////////////////////////	Disengagement)	Voltage (VAC)**	orientations	Min.	Max.	Min.	Max.
-	03	-	-	-	2	-	-	-55	+175

\*The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current. \*\*Current leakage less than 2 milliamps at (VAC)

Contact Autosport Technical Support for more details of specific products to meet your sealed electrical connection requirements.

#### CONTACTS & TOOLING PART NUMBERS

Connector Type	Part Number
Plug (standard)	ASCX603-1SN-050
Inline – receptacle	ASCX103-1PN-050
Flanged – receptacle	ASCX003-1PN-050
Portable antenna plug	ASCX603-1SN-ANT20

All dimensions are in mm unless otherwise stated.

### **Special Contacts**



### **Thermocouple Contacts**

- Available in #22 for Autosport Range
- Available in #23 for Micro<sup>Lite</sup> Series connectors
- Engineered in Chromel and Alumel
- Designed exclusively for DEUTSCH connectors

#### THERMOCOUPLE #22 FOR AUTOSPORT RANGE

Description	Socket
Chromel pin	605346
Chromel socket	605347
Alumel pin	605348
Alumel socket	605349

Description	Socket
Chromel pin	605378-CR
Chromel socket	605380-CR
Alumel pin	605378-AL
Alumel socket	605380-AL

### CUSTOM MADE CONTACTS

In addition to Thermocouple contacts, we are able to engineer special solutions for different wire sizes on our regular contact range.



### **AS4 Flangeless Option**



### **AS4 FLANGELESS**

- Weight-saving alternative to AS1 receptacle
- Available on AS shells 8 24
- Added knurl for easier coupling
- Factory modified change to save team's time - Available on shell sizes 8 - 24
  - Sample part number: AS410-35PN
  - (AS4 shell type denotes flangeless option)

For more information and ordering details please call our TE Technical Support on +44 (0) 1424 857088 or email autosport@te.com

### **Clinchnut AS Series Connectors**



### **CLINCHNUT AS SERIES**

- A replacement for nutplates
- Available for PCB and flange mounted versions
- Time-saving option
- Available across the range of AS connectors

#### CLINCHNUT AS SERIES GENERAL SPECIFICATION


Contact Size	Shell Size	Max. Current (Amps)	Durability (Cycles of Engagement &	Dielectric Withstanding	No. of Keyway Orientations		ealing m)		erature C)*
SILC	SILC	(////////	Disengagement)	Voltage (VAC)**	onentations	Min.	Max.	Min.	Max.
-	-	-	500	-	-	-	-	-55	+175

\* The upper limit is the maximum internal hot-spot temperature resulting from the combination of the ambient temperature and heating due to current.


\*\* Current leakage less than 2 milliAmps at (VAC)

Mod Code	978M
----------	------


### Low Profile PCB Connector



### LOW PROFILE PCB CONNECTOR



2 HOLES Ø 3.60 ±0.20



PANEL CUT-OUT DETAILS

Contact	ØХ	ØY
Size	Max.	Max.
22	0.72	1.25
20	0.72	1.25
16	1.57	2.61

	Black Zinc Plating	Black Zinc Nickel Plating
Mod Code	118J	120Z

Shell Size	A REF	B ± 0.20	Ø C + 0.1 - 0.0	Ø D + 0.0 - 0.13	E + 0.15 - 0.0	F ± 0.10	ØG Max.	Ø H ± 0.10	L Max.
8	16.50	21.40		12.00			11.10	14.50	27.20
10	19.50	25.90		15.00		-	14.27	17.40	32.00
12	24.00	29.10		19.05			17.44	21.90	35.20
14	27.00	32.50		22.22		1000	20.60	25.00	38.40
16	30.30	34.80	3.2	25.40	21.24	20.05	23.77	28.20	41.00
18	33.70	38.20		28.57			26.94	31.40	44.70
20	37.00	41.60		31.75			30.11	34.60	47.90
22	40.00	44.95		34.90			33.29	37.75	51.10
24	43.30	49.35		38.10			36.46	40.90	55.80


All dimensions are in mm unless otherwise stated.


### AS3 Through Bulkhead





#### **AS3 THROUGH BULKHEAD**

- Military proven design
- Scoop-proof interface with shell to shell grounding
- Positive locking coupling mechanism
- Environmentally sealed to IP67
- Thermal cycle tested
- Fully intermateable with AS range of products
- Gold plated crimp contacts
- 4 hole mounting style









PART NUMBERS						
AS310-35PPN	Further options available,					
AS312-35PPN	please contact sales					
AS314-35PPN	offices for details.					

Contact TE for more details of specific products to meet your sealed electrical connection requirements.

All dimensions are in mm unless otherwise stated.

### **AS Fiber Optics Series Connectors**



### AS FIBER OPTIC SOLUTIONS

High quality fiber optic contacts are available in sizes 10-02, 10-03, for any AS Series connector planform having size 16 contact locations, e.g. 12-04, 14-97, 16-08, 20-16, 20-39, 22-21 and 24-29.

The precision ceramic ferruled fiber optic contacts are available for high quality (aerospace type specification) optic cables and silica glass fibers, enabling high speed, EMI / RFI immune data transmission.

The optical contacts are designed to meet MIL-T-29504/5.

### **Black Zinc Nickel Option**

Black Zinc Nickel: All AS Series connectors are available with black zinc nickel plating.

### **Termination Boots and Accessories**



## Gaskets

Designed specifically for TE's DEUTSCH autosport flanged connectors, these gaskets are available from size O2 through to 24 shells.

Constructed from fluoroelastomer polymer they assist in sealing the connectors to the mounting point and have been manufactured to withstand the temperatures, vibration and fluids found in the modern racing environment.

For part numbers please refer to page 49.



# Nut Plates

Nut plates are available for all AS two-hole flange mounted connector receptacles.

They are designed to simplify connector-to-bulkhead assembly, particularly in confined spaces, by eliminating the need to position loose nuts and washers. Nut plates are also anti-vibration and make assembly quicker and easier.

For part numbers please refer to page 49.

# Braid Termination Systems

Attaching braid to the back of an autosport connector can be done in a number of ways, depending on the environment the connector will be operating in. The standard practice of a metal strap on the braid to fasten it to the groove at the back of the shell is seen as a reliable solution with tooling and straps available from a number of sources.

TE Connectivity's engineers would suggest both the TE Connectivity screened backshell options which can be found on-line at www.te.com/usa-en/product-CX6566-000.html or the Glenair Band-IT system which uses the part numbers 600-057 (for the autosport connector sizes up to #16) or 600-083 (for the autosport connector sizes up over #16).

### How to Order

		2	6	46	6	Ð
			•			
	AS	*	* —	* *	* — HE — *	**
Range Ref:						
Style: 0 = 2-Hole Flange Ref 1 = Inline Receptacle 2 = 2-Hole Flange Ref 3 = Through Bulkhea 4 = Weld-Mounting / 6 = Free Plug 7 = Jam-Nut Mountin 8 = Protective Cap for 9 = Protective Cap for	ceptacle with PCB Conta d ' Flangeless ng or Plug	icts				
Shell Size:						
Contact Arrangeme	nt:					
Insert Type: P = Pin S = Socket						
Shell Keyways: N = Red (Standard) A = Yellow B = Blue C = Orange D = Green E = Grey						
Harsh Environment:						
Modification Code:						

#### All TE's DEUTSCH autosport part numbers work to the same principles. The part number is broken down into sections as follows:

- 'AS' indicates that it is an autosport connector all TE's DEUTSCH autosport connectors start like this. There may be another letter after the AS - this designates a particular series. For example ASL = Micro<sup>LITE</sup>, ASDD = Double Density.
- 2. The next major element is the connector style.
  - 0 = 2 hole flanged receptacle
  - 1 = Inline receptacle
  - 2 = 2 hole flanged receptacle with fixed PCB contacts
  - 3 = Through bulkhead
  - 4 = Weld mounting / flangeless
  - 6 = Free plug
  - 7 = Jam-nut mounting
  - 8 = Protective cap for plug
  - 9 = Protective cap for receptacle

Please note: not all of these options are available on

all products; the relevant product pages will give you this information.

- 3. Relates to the required shell size. This will range from O2 (small) to 24 (large).
- 4. Is the planform detail (number of contacts).
- Indicates the gender of a plug or receptacle. 'P' for pin or 'S' for socket.
- Designates a keyway. Only connectors of the same keyway can mate. The options are: N, A, B, C, D, E or U for universal or no keyway option. The 'U' option should only be selected for test harnesses and not for racing applications.
- 7. After all these elements there may be a 4-character code, which designates a special modification. For instance this can be a special contact length or a non-standard plating finish. For more information on modification codes please contact the TE Technical Support on +44 (0) 1424 857 088 or email autosport@te.com

For details of the ordering procedure for your area, please contact the relevant local distributor. A list of these can be found on the reverse of this brochure or on our website **www.te.com/autosport** 

### **Reference Guide**

### CONTACT TYPE

CONTACT SIZE	PART NO.	P/S	WIRE RANGE	COLOUR BAND	Max. CURRENT	CRIMP TOOL	POSITIONE	{	PLASTIC TOOLS INSERT/REMOVAL
Size 24 ASDD excluding 9-Way	605719-31	Р	24-30	Nono	None 3 Amps	M22520/2-01	610286	Р	605837
	605721	S	24-50	NOTE	5 Amps	19122520/2-01	610287	S	Orange/White
Size 24 ASDD 9 Way, ASX 5/6, ASU 5 Way	605705-31	Р	24-30	None	3 Amps	M22520/2-01	605839	Р	605837
	605704	S	24-50	NOTE	605840 s	S	Orange/White		
Size 24	605719-31	Р	24.70	Nana	7 Among	M22520/2_01	605839	Р	605837
ASDD 7-11	612532	S	24-30	None	3 Amps	M22520/2-01	M22520/2-09	S	Orange/ White
C' 27	604927-31	Р	22.20	N		N22520/2.01	604972	Р	M81969/14-01
Size 23	604935	s	22-28	None	3 Amps	M22520/2-01	604973	S	Green/White
c:	38941-22	Р	22.26	Orange, Blue, Black	<b>F A</b>	N22520/2.01	M22520/2-09	Р	M81969/14-01
Size 22	38943-22		22-26	Orange, Yellow, Grey	5 Amps	M22520/2-01	M22520/2-07	S	Green/White
ci 20	38941-20	Р	20.24	Orange, Blue, Orange	75 Augus	M22520/2_01	M22520/2-10	Р	M81969/14-10
Size 20	38943-20	S	20-24	Orange, Green, Brown	7.5 Amps	M22520/2-01	M22520/2-10	S	Red/Orange
Ciao 10	38941-16	Р	16 20	Orange, Blue, Yellow	20 America	N22520 /4 04	M22520/1-04	Р	M81969/14-03
Size 16	38943-16	S	16-20	Orange, Green, Red	20 Amps	M22520/1-01	M22520/1-04	S	Blue/White
AS Mini Size 22	38941-22	Р	22-26	Orange, Blue, Black	5 Amps	M22520/2-01	M22520/2-09	Р	M81969/14-01
	604887	S	22-20	None	2 ATTIPS	1922220/2-01	605000	S	Green/White
AS Mini Size 20	38941-20	Р	20-24	Orange, Blue, Orange	7.5 Amps	25 Amps M22520/2-01 P M81969/14-10	M81969/14-10		
AS FILLI SIZE ZU	6862-201-20278	S	20-24	None	1.7 AUDA	1122320/2-01	M22520/2-10	S	Red/Orange
Size 22	604946-31	Р					605463	Р	M81969/14-01
AS Composite/ASU 3-Way, ASX 3-Way	604984	S	22-28	None	5 Amps	M22520/2-01	605464	S	Green/White

#### **BOOT INFORMATION**

	STRAIG	HT BOOT	90 DEGREE BOOT		
SHELL SIZE	RAYCHEM	HELLERMAN	RAYCHEM	HELLERMAN	
ASX (Size 02)	203W301-25-G02	1037-4-G	223W601	1182-4-G	
ASU (Size 03)	204W221-25-G03	1037-4-G	224W221-25-G03	1182-4-G	
ASC	204W221	1030-4-G	224W221	1181-4-G	
ASL	204W221	1030-4-G	224W221	1181-4-G	
AS Mini	202K121	152-42-G	222K121	1152-4-G	
08	202K121	152-42-G	222K121	1152-4-G	
10	202K132	152-42-G	222K132	1152-4-G	
12	202K142	154-42-G	222K142	1154-4-G	
14	202K142	155-42-G	222K142	1155-4-G	
16	202K153	156-42-G	222K152	1156-4-G	
18	202K153	156-42-G	222K152	1156-4-G	
20	202K163	157-43-G	222K163	1157-4-G	
22	202K163	157-43-G	222K163	1157-4-G	
24	202K174	157-43-G	222K174	1157-4-G	

### **Reference Guide**

### ACCESSORIES

SHELL SIZE	NUTPLATE	GASKET	PLUG/RECEPTACLE	PROTECTIVE CAP
02 ( ASV 7/E )	ATM396-2 M2	GV-2	Plug	611546
02 ( ASX 3/5 )	AT M390-2 M2	UV-Ζ	Receptacle	611545
02 ( ASX 6 only )	ATM396-2 M2	GV-2	Plug	611637
02 ( ASA 0 011) )		UV Z	Receptacle	611636
03 (ASU 3/5)	ATM396-4 M2	GV-3	Plug	605687
UJ (AJU J)	AIRDJU 4 RZ	075	Receptacle	605684
06 (151)	ATM396-6 M2.5	GV-6	Plug	604027
06 (ASL)	AII'I390-0 I'IZ.3	0-40	Receptacle	604029
07 (Mini)	ATM70C 7 M7	CU 7	Plug	AS807
07 (Mini)	ATM396-7 M3	GV-7	Receptacle	AS907
08	ATM70C 0 M7	GV-8	Plug	AS808
Uδ	ATM396-8 M3	QA-AD	Receptacle	AS908
10	ATM706 10 M7	GV-10	Plug	AS810
	ATM396-10 M3		Receptacle	AS910
	ATM70C 12 M7	GV-12	Plug	AS812
12	ATM396-12 M3		Receptacle	AS912
14	ATM706 14 M7	CV 14	Plug	AS814
14	ATM396-14 M3	GV-14	Receptacle	AS914
16	ATM706 16 M7	CV 16	Plug	AS816
ID	ATM396-16 M3	GV-16	Receptacle	AS916
10	ATM70C 10 M7	CV/ 10	Plug	AS818
18	ATM396-18 M3	GV-18	Receptacle	AS918
20	ATM70C 20 M7	CU 20	Plug	AS820
20	ATM396-20 M3	GV-20	Receptacle	AS920
22		CL 12	Plug	AS822
22	ATM396-22 M3	GV-22	Receptacle	AS922
24		01.21	Plug	AS824
24	ATM396-24 M3	GV-24	Receptacle	AS924

### WIRE SIZES AND DIMENSIONS

AUTOSPORT SIZE		FINISHED WIRE DIMENSIONS			
CONTACT SIZE	WIRE SIZE (AWG)	CONDUCTOR		INSULATION	
		Min.	Max.	Min.	Max.
24	30,28,26,24	0.254mm 0.010in	0.511mm 0.02in	0.56mm 0.22in	1.02mm 0.040in
23	28,26,24,22	0.321mm .012in	0.790mm .031in	0.60mm .023in	1.37mm .054in
22	26,24,22	0.405mm .015in	0.790mm .031in	0.76mm .030in	1.37mm .054in
20	24,22,20	0.511mm .02in	0.970mm .038in	1.02mm .040in	2.11mm .083in
16	20,18,16	0.812mm .031in	1.530mm .60in	1.65mm .65in	2.77mm .109in

### **FILLER PLUGS**

CONTACT SIZE	PART NUMBER	
24	600300-24	
23	600300-22	
22	600300-22	
20	600300-20	
16	600300-16	

### **Notes**

### **Notes**

#### Empower Engineers to Solve Problems, Moving the World Forward.

AMP | AGASTAT | CII | DEUTSCH | DRI | HARTMAN | KILOVAC MICRODOT | NANONICS | POLAMCO | Raychem | SEACON

DEUTSCH Autosport Distribution Network	Country	Contact
GR Motorsport Electrics PTY Ltd	Asia Pacific	+61 398 004900
Davum TMC	France	+33 1483 68401
AVIO Race S.r.L	Italy	+39 0597700253 / info@avioraceusa.com
Global Active Technology	Japan	+81 42 945 1515
I S Motorsport Inc	North America	+1 317 244 6643
CosworthElectronics Inc		+1 317 259 8900
Servo Interconnect Ltd	United Kingdom	+44 (0) 1424 857 088

### **CONNECT WITH US**

We make it easy to connect with our experts and are ready to provide all the support you need. Visit **te.com/support** to chat with a Product Information Specialist.

### **QUALITY STARTS WITH THE RIGHT APPLICATION TOOLING**

Creating a quality crimp connection is essential to delivering high performance and reliability in extreme environments. From low to high volume wire processing, TE has you covered with a full range of application tooling and a global field service team.

- View all application tooling
- · Connect with our experts to find the right tool for your application

#### te.com/autosport

AMP, AGASTAT, CII, DEUTSCH, DRI, HARTMAN, KILOVAC, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, TE, TE Connectivity, and TE connectivity (logo) are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2022 TE Connectivity All Rights Reserved

1-1773721-8 12/22

#### DEUTSCH AUTOSPORT INTERCONNECTION SOLUTIONS

TE Connectivity Aerospace, Defense & Marine 2900 Fulling Mill Road Middletown, PA 17057

