


CGPT



GENERAL PURPOSE, FLAME-RETARDANT* POLYOLEFIN TUBING

A tough, flexible, general purpose polyolefin tubing with good resistance to common fluids and solvents and a high dielectric strength. Its unique blend of chemical, electrical, and physical properties makes it suitable for a wide range of applications, including electrical insulation, strain relief, cable bundling, colour-coding and identification of wires, cables, pipes, and electrical and electronic components, and mechanical protection.

TEMPERATURE RATING

- Continuous operating temperature from **-40°C up to +135°C**
- Minimum shrink temperature: **+80°C**
- Minimum full recovery temperature: **+120°C**

SPECIFICATIONS

- SPEC: **108-120044**
- UL: **E35586, 600 V, 125°C**
- CSA: **LR31929, 600 V, 125°C**
- Flammability Rating:
ASTM D2671, Procedure B (not clear)

MARKETS

- Automotive
- Aerospace
- Appliances
- Defense & Military
- Automation & Control
- Industrial & Commercial Transportation
- Rail
- Industrial Machinery


TYPICAL APPLICATION

- Suitable for a wide range of applications including electrical insulation, strain relief, cable bundling, color-coding, and mechanical protection.

PRODUCT BENEFITS

- 2:1 and 3:1 shrink ratio
- Very good chemical and solvent resistance
- Flexible
- Excellent physical and electrical performance
- RoHS compliant

DIMENSIONS (MILLIMETERS/INCHES)




CGPT 2:1 RATIO STANDARD SIZES

SIZE	INSIDE DIAMETER AS SUPPLIED (MIN) MM (INCH) D		INSIDE DIAMETER AFTER RECOVERY (MAX) MM (INCH) d		WALL THICKNESS AFTER RECOVERY (NOM) MM (INCH) W		WALL THICKNESS TOLERANCE AFTER RECOVERY	
	mm	in	mm	in	mm	in	mm	in
1.2/0.6	1.20	.047	0.60	.024	0.45	.018	0.12	.005
1.6/0.8	1.60	.063	0.80	.031	0.45	.018	0.12	.005
2.4/1.2	2.40	.094	1.20	.047	0.50	.020	0.12	.005
3.2/1.6	3.20	.126	1.60	.063	0.50	.020	0.12	.005
4.8/2.4	4.80	.189	2.40	.094	0.50	.020	0.12	.005
6.4/3.2	6.40	.252	3.20	.126	0.65	.026	0.15	.006
9.5/4.8	9.50	.374	4.80	.189	0.65	.026	0.15	.006
12.7/6.4	12.70	.500	6.40	.252	0.65	.026	0.15	.006
19/9.5	19.00	.748	9.50	.374	0.75	.030	0.15	.006
25.4/12.7	25.40	1.00	12.70	.500	0.90	.035	0.20	.008
32/16	32.00	1.220	16.00	.63	0.95	.037	0.20	.008
38/19	38.00	1.496	19.00	.748	1.00	.039	0.20	.008
51/26	51.00	2.008	26.00	1.02	1.15	.045	0.25	.010
76/38	76.00	2.992	38.00	1.496	1.25	.049	0.25	.010
102/51	102.00	4.016	51.00	2.008	1.40	.055	0.30	.011

CGPT 3:1 RATIO STANDARD SIZES

SIZE	INSIDE DIAMETER AS SUPPLIED (MIN) MM (INCH) D		INSIDE DIAMETER AFTER RECOVERY (MAX) MM (INCH) d		WALL THICKNESS AFTER RECOVERY (NOM) MM (INCH) W		WALL THICKNESS TOLERANCE AFTER RECOVERY	
	mm	in	mm	in	mm	in	mm	in
1.5/0.5	1.50	.059	0.50	.020	0.45	.018	0.12	.005
3/1	3.00	.118	1.00	.039	0.55	.022	0.12	.005
6/2	6.00	.236	2.00	.079	0.65	.026	0.12	.005
9/3	9.00	.354	3.00	.118	0.75	.030	0.15	.006
12/4	12.00	.472	4.00	.157	0.75	.030	0.15	.006
18/6	18.00	.709	6.00	.236	0.85	.033	0.15	.006
24/8	24.00	.945	8.00	.315	1.00	.039	0.20	.008
39/13	39.00	1.535	13.00	.512	1.15	.045	0.25	.010

ORDERING INFORMATION

Colour	<p>Standard: Black (-0), White (-9), Red (-2), Blue (-6), Yellow (-4), Brown (-1), Grey (-8), Clear (-X), Yellow/Green (-45) as indicated by an ***</p> <p>Nonstandard: Orange (-3), Green (-5), Violet (-7), in 2:1 sizes, 1.2/0.6 through 51/26 only.</p>
Size selection	<p>Always order the largest size that will shrink snugly over the component to be covered. Special order sizes are available upon request.</p>
Standard packaging****	<p>On spools.</p>
Ordering Description	<p>Specify product family, size/range, color and package</p> <p>CGPT-X/X-X-X</p>  <ul style="list-style-type: none"> → Package → Color → Size/Range → Product Family

****Available in the convenient RaySpool packaging/dispensing system for sizes:
2:1 - 2.4/1.2 up to 25.4/12.7, 3:1 - 3/1 up to 24/8

Are you looking to seal out moisture, offer enhanced strain relief, or provide rigorous mechanical protection?
Do you need a flame retardant product? Leverage TE Connectivity's (TE) comprehensive portfolio of heat shrink tubing products in a wide range of applications.

Learn more: [TE.com/heatshrinktubing](https://www.te-connectivity.com/heatshrinktubing)

© 2024 TE Connectivity. All Rights Reserved.

TE Connectivity, TE connectivity (logo), TE and Raychem are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

05/24