

# DESIGN OBJECTIVES

## 108-101528

The product described in this document has not been fully tested to ensure conformance to the requirements outlined herein. TE Connectivity makes no representation or warranty, express or implied, that the product will comply with these requirements, Further, TE Connectivity reserves the right these requirements based on the results of additional testing and evaluation. Contact TE Connectivity Engineering for further information. If necessary, This document will become the Product Specification at successful completion of testing.

### 1. Scope:



#### 1.1 Content


This specification covers the requirements for product performance, test methods and quality requirements for TE Connectivity pin header for PCB connections. The header is soldered onto the PCB.

Pin header assy: P/N: \*-2311622-\*, \*-2311621-\*, \*-2320179-\*, \*-2320178-\*, \*-2311610-\*, \*-2322613-\*

Suitable mating connector: 2301695-\*, 2322346-\*, 2322637-\*

| P/N         | Pin Position | Type | Applicable Plug | Terminal P/N                          |
|-------------|--------------|------|-----------------|---------------------------------------|
| *-2311621-* | 8            | 90°  | 2322346-*       | 928999-*/<br>/963715-*/<br>/1355717-* |
| *-2320179-* | 8            | 180° | 2322346-*       |                                       |
| *-2322610-* | 12           | 90°  | 2322637-*       |                                       |
| *-2322613-* | 12           | 180° | 2322637-*       |                                       |
| *-2311622-* | 16           | 90°  | 2301695-*       |                                       |
| *-2320178-* | 16           | 180° | 2301695-*       |                                       |
| *-2329531-* | 20           | 90°  | 2329592-*       |                                       |
| *-2330352-* | 20           | 180° | 2329592-*       |                                       |



|     |                                  |     |            |  |  |           |           |
|-----|----------------------------------|-----|------------|--|--|-----------|-----------|
|     |                                  |     |            | DR<br>K.WEI<br>18JAN2017                   |  TE Connectivity<br>Shanghai, China |           |           |
|     |                                  |     |            | CHK<br>W.WU<br>01DEC2017                   |  |           |           |
| A3  | Add Explanation for 3.5.4        | K.W | 04JAN 2019 | APP<br>I.YIN<br>05DEC2017                  | NO.<br>108-101528  | REV<br>A3 | LOC<br>ES |
| A2  | Change Drop Test Information     | K.W | 11MAY2018  | PAGE TITLE<br>1 of 11 TecMQS Series Header |  |           |           |
| A1  | Add Prefix of P/N<br>Add New P/N | K.W | 08APR2018  |  |  |           |           |
| A   | Release                          | K.W | 18JAN2017  |  |  |           |           |
| LTR | REVISION RECORD                  | DR  | DATE       |  |  |           |           |

## 1.2 Qualification

- A. When tests are performed on the subject product line, the procedures specified in USCAR-2 Revision 6 specifications shall be used. All inspections shall be performed using the applicable Inspection Plan and Product Drawing.

## 2. Applicable Documents:

The following documents form a part of this Specification to the extent specified herein. In the event of conflict between the requirements of this Specification and the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

### 2.1 Spec

- A. USCAR-2 Revision 6
- B. GMW3191

## 3. Requirements:

### 3.1 Design and Construction

Product shall be of the design, construction and physical dimensions specified in the Applicable product drawing.

### 3.2 Materials

- A. Contact
  - Material: 0.63 SQ Pin CuZn30
  - Finish: Tin over Nickel
- B. Housing
  - Material: PA10T or SPS
- C. Plug housing
  - Material: PBT-GF10

### 3.3 Ratings:

Operating temperature Range : -40°C to + 105°C

### 3.4 Performance and Test Descriptions

The product is designed to meet the electrical, mechanical and environmental performance requirements specified in fig.1 All tests are performed at test condition of the USCAR-2 Revision 6 specifications unless otherwise specified.

### 3.5 Requirements and Procedures Summary



TE Connectivity  
Shanghai, China

PAGE

2 of 11

NO.


108-101528

REV


A3

LOC

ES


| Para.   | Test items   | Requirements   | Procedures  |            |     |     |
|---|--|--|---|------------|-----|-----|
| <b>MECHANICAL TEST</b>  |  |  |   |            |     |     |
| 3.5.1   | Visual Examination   | The specimen under test must not show any evidence of deterioration, cracks, deformities, etc. that could affect function.   | <b>USCAR-2 Revision 6 Section 5.1.8</b><br>Visually, Dimensionally and Functionally inspected per applicable inspection plan.   |            |     |     |
| 3.5.2   | Terminal insertion force                                   | Insertion force $\leq 30\text{N}$  | <b>USCAR-2 Revision 6 Section 5.4.1</b><br>Insert the terminal straight into the connector at a uniform rate not to exceed 50mm per minute. Upon reaching the forward stop, continue applying force until failure point of the forward stop is reached.                 |            |     |     |
| 3.5.3   | Terminal retention force                                   | 1st lock $\geq 30\text{N}$<br>1st lock+2nd lock $\geq 60\text{N}$ (after Moisture Conditioning)<br>1st lock+2nd lock $\geq 50\text{N}$ (after Temp/Humidity and HTE)   | <b>USCAR-2 Revision 6 Section 5.4.1</b><br>Pull the terminal straight back from connector. Increase the pullout force at a uniform rate not to exceed 50mm/min, until pullout occurs.   |            |     |     |
| 3.5.4   | 2nd lock open and close force                              | Pre-set to lock 60N Max. (hinge length $< 15\text{mm}$ )<br>Pre-set to lock 60N Max. (hinge length $\geq 15\text{mm}$ )<br>Lock to pre-set 10~60N (hinge length $< 15\text{mm}$ )<br>Lock to pre-set 10~75N (hinge length $\geq 15\text{mm}$ ) | <b>USCAR-2 Revision 6 Section 5.4.5</b><br>Engage each component to be tested, with its retaining mechanism in place, at a rate not exceed 50mm/min<br>With the component fully installed and properly fixtured, disengage the component at a rate not exceed 50mm/min. |            |     |     |
| 3.5.5   | Connector-to-Connector mating Force                        | Mating force $\leq 75\text{N}$<br>(For 2329531-* and 2330352-*)<br>Mating force $\leq 90\text{N}$ )  | <b>USCAR-2 Revision 6 Section 5.4.2</b><br>Connectors to be mated together by applying a measured force at speed 50 mm/min to slide fully seated and locked at the first time.  |            |     |     |
| 3.5.6   | Connector-to-Connector Unmating Force with Lock Disengaged | Unmating force $\leq 75\text{N}$<br>(For 2329531-* and 2330352-*)<br>Unmating force $\leq 90\text{N}$ )  | <b>USCAR-2 Revision 6 Section 5.4.2</b><br>Connectors with primary lock to be unmated by applying a measured force at speed 50 mm/min to slide out at the first time.   |            |     |     |
| 3.5.7   | Connector-to-Connector Unmating Force with Lock Engaged    | Unmating force $\geq 110\text{N}$  | <b>USCAR-2 Revision 6 Section 5.4.2</b><br>Connectors with primary lock fully engaged by applying a measured force at speed 50 mm/min to slide out at the first time.   |            |     |     |
|  |  | TE Connectivity<br>Shanghai, China   | PAGE  | NO.        | REV | LOC |
|   |  |  | 3 of 11   | 108-101528 | A3  | ES  |

|                        |                                    |   |  |
|------------------------|------------------------------------|---|--|
| 3.5.8                  | Polarization Feature Effectiveness | The connection system must withstand a specified mis-mating force without damage to the connector and no electrical contact shall be made between the male/female terminals.  | <b>USCAR-2 Revision 6 Section 5.4.4</b><br>Attempt to engage the connector halves at a rate not to exceed 50mm/min. until a force of 3X the maximum value of a properly mated connector is applied. Hold force for 3 seconds.  |
| 3.5.9                  | Pin Push-Out Force                 | The minimum force required is 15N.  | <b>USCAR-2 Revision 6 Section 5.7.1</b><br>Moisture condition samples at 95-98% relative humidity at 40C° for 6hours<br>Apply an axial load to the front and back of the<br>Contact<br>Operation speed: 50mm/min   |
| 3.5.10                 | Connector Cycling                  | Re-mate connectors in preparation for future test sequences or follow directions in the respective procedure to follow  | <b>USCAR-2 Revision 6 Section 5.1.7</b><br>Completely mate and un-mate each connector pair 10 times  |
| 3.5.11                 | Connector Integration drop test    | Prepare three assemblies, and every assembly is assembled by four commodity headers, drop every assemblies at a time once onto a horizontal concrete surface from a height of at least 1 meter. Only judge the “Lego” structure | <b>USCAR-2 Revision 6 Section 5.4.8</b><br>Fall surface: concrete<br>Drop height: 1.0 m  |
| 3.5.12                 | Lego structure bending resistance  | The bending force to destroy “Lego” is Min50N   | Two single headers integration(A+B), fix A, Measure the force required to destroy the “Lego” (the point of application of force on the centre of B)<br>Then fix B, measure A (Integration B+A) (5 integrations for A+B, 5 integrations for B+A)Measure sketch map shown as Fig 3 |
| 3.5.13                 | Lego structure mating force        | The mating force of lego is max 75N   | Fix A single header, measure the force to mating B lego in A until the lock engage<br>Then fix B measure A<br>The measure sketch map shown as Fig 4  |
| <b>ELECTRICAL TEST</b> |                                    |   |  |
| 3.5.14                 | Dry Circuit Resistance             | Dry Circuit Resistance $\leq 20\text{m}\Omega$  | <b>USCAR-2 Revision 6 Section 5.3.1</b><br>Measure and record the resistance across 150mm of conductor to be use for this test.  |
| 3.5.15                 | Voltage Drop                       | Voltage Drop $\leq 50\text{mV}$   | <b>USCAR-2 Revision 6 Section 5.3.2</b><br>Measure and record the millivolt drop across 150mm of the conductor size and insulation type to be used during the test.  |
| 3.5.16                 | Insulation Resistance              | Insulation resistance $\geq 100\text{M}\Omega$  | <b>USCAR-2 Revision 6 Section 5.5.1</b><br>Test condition: U=500V (DC)   |

|  |         |            |     |     |
|--|---------|------------|-----|-----|
|  TE Connectivity<br>Shanghai, China | PAGE    | NO.        | REV | LOC |
|  | 4 of 11 | 108-101528 | A3  | ES  |

|                         |                               |   |  |
|-------------------------|-------------------------------|---|--|
| 3.5.17                  | Dielectric strength           | No creeping discharge or flashover shall occur  | <b>GMW3191 Section 4.3.6</b><br>1000V at 50Hz or 60 Hz or 1600V DC for at least 1min   |
| 3.5.18                  | Current Capability Test       | Current 5A, Increase temperature 55°C max<br>wire range 0.75mm <sup>2</sup> and measure 4 pins(the positions of pins see the Fig.5, Measured by applying all 4 signal pins with series circuit, Derating Curve of 12way header is shown as Fig.9) | <b>USCAR-2 Revision 6 Section 5.3.3</b><br>1) Measure and record the voltage drop, using the expected Maximum Current Capability of TUT.<br>2) Test the sample terminal pairs at 23°C ± 5 °C. Slowly increase the power supply output until it is providing no greater than 50% of the expected Maximum Current Capability of the TUT.<br>3) Wait at least 15 minutes, record the ambient temperature, the temperature of each terminal pair interface, the millivolt drop across each terminal pair.<br>4) Increase the current by no more than 10% of the expected Maximum Current Capability and repeat 3). |
| <b>ENVIRONMENT TEST</b> |                               |   |  |
| 3.5.19                  | Vibration/Mechanical Shock    | There must be no instance in which the resistance of any terminal air exceeds 7.0 Ω for more than 1 microsecond for circuit continuity monitoring.<br>3.5.14 Dry Circuit Resistance<br>3.5.15 Voltage Drop  | <b>USCAR-2 Revision 6 Section 5.4.6</b><br>Vibration class V1(see the Fig.6)   |
| 3.5.20                  | Temperature/Humidity Cycling  | 3.5.14 Dry Circuit Resistance<br>3.5.15 Voltage Drop<br>3.5.16 Insulation resistance  | <b>USCAR-2 Revision 6 Section 5.6.2</b><br>Temperature: -40°C~105°C<br>Cycles: 40 cycles(see the Fig.7)  |
| 3.5.21                  | High Temperature Exposure     | 3.5.14 Dry Circuit Resistance<br>3.5.15 Voltage Drop  | <b>USCAR-2 Revision 6 Section 5.6.3</b><br>Place the samples in the chamber, set to 105 °C, and leave the samples in the chamber for 1008 hours.   |
| 3.5.22                  | Thermal Shock                 | There must be no instance in which the resistance of any terminal air exceeds 7.0 Ω for more than 1 microsecond for circuit continuity monitoring.<br>3.5.14 Dry Circuit Resistance<br>3.5.15 Voltage Drop  | <b>USCAR-2 Revision 6 Section 5.6.1</b><br>-40°C/30min, +105°C/30min.<br>Make this one cycle.<br>Repeat 100 cycles.  |
| 3.5.23                  | Reflow soldering pretreatment | After reflow soldering, the plastic housing should not blister, melt or occur any discoloration.<br>Meet all test items follow sequences  | Reflow soldering simulation<br>(the reflow temperature curve shown as Fig.8 max temperature:260°C)   |

Fig .1


|  |         |            |     |     |
|--|---------|------------|-----|-----|
|  TE Connectivity<br>Shanghai, China | PAGE    | NO.        | REV | LOC |
|  | 5 of 11 | 108-101528 | A3  | ES  |

### 3.6 Product Qualification Test and Sequence

| Test or Examination |  | Test Group |       |       |       |       |       |       |        |       |       |
|---------------------|--|------------|-------|-------|-------|-------|-------|-------|--------|-------|-------|
|                     |  | 1          | 2     | 3     | 4     | 5     | 6     | 7     | 8      | 9     | 10    |
| 3.5.1               | Visual Examination   | 1,3,6      | 1,3,6 | 1,3,6 | 1,3,5 | 1,3,5 | 1,3,9 | 1,3,9 | 1,3,11 | 1,3,9 | 1,3,5 |
| 3.5.2               | Terminal insertion force                                   |            |       |       |       |       |       |       |        |       |       |
| 3.5.3               | Terminal retention force                                   |            |       |       |       |       |       |       |        |       |       |
| 3.5.4               | 2 <sup>nd</sup> lock open and close force                  |            |       |       |       |       |       |       |        |       |       |
| 3.5.5               | Connector-to-Connector mating Force                        |            | 4     | 4     |       |       |       |       |        |       |       |
| 3.5.6               | Connector-to-Connector Unmating Force with Lock Disengaged |            | 5     |       |       |       |       |       |        |       |       |
| 3.5.7               | Connector-to-Connector Unmating Force with Lock Engaged    |            |       | 5     |       |       |       |       |        |       |       |
| 3.5.8               | Polarization Feature Effectiveness                         |            |       |       | 4     |       |       |       |        |       |       |
| 3.5.9               | Pin Push-Out Force   |            |       |       |       | 4     |       |       |        |       |       |
| 3.5.10              | Connector Cycling  | 4          |       |       |       |       | 4     | 4     | 4      | 4     |       |
| 3.5.11              | Connector integration drop test                            |            |       |       |       |       |       |       |        |       | 4     |
| 3.5.12              | Lego structure bending resistance                          |            |       |       |       |       |       |       |        |       |       |
| 3.5.13              | Lego structure mating force                                |            |       |       |       |       |       |       |        |       |       |
| 3.5.14              | Dry Circuit Resistance                                     |            |       |       |       |       | 5,7   | 5,7   | 5,7    | 5,7   |       |
| 3.5.15              | Voltage Drop   |            |       |       |       |       | 8     | 8     | 8      | 8     |       |
| 3.5.16              | Insulation Resistance                                      |            |       |       |       |       |       |       | 9      |       |       |
| 3.5.17              | Dielectric strength  |            |       |       |       |       |       |       | 10     |       |       |
| 3.5.18              | Current Capability test                                    | 5          |       |       |       |       |       |       |        |       |       |
| 3.5.19              | Vibration/Mechanical Shock                                 |            |       |       |       |       | 6     |       |        |       |       |
| 3.5.20              | Temperature/Humidity Cycling                               |            |       |       |       |       |       |       | 6      |       |       |
| 3.5.21              | High Temperature Exposure                                  |            |       |       |       |       |       |       |        | 6     |       |
| 3.5.22              | Thermal Shock  |            |       |       |       |       |       | 6     |        |       |       |
| 3.5.23              | Reflow soldering pretreatment                              | 2          | 2     | 2     | 2     | 2     | 2     | 2     | 2      | 2     | 2     |
| Sample Size         |  | 5          | 5     | 5     | 5     | 4     | 8     | 8     | 8      | 8     | 9     |

| Test or Examination |  | Test Group |     |    |  |  |  |  |  |  |  |  |  |  |
|---------------------|--|------------|-----|----|--|--|--|--|--|--|--|--|--|--|
|                     |  | 11         | 12  | 13 |  |  |  |  |  |  |  |  |  |  |
| 3.5.1               | Visual Examination   | 1,4        | 1,3 | 1  |  |  |  |  |  |  |  |  |  |  |
| 3.5.2               | Terminal insertion force                                   | 2          |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.3               | Terminal retention force                                   | 3          |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.4               | 2 <sup>nd</sup> lock open and close force                  |            | 2   |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.5               | Connector-to-Connector mating Force                        |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.6               | Connector-to-Connector Unmating Force with Lock Disengaged |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.7               | Connector-to-Connector Unmating Force with Lock Engaged    |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.8               | Polarization Feature Effectiveness                         |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.9               | Pin Push-Out Force   |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.10              | Connector Cycling  |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.11              | Connector integration drop test                            |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.12              | Lego structure bending resistance                          |            |     | 3  |  |  |  |  |  |  |  |  |  |  |
| 3.5.13              | Lego structure mating force                                |            |     | 2  |  |  |  |  |  |  |  |  |  |  |
| 3.5.14              | Dry Circuit Resistance                                     |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.15              | Voltage Drop   |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.16              | Insulation Resistance                                      |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.17              | Dielectric strength  |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.18              | Current Capability test                                    |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.19              | Vibration/Mechanical Shock                                 |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.20              | Temperature/Humidity Cycling                               |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.21              | High Temperature Exposure                                  |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.22              | Thermal Shock  |            |     |    |  |  |  |  |  |  |  |  |  |  |
| 3.5.23              | Reflow soldering pretreatment                              |            |     |    |  |  |  |  |  |  |  |  |  |  |
| Sample Size         |  | 10         | 10  | 5  |  |  |  |  |  |  |  |  |  |  |

Fig. 2

|  |         |            |     |     |
|--|---------|------------|-----|-----|
|  TE Connectivity<br>Shanghai, China | PAGE    | NO.        | REV | LOC |
|  | 7 of 11 | 108-101528 | A3  | ES  |

## 4. QUALIFICATION TEST

### 4.1 Sample selection

Samples shall be prepared in accordance with applicable specification.

### 4.2 Test sequence

Qualification test shall be conducted as sequence specified in Fig. 2

### 4.3 Requalification test


If changes significantly affecting form, fit or function are made to product or manufacturing process, product assurance shall co-ordinate requalification testing, consisting of all or part of original testing sequence as determined by developments, product, quality and reliability engineering.

### 4.4 Acceptance

Acceptance is based on verification that product meets requirements of Fig 1. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify product. When product failure occurs, Corrective action shall be taken and sample resubmitted for qualification. Testing to confirm corrective action is required before resubmitted.

### 4.5 Quality conformance inspection

Applicable TE quality inspection plan will specify sampling acceptable quality level to be used. Dimensional and functional requirements shall be accordance with applicable product drawings and this specification.

|   |                                    |         |            |     |     |
|---|------------------------------------|---------|------------|-----|-----|
|  | TE Connectivity<br>Shanghai, China | PAGE    | NO.        | REV | LOC |
|   |                                    | 8 of 11 | 108-101528 | A3  | ES  |



## 5. APPENDIX

### 5.1 Lego bending resistance measure sketch map




Fig 3. Lego bending resistance measure sketch map

### 5.2 Lego mating sketch map





Fig 4. Lego mating sketch map

|   |                                    |         |            |     |     |
|---|------------------------------------|---------|------------|-----|-----|
|  | TE Connectivity<br>Shanghai, China | PAGE    | NO.        | REV | LOC |
|   |                                    | 9 of 11 | 108-101528 | A3  | ES  |

### 5.3 The positions of pins for Current Capability Test




Fig 5. The positions of pins for current capability test

### 5.4 Vibration class graphs






Fig 6. The vibration class V1 graphs

### 5.5 Temperature/humidity cycling schedule



Key: 1 (-40)°C    2 (80 – 90)°C    3 Test temperature per Table 5.1.4.1 (Class 3 shown for illustration only)  
 4 Relative Humidity, uncontrolled. Do not vent chamber at hour 5.    5 (80 – 100)% Relative Humidity

Fig 7. Temperature/humidity cycling schedule

|  |          |            |     |     |
|--|----------|------------|-----|-----|
|  TE Connectivity<br>Shanghai, China | PAGE     | NO.        | REV | LOC |
|  | 10 of 11 | 108-101528 | A3  | ES  |

## 5.6 Reflow temperature




Fig 8. Reflow Temperature curve

## 5.7 Derating Curve of 12 Way Header (all pins together)





Fig 9. 12 Way Header Derating Curve

|   |                                    |          |            |     |     |
|---|------------------------------------|----------|------------|-----|-----|
|  | TE Connectivity<br>Shanghai, China | PAGE     | NO.        | REV | LOC |
|   |                                    | 11 of 11 | 108-101528 | A3  | ES  |