

## 2.29 CLUSTER REC AMPLIVAR

### 1. INTRODUCTION

#### 1.1. Purpose

Testing was performed on the TE Connectivity (TE) 2.29 CLUSTER REC AMPLIVAR TYPE 1742981-1 and 1742964-1 to determine its conformance to the requirements (108-2008 Rev H) of LLCR, Crimp Tensile strength and Temperature rising.

#### 1.2. Scope

This report covers the electrical and mechanical performance of 2.29 CLUSTER REC AMPLIVAR TYPE 1742981-1 and 1742964-1. Testing was performed at TE Connectivity Shanghai Electrical Test Laboratory between Aug. 30<sup>th</sup>, 2019 and Sep. 20<sup>th</sup>, 2019. The test file number for this testing is TP-19-02414.

#### 1.3. Conclusion

Based on the test results, all part numbers listed in paragraph 1.5 meet the performance requirements list in test sequence. The product could terminate the 3 magnet wires without stripping the coating.

#### 1.4. Product Description

Part Number	Part Description	Wire Dia	Crimp Height
1742981-1	2.29 DIA CLUST PIN AMPLVR REC 400-1600	0.32DIA x 3	1.07 ±0.05
		0.49DIA x 3	1.27 ±0.05
1742964-1	2.29 DIA CLUSTER PIN AMPLV REC 1600-4800	0.51DIA x 3	1.47 ±0.05
		0.91DIA x 3	1.76 ±0.05

#### 1.5. Test Specimens

The test specimens were representative of normal production lots, and the following part numbers were used for testing (see Figure 1).

Test Group	Quantity	Part Number	Description
1	12	1742981-1	Receptacle 1742981-1 crimp with 3xØ0.32mm Cu magnet wire
2	12	1742981-1	Receptacle 1742981-1 crimp with 3xØ0.32mm Al magnet wire
3	12	1742981-1	Receptacle 1742981-1 crimp with 3xØ0.49mm Cu magnet wire
4	12	1742981-1	Receptacle 1742981-1 crimp with 3xØ0.49mm Al magnet wire
5	12	1742964-1	Receptacle 1742964-1 crimp with 3xØ0.51mm Cu magnet wire

6	12	1742964-1	Receptacle 1742964-1 crimp with 3xØ0.51mm Al magnet wire
7	12	1742964-1	Receptacle 1742964-1 crimp with 3xØ0.91mm Cu magnet wire
8	12	1742964-1	Receptacle 1742964-1 crimp with 3xØ0.91mm Al magnet wire

**Figure 1**

1.6. Qualification Test Sequence

Test or Examination	Test Groups (a)	
	1	2
	Test Sequence (b)	
Examination of Product	1	1
Low Level Contact Resistance	2	
Temperature rise vs current	3	
Crimp Tensile Strength		2
Final examination of product	4	3



**NOTE**

- (a) See Paragraph 1.5.
- (b) Numbers indicate sequence which tests were performed.

**Figure 2**

1.7. Environmental Conditions

Unless otherwise stated, the following environmental conditions prevailed during testing:

Temperature: 15°C to 35°C  
 Relative Humidity: 20% to 80%

**2. SUMMARY OF TESTING**

2.1. Initial Examination of Product

Specimens were visually examined according to EIA 364-18B and no evidence of physical damage detrimental to the operation of the part was observed.

2.2 Low Level Contact Resistance

All LLCR measurements taken at 100 milliamperes maximum and 20 millivolts maximum open circuit voltage were less than 3.0milliohms initial and less than of 6milliohms (Final).

### 2.3 Temperature Rise vs. Current




Figure 3: 1742981-1 Temperature Rise




Figure 4: 1742964-1 Temperature Rise

## 2.4 Crimp Tensile Strength

Test data shown as below: (Unit: N)

Test Set	1742981-1 Crimp Tensile Strength			
Wires	3xØ 0.32mm Cu	3xØ 0.32mm Al	3xØ 0.49mm Cu	3xØ 0.51mm Al
Max.	23.7	9.1	48.0	20.5
Min.	20.8	7.8	46.1	20.0
Mean	22.5	8.4	47.4	20.2

Test Set	1742964-1 Crimp Tensile Strength			
Wires	3xØ 0.49mm Cu	3xØ 0.51mm Al	3xØ 0.91mm Cu	3xØ 0.91mm Al
Max.	48.3	22.2	169.2	64.2
Min.	47.6	18.7	167.4	59.9
Mean	47.9	20.4	168.3	63.2

## 3. TEST METHODS

### 3.1 Examination of Product

Specimens were visually examined as stated in TE Connectivity Product Specification 108-5205, Rev. E, paragraph 3.4 and in accordance with test procedure EIA-364-18B.

### 3.2 Low Level Contact Resistance

Specimens were subjected to a low level contact resistance test as stated in TE Connectivity Product Specification 108-5574, Rev B, Paragraph 3.5 and in accordance with test procedure EIA-364-23C. Using a four terminal measuring technique, low level contact resistance was measured using a test current maintained at a 100 milliamperes maximum with a 20 millivolt maximum open circuit voltage. The measurement points were at the locations indicated in Figure 1.




Fig 1 Low Level Connect Resistance

### 3.3 Temperature Rise vs. Current

Temperature rise curves were produced by measuring individual contact crimp temperatures at a minimum of 5 different current levels. These measurements were plotted to produce a temperature rise vs current curve. Type "T" (30 AWG) thermocouples were attached to the crimps of the individual contacts to measure their temperatures. The ambient temperature was then subtracted from this measured temperature to find the temperature rise. When the temperature rise of 3 consecutive readings taken at 5 minute intervals did not differ by more than 1°C, the temperature measurement was recorded. Testing was conducted in accordance with EIA-364-70B, Method 2.

### 3.4 Crimp Tensile

The specimen was held in a slotted plate that was mounted to a free floating x-y rotational table to allow for axial alignment. The x-y rotational table was attached to the base of the tensile/compression machine. The wire was clamped in a jaw that was attached to the moveable crosshead of the tensile/compression machine. Force was then applied in an upward direction at a rate of 1.0 inch per minute until failure occurred. Wire tensile strength for Test Set 5 was determined by pulling one wire specimen. The wire was fed around the barrel and clamped at the end. Force was then applied in an upward direction at a rate of 1.0 inch per minute until failure. The wire tensile strength values for the wires in Test Sets 6 through 8 were calculated using the maximum wire tensile strength from breakage that occurred outside the crimp area during testing. All minimum crimp tensile requirements for all test sets were calculated from 70% of the wire tensile values for each wire size. Testing was conducted in accordance with EIA-364-8.