



RK 6743 Revision 4

TRSA Sleeving

SCOPE

This Quality Assurance Specification establishes the quality standard for a heat-shrinkable, flexible polyolefin sleeving.

Approved Signatories*

* This document is electronically reviewed and approved - therefore no signatures will appear.

1. REVISION HISTORY

Revision Number	Change Request	Date	Incorporated By
2	CR98-DM-0199	24 September 1998	L. Abrams
3	Via DMTEC	31 March 2014	C. Diss
4	Via DMTEC	31 March 2014	C. Diss

2. REQUIREMENTS**2.1 Composition, Appearance and Colour**

The sleeving shall be homogeneous and free from pinholes, bubbles, cracks and inclusions. The colour shall be as specified in the contract or order.

2.2 Dimensions

Size	Inside Diameter as supplied (min) mm	Inside Diameter after recovery (max) mm	Wall Thickness after recovery mm
1.5/0.5	1.5	0.5	0.45 ± 0.10
3/1	3.0	1.0	0.55 ± 0.10
6/2	6.0	2.0	0.65 ± 0.10
9/3	9.0	3.0	0.75 ± 0.12
12/4	12.0	4.0	0.75 ± 0.12

Sleeving of special expanded or recovered dimensions may be supplied as specified in the contract or order.

2.3 Test Requirements

The test requirements shall be as specified in Table 1.

3. TEST METHODS

3.1 Unless otherwise specified, tests shall be carried out on specimens of sleeving recovered by conditioning in a fan assisted air circulating oven at $200 \pm 5^\circ\text{C}$ for 4 ± 1 minutes and allowed to cool in air to ambient temperature. No pre-conditioning period is required prior to testing. Unless otherwise specified, all tests shall be made under standard ambient conditions according to IEC Publication 212. In cases of dispute the tests shall be carried out at a temperature of $23 \pm 2^\circ\text{C}$ and at $50 \pm 5\%$ relative humidity.

3.2 Dimensions and Longitudinal Change

The test method shall be as specified in ASTM D2671.

The length and inside diameter of three 150mm long specimens of expanded sleeving shall be measured. The specimens shall be recovered in a fan assisted air circulating oven and the length and inside diameter of each shall be measured. The longitudinal change shall be expressed as a percentage of the original length. The minimum and maximum recovered wall thickness shall be determined.

TEST METHODS (Cont'd)**3.3 Tensile Strength and Ultimate Elongation**

The test method shall be as specified in ISO 37.
Five tubular specimens 125mm long shall be tested. Initial jaw separation shall be 50 mm and rate of jaw separation shall be 100 ± 10 mm per minute.
The test shall be carried out at a temperature of $23 \pm 2^\circ\text{C}$

3.4 Secant Modulus

The test method shall be as specified in Method A of ASTM D882.
Five tubular specimens 150mm long shall be tested. Initial jaw separation shall be 100mm and rate of jaw separation 10 ± 1 mm per minute.
The test shall be carried out at a temperature of $23 \pm 2^\circ\text{C}$.

3.5 Specific Gravity

The test method shall be as specified in Method A of ISO 1183.

3.6 Heat Shock

The test method shall be as specified in ASTM D2671.
The specimens shall be conditioned in a fan assisted air circulating oven as specified in Table 1.

3.7 Heat Ageing

The test method shall be as specified in ISO 188.
Five tensile test specimens prepared as in Clause 3.3 shall be conditioned in a fan assisted air circulating oven as specified in Table 1. After conditioning the specimens shall be removed from the oven, allowed to cool naturally to room temperature and tested for Ultimate Elongation according to clause 3.3.

3.8 Low Temperature Flexibility

The test method shall be as specified in Procedure C of ASTM D2671.
Mandrel diameter shall be $15 \times$ specimen thickness $\pm 10\%$. For tubular specimens the thickness is the outside diameter.
The specimens and mandrel shall be conditioned as specified in Table 1.

3.9 Flammability

The test method shall be as specified in ASTM D876.

3.10 Electric Strength

The test method shall be as specified in IEC 60243-1 (Short time test).

TEST METHODS (Cont'd)**3.11 Copper Contact Corrosion**

The test method shall be as specified in ASTM D2671.

The specimens shall be conditioned in a fan assisted air circulating oven as specified in Table 1, allowed to cool naturally to room temperature and tested for Ultimate Elongation according to Clause 3.3.

3.12 Copper Mirror Corrosion

The test method shall be as specified in ASTM D2671.

The specimens shall be conditioned as specified in Table 1.

3.13 Water Absorption

The test method shall be as specified in Method 1 of ISO 62.

Three tubular specimens 50mm long shall be cut from the sleeving.

3.14 Fluid Resistance

The test method shall be as specified in ISO 1817.

Five tensile test specimens prepared as in Clause 3.3. shall be completely immersed in each of the fluids for the times and temperatures specified in Table 1. The volume of the fluid shall not be less than 20 times that of the specimen. After immersion, lightly wipe the specimens and allow to air dry at $23 \pm 2^\circ\text{C}$ for $1\text{h} \pm 15\text{m}$. The Tensile Strength and Ultimate Elongation of each specimen shall be tested according to Clause 3.3. The test shall be repeated on the remaining specified fluids.

3.15 Fungus Resistance

The test method shall be as specified in ISO 846.

The specimens shall be conditioned for 56 days, and tested for Tensile Strength and Ultimate Elongation according to Clause 3.3.

4. RELATED STANDARDS & issue

ASTM D876-00	Standard Test Methods for Nonrigid Vinyl Chloride Polymer Tubing Used for Electrical Insulation
ASTM D882-02	Standard Test Methods for Tensile Properties of Thin Plastic Sheet
ASTM D2671-00	Standard Test Methods for Heat-Shrinkable Tubing for Electrical Use
IEC 60212: 1971	Standard Conditions for Use Prior to and During Testing of Solid Electrical Insulating Materials
IEC 60243-1: 1998	Methods of Test for Electric Strength of Solid Insulating Materials Part 1 Tests at Power Frequencies
ISO 37: 1994	Rubber, vulcanized or thermoplastic - Determination of Tensile Stress-Strain Properties
ISO 62: 1999	Determination of Water Absorption
ISO 188: 1998	Rubber, vulcanized - Accelerated Ageing or Heat Resistance Tests.
ISO 846: 1997	Plastics - Evaluation of the action of microorganisms.
ISO 1183: 1987	Methods for determining the density and relative density of non-cellular plastics
ISO 1817: 1999	Rubber, vulcanized - Determination of the effect of liquids

Subsequent amendments to, or revisions of, any of the above publications apply to this standard only when incorporated in it by updating or revision.

5. SAMPLING

Tests shall be carried out on a sample taken at random from each batch of finished sleeving. A batch of sleeving is defined as that quantity of sleeving extruded at any one time. Testing frequency shall be Production Routine, 10th Batch or Qualification. Production Routine tests consisting of Visual Examination, Dimensions and Longitudinal Change shall be carried out on every batch of sleeving. 10th batch tests shall consist of Tensile Strength, Ultimate Elongation, Secant Modulus at 2% Strain and Specific Gravity. Qualification tests shall be carried out to the requirements of the Design Authority.

6. PACKAGING

Packaging shall be in accordance with good commercial practice. Each package shall bear an identification label showing material quantity, description, size, colour and batch number. Additional information shall be supplied as specified in the contract or order.

TABLE 1 Test Requirements

Test	Test Method	Test Requirements
Visual Examination	-	As per Clause 2.1
Dimensions	ASTM D2671	As per Clause 2.2
Longitudinal Change	ASTM D2671	0 to -10%
Tensile Strength	ISO 37	10 MPa minimum
Ultimate Elongation	ISO 37	250% minimum
Secant Modulus at 2% strain	ASTM D882	100 MPa maximum
Specific Gravity	ISO 1183	1.35 maximum
Heat Shock (4h ± 15m at 250 ± 5°C)	ASTM D2671	No dripping, cracking or flowing
Heat Ageing (168 ± 2h at 175 ± 3°C) - Ultimate Elongation	ISO 188 ISO 37	 150% minimum
Low Temperature Flexibility (4h ± 15m at -55 ± 2°C)	ASTM D2671	No cracking
Flammability	ASTM D876	Duration of burning 15s maximum
Electric Strength	IEC 243	20 MV/m minimum
Copper Contact Corrosion (24 ± 2h on copper mandrel at 90-95% RH, 23 ± 2°C, followed by 168 ± 2h on mandrel at 160 ± 3°C) - Ultimate Elongation	ASTM D2671 ISO 37	No corrosion of mandrel 200% minimum
Copper Mirror Corrosion (16h ± 30m at 175 ± 3°C)	ASTM D2671	No corrosion of mirrors
Water Absorption (24 ± 2h immersion at 23 ± 2°C)	ISO 62	0.5% maximum

TABLE 1 Test Requirements (Cont'd)

Test	Test Method	Test Requirements
Fluid Resistance (24 ± 2h immersion 23 ± 2°C) <ul style="list-style-type: none"> • Gasoline Fuel to ISO 1817 Test Liquid B • Hydraulic Fluid (Phosphate Ester based) to ISO 1817 Test Liquid 103 • Lubricating Oil. (Ester based) to ISO 1817 Test Liquid 101 - Tensile Strength - Ultimate Elongation	ISO 1817 ISO 37	 5 MPa minimum 200% minimum
Fungus Resistance - Tensile Strength - Ultimate Elongation	ISO 846 ISO 37	 10 MPa minimum 250% minimum

In line with a policy of continual product development, TE Connectivity reserves the right to make changes in construction, materials and dimensions without further notice. You are advised, therefore, to contact TE Connectivity, should it be necessary to ensure that this document is the latest issue.