



2.4 GHZ WATERPROOF DIPOLE ANTENNA, IP67

2.4 GHz – 2.5 GHz Waterproof Dipole 2 dBi
Antenna, IP67

ORDERING INFORMATION

ORDER NUMBER	DESCRIPTION
001-0010	2.4 GHz Waterproof Dipole Antenna for Reverse Polarity SMA Connector, IP67
080-0013	U.FL to Reverse Polarity SMA Cable, 105mm, O-Ring Seal
080-0014	U.FL to Reverse Polarity SMA Cable, 210mm, O-Ring Seal

Table 1 Orderable Part Numbers

SPECIFICATIONS

SPECIFICATION	VALUE
Gain	+2 dBi
Impedance	50 ohms
Type	Dipole
Polarization	Linear Vertical
VSWR	≤2.5 : 1
Frequency	2400 - 2500 MHz
Weight	18g
Size	114 mm × 13 mm
Antenna Color	Black
Operating Temp	-40°C to +85°C
UL Rating	UL 94HB

Table 2 Specifications

PHYSICAL DIMENSIONS (MM)




Figure 1 Physical Dimensions

TYPICAL ANTENNA REFLECTION PERFORMANCE




Figure 2 Typical Antenna Reflection Performance

TYPICAL ANTENNA RADIATION PERFORMANCE




Figure 3 Typical E-Plane Antenna Radiation Performance

Total Gain (RSS of Vertical and Horizontal Polarization) (dB)




Figure 4 Typical H-Plane Antenna Radiation Performance

TE TECHNICAL SUPPORT CENTER

- USA: +1 (800) 522-6752
- Canada: +1 (905) 475-6222
- Mexico: +52 (0) 55-1106-0800
- Latin/S. America: +54 (0) 11-4733-2200
- Germany: +49 (0) 6251-133-1999
- UK: +44 (0) 800-267666
- France: +33 (0) 1-3420-8686
- Netherlands: +31 (0) 73-6246-999
- China: +86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original