
IDC SSL Connector

1. SCOPE

1.1. Content

This specification defines performance, tests and quality requirements for the TE Connectivity (TE) Insulation Displacement (IDC) Solid State Lighting (SSL) Connector used with 18 to 24 AWG solid and stranded copper wire in indoor and outdoor lighting.

1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Successful qualification testing on the subject product line was completed on 21Dec10. The Qualification Test Report number for this testing is 501-742. This documentation is on file at and available from Engineering Practices and Standards (EPS).

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. Unless otherwise specified, the latest edition of the document applies. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1. TE Documents

114-13266: Application Specification (IDC SSL Connector)
501-742: Qualification Test Report (IDC SSL Connector)

2.2. Industry Document

EIA-364: Electrical Connector/Socket Test Procedures Including Environmental Classifications

2.3. Reference Document

109-197: Test Specification (Tyco Electronics Test Specifications vs EIA and IEC Test Methods)

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

3.2. Materials

Materials used in the construction of this product shall be as specified on the applicable product drawing.

3.3. Ratings

Voltage: 400 volts AC RMS, 400 volts DC
Current: 8.5 amperes maximum for 18 AWG wire, 7.5 amperes maximum for 20 AWG wire, 7 amperes maximum for 22 AWG wire and 6 amperes maximum for 24 AWG wire.
Temperature: -40° to 105°C

3.4. Performance and Test Description

Product is designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1. Unless otherwise specified, all tests shall be performed at ambient environmental conditions.

3.5. Test Requirements and Procedures Summary

Test Description	Requirement	Procedure
Initial examination of product.	Meets requirements of product drawing and Application Specification 114-13266.	EIA-364-18. Visual and dimensional (C of C) inspection per product drawing.
Final examination of product.	Meets visual requirements.	EIA-364-18. Visual inspection.
ELECTRICAL		
Low Level Contact Resistance (LLCR).	18 milliohms maximum initial. ΔR 5 milliohms maximum.	EIA-364-23. Subject specimens to 100 milliamperes maximum and 20 millivolts maximum open circuit voltage. See Figure 3.
Withstanding voltage.	One minute hold with no breakdown or flashover.	EIA-364-20, Condition I. 1500 volts AC at sea level. Test between adjacent contacts.
Insulation resistance.	One megohm minimum.	EIA-364-21. 500 volts DC, 2 minute hold. Test between adjacent contacts.
Temperature rise vs. current.	30°C maximum temperature rise at specified current.	EIA-364-70, Method 1. Stabilize at a single current level until 3 readings at 5 minute intervals are within 1°C.
MECHANICAL		
Random vibration.	No discontinuities of 1 microsecond or longer duration. See Note.	EIA-364-28, Test Condition VII, Condition Letter D. Subject specimens to 3.10 Gs rms between 20 to 500 Hz. Fifteen minutes in each of 3 mutually perpendicular planes. See Figure 4.
Mechanical shock.	No discontinuities of 1 microsecond or longer duration. See Note.	EIA-364-27, Method H. Subject specimens to 30 G's half-sine shock pulses of 11 milliseconds duration. Three shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks. See Figure 4.

Test Description	Requirement	Procedure										
Wire termination force.	See Figure 5	EIA-364-13. Measure force necessary to terminate wires at a maximum rate of 12.7 mm [.5 in] per minute.										
Termination tensile strength, parallel.	<table border="1"> <thead> <tr> <th>Wire Size (AWG)</th> <th>Crimp Tensile (N [lbf] minimum)</th> </tr> </thead> <tbody> <tr> <td>18 solid</td> <td>102 [23]</td> </tr> <tr> <td>18 stranded</td> <td>53.4 [12]</td> </tr> <tr> <td>24 solid</td> <td>44.5 [10]</td> </tr> <tr> <td>24 stranded</td> <td>22.2 [5]</td> </tr> </tbody> </table>	Wire Size (AWG)	Crimp Tensile (N [lbf] minimum)	18 solid	102 [23]	18 stranded	53.4 [12]	24 solid	44.5 [10]	24 stranded	22.2 [5]	EIA-364-8. Determine tensile strength by pulling parallel to terminated wire at a maximum rate of 12.7 mm [.5 in] per minute. See Figure 6.
Wire Size (AWG)	Crimp Tensile (N [lbf] minimum)											
18 solid	102 [23]											
18 stranded	53.4 [12]											
24 solid	44.5 [10]											
24 stranded	22.2 [5]											
Termination tensile strength, perpendicular.	<table border="1"> <thead> <tr> <th>Wire Size (AWG)</th> <th>Crimp Tensile (N [lbf] minimum)</th> </tr> </thead> <tbody> <tr> <td>18 solid</td> <td>13.5 [3]</td> </tr> <tr> <td>18 stranded</td> <td>17.8 [4]</td> </tr> <tr> <td>24 solid</td> <td>8.9 [2]</td> </tr> <tr> <td>24 stranded</td> <td>8.9 [2]</td> </tr> </tbody> </table>	Wire Size (AWG)	Crimp Tensile (N [lbf] minimum)	18 solid	13.5 [3]	18 stranded	17.8 [4]	24 solid	8.9 [2]	24 stranded	8.9 [2]	EIA-364-8. Determine tensile strength by pulling perpendicular to terminated wire at a maximum rate of 12.7 mm [.5 in] per minute. See Figure 7.
Wire Size (AWG)	Crimp Tensile (N [lbf] minimum)											
18 solid	13.5 [3]											
18 stranded	17.8 [4]											
24 solid	8.9 [2]											
24 stranded	8.9 [2]											
ENVIRONMENTAL												
Thermal shock.	See Note.	EIA-364-32, Test Condition VIII. Subject specimens to 25 cycles between -40 and 105°C with 30 minute dwells at temperature extremes and 1 minute transition between temperatures.										
Humidity/temperature cycling.	See Note.	EIA-364-31, Method III. Subject specimens to 10 cycles (10 days) between 25 and 65°C at 80 to 100% RH.										
Temperature life.	See Note.	EIA-364-17, Method A, Test Condition 4. Subject specimens to 105°C for 648 hours.										

NOTE *Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Requalification Test Sequence shown in Figure 2.*

Figure 1

3.6. Product Qualification and Requalification Test Sequence

Test or Examination	Test Group (a)				
	1	2	3	4	5
	Test Sequence (b)				
Initial examination of product	1	1	1	1	1
LLCR	2,5	2,7			
Withstanding voltage			3,8		
Insulation resistance			2,7		
Temperature rise vs. current		3,8			
Random vibration	3	6			
Mechanical shock	4				
Wire insertion force				2	2
Termination tensile strength, parallel				3	
Termination tensile strength, perpendicular					3
Thermal shock			4		
Humidity/temperature cycling		4	5		
Temperature life		5	6		
Final examination of product	6	9	9	4	4

NOTE (a) See paragraph 4.1.A.
 (b) Numbers indicate sequence in which tests are performed.

Figure 2

4. QUALITY ASSURANCE PROVISIONS

4.1. Qualification Testing

A. Specimen Selection

Specimens shall be prepared in accordance with applicable instruction sheets and shall be selected at random from current production. Each test group shall consist of a minimum of 5 specimens.

B. Test Sequence

Qualification inspection shall be verified by testing specimens as specified in Figure 2.

4.2. Requalification Testing

If changes significantly affecting form, fit or function are made to the product or manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

4.3. Acceptance

Acceptance is based on verification that the product meets the requirements of Figure 1. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify the product. If product failure occurs, corrective action shall be taken and specimens resubmitted for qualification. Testing to confirm corrective action is required before resubmittal.

4.4. Quality Conformance Inspection

The applicable quality inspection plan shall specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.




Figure 3
LLCR Measurement Points




Figure 4
Vibration and Mechanical Shock Mounting Fixture

Position Size	Wire Size (AWG)	
	18	24
Stranded Wire		
1	222.4 [50]	133.4 [30]
4	778.4 [175]	556 [125]
Solid Wire		
1	178 [40]	89 [20]
4	890 [200]	444.8 [100]

NOTE All values in N [lbf] maximum

Figure 5
Wire Termination Force




Figure 6
Termination Tensile Strength, Parallel




Figure 7
Termination Tensile Strength, Perpendicular