





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	21OCT2015	RG	SH



SCALE 4.000

- NOTES:
- UNLESS OTHERWISE SPECIFIED
 - 1. INTERPRET DRAWING PER ASME Y14.5M - 1994.
 - 2. 0,2mm MAX BURR.
 - 3. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
 - 4. RoHS COMPLIANT AND CERTIFIED.



NICKEL PLATED	ALUMIMUM	2170127-3
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Robert Gan	21OCT2015	TE Connectivity	
DIMENSIONS: mm		CHK	21OCT2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Sean Han		NAME QSFP SINGLE CUSTOM EXTRUSION	
0 PLC ±0.5		PRODUCT SPEC		HEATSINK HEIGHT 8.5MM	
1 PLC ±0.25		APPLICATION SPEC		6.5mm TALL	
2 PLC ±0.25		WEIGHT		SIZE	RESTRICTED TO
3 PLC ±0.25		Customer Drawing		A20779	-
4 PLC ±0.25		SCALE 4.000		C-2170127	
ANGLES ±8°		SHEET		OF	REV
FINISH		SHEET		OF	REV
SEE TABLE		SHEET		OF	REV
SEE TABLE		SHEET		OF	REV