

DESIGN OBJECTIVES

108-3645

The product described in this document has not been fully tested to ensure conformance to the requirements outlined herein. TE Connectivity makes no representation or warranty, express or implied, that the product will comply with these requirements, Further, TE Connectivity reserves the right these requirements based on the results of additional testing and evaluation. Contact TE Connectivity Engineering for further information. If necessary, this document will become the Product Specification at successful completion of testing.

1 SCOPE

1.1 Content

This specification covers the performance, tests and quality requirements for the TE AK2 Short Circuit Ring (SCR).

1.2 Qualification


When tests are performed on the subject product line, the procedures specified in TE 109 series specifications shall be used unless otherwise specified. All inspections shall be performed using the applicable inspection plans and product drawings.

2 APPLICABLE DOCUMENTS

The following documents form part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, the referenced documents shall take precedence.

2.1 TE Drawings

1823640 / C1823640:	SHORT CIRCUIT RING ASSY
1823639:	SHORT CIRCUIT RING HSG
1823638:	SHORT CIRCUIT CONTACT

				DR W.ZHANG	 TE Connectivity Shanghai, China		
				CHK J.CHANG			
				APP I.YIN	NO. 108-3645	REV A	LOC ES
A	Released	W.Z	2012 JAN 20	PAGE	AK2 Short Circuit Ring		
LTR	REVISION ECORD	DR	DATE	1 of 6			

2.2 TE Documents

- A. 109-1: General requirements for test specifications.
- B. VDA AK2 Interface Drawing 8377216 5.
- C. ISO 19072: Connection interface for pyrotechnic devices - Part 1: Pocket interface definition
- D. ISO 19072: Connection interface for pyrotechnic devices - Part 2: Test methods and general performance requirements
- E. ISO 19072: Connection interface for pyrotechnic devices - Part 4: Pyrotechnic device and harness connector assy – Type 2.
- F. ISO 8092: Connections for on-board electrical wiring harnesses – Part 2: Definitions, test methods and general requirements

3 DEFINITION OF TERMS

For the purpose of this specification, the following terms shall apply:

3.1 Short Circuit Contact

An electrically conductive member, used as a component of an assembly to form a circuit connection.

3.2 Housing

A dielectric component member of an assembly, made of insulating material that retains the shorting contact.

3.3 SCR (Short Circuit Ring)

A short circuit ring comprises of a short circuit contact to link gas generator pins and a housing to retain the squib connector in the gas generator.



TE Connectivity
Shanghai, China

PAGE

2 of 6

NO.

108-3645

REV

A

LOC

ES

4 REQUIREMENTS

4.1 MATERIALS

A Short circuit contact: Stainless Steel with gold plated contact interface.

B Housing: Moulded in 10% Glass Filled PBT.

4.2 RATINGS

A. Voltage: 6-18V

B. Temperature: -40 to +105 °C
Storage Temperature: -40 to +90 °C (+100 °C, 1h)

C. Relative Humidity: Up to 95%

5 TEST DESCRIPTION

The product is designed to meet the electrical, mechanical and environmental performance requirements specified in the following sections of this document. All tests are performed at ambient environmental conditions per AMP specification 109-1 unless otherwise specified.



TE Connectivity
Shanghai, China

PAGE

3 of 6

NO.

108-3645

REV

A

LOC

ES

5.1 Test requirements and procedures

Para.	Test items	Requirements	Procedures
5.1.1	Visual inspection	The test specimens are to be inspected for defects or changes before and after the test.	In accordance with ISO19072-2, Part 4.2
5.1.2	Squib connector Mating and un-mating (10 cycles)	Shall meet requirements of subsequent tests. Mating / un-mating force measurement is not required.	In accordance with ISO 8092-2, Part 4.3 (Mating / un-mating force measurement is not required.)
5.1.3	Mechanical strength of SCR in squib holder	>20N	In accordance with ISO19072-2, Part 4.5
5.1.4	Combination of temperature / humidity / vibration	Shall meet requirements of subsequent tests. Contact resistance measurements are not required.	In accordance with ISO19072-2, Part 4.6 (Contact resistance measurements are not required.)
5.1.5	Polarisation	Electrical connection shall not be possible with $\leq 100N$ Shorting contact shall not be opened with $\leq 200N$	In accordance with ISO19072-2, Part 4.8
5.1.6	Thermal Ageing	Shall meet requirements of subsequent tests	In accordance with ISO19072-2, Part 4.12 Duration: 100h, Temp: 125 degC Test to be completed with squib connector mated.
5.1.7	Opening and Closing of the short circuit	Correct opening sequence as per ISO 19072-2, table B.1	In accordance with ISO19072-2, Part 4.13
5.1.8	Short Circuit resistance	Circuit resistance from pin to pin across shorting contact: $\leq 100mOhms$ Bulk resistance of shorting contact $\leq 40mOhms$	In accordance with ISO19072-2, Part 4.14
5.1.9	Shorting contact Force	>0.5N	Measure the shorting contact force in its shorted position against pin (see drg 1703886 for required contact deflection).
5.1.10	Shorting contact retention force	>25N	Contact to be removed from housing at a speed rising to 25mm/min.



TE Connectivity
Shanghai, China

PAGE

4 of 6

NO.

108-3645

REV

A

LOC

ES

5.2 TEST SEQUENCE

TEST DESCRIPTION		TEST GROUP					
		A	B	C	D	E	F
5.1.1	Visual inspection	1, 4	1, 5	1, 3	1, 7	1, 5	1, 3
5.1.2	Squib connector Mating and un-mating (10 cycles)				2		
5.1.3	Mechanical strength of SCR in squib holder	3					
5.1.4	Combination of temperature / humidity / vibration		3				
5.1.5	Polarization			2			
5.1.6	Thermal Ageing	2			5	3	
5.1.7	Opening and Closing of the short circuit				3		
5.1.8	Short Circuit resistance		2,4		4,6		
5.1.9	Shorting contact Force					2,4	
5.1.10	Shorting contact retention force						2



TE Connectivity
Shanghai, China

PAGE

5 of 6

NO.

108-3645

REV

A

LOC

ES

6 TEST SAMPLES

DESCRIPTION	SAMPLE QUANTITIES					
	A	B	C	D	E	F
SCR ASSY 1-1823640-1	10	10	4	10	10	10
SCR ASSY 2-1823640-1			3			
SCR ASSY 3-1823640-1			3			
SCR ASSY 4-1823640-1			3			
SQUIB connector Code A & 1M Cable assy		10	4	10	10	
SQUIB connector Code B & 1M Cable assy			3			
SQUIB connector Code C & 1M Cable assy			3			
SQUIB connector Code D & 1M Cable assy			3			
Pocket interface - Type VDA AK /BNA	5	5	5	5		
Pocket interface –Type ISO19072-1	5	5	5	5		



TE Connectivity
Shanghai, China

PAGE

6 of 6

NO.

108-3645

REV

A

LOC

ES