




REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
D		REV PER ECO 20-001334	6-23-20	CT VR



- 1 MODULE MARKED WITH TE PART NO. USING .060 MINIMUM HIGH CHARACTERS.
- 2 MODULE MARKED WITH "AMP" AND DATE CODE USING .060 MINIMUM HIGH CHARACTERS.
- 3 SCHEMATIC DIAGRAM MARKED IN AREA SHOWN
- 4. CONTACTS ARE PACKAGED IN A SEPARATE CONTAINER AND SHIPPED WITH CONNECTOR.



DESCRIPTION	MATERIAL	FINISH
MODULE ASSEMBLY	EPOXY EPIALL 1908-B, OR E-484, OR FIBERITE E-8354	COLOR: BLACK
GROMMET	FLUORSILICONE BLEND	COLOR: RED
RETAINING CLIP	STAINLESS STEEL PER QQ-S-766	NONE
CONTACT SOCKET	COPPER ALLOY 172 OR COPPER ALLOY 173 WITH LEAD	GOLD PLATE OVER NICKEL UNDERPLATE
CAPACITOR	CK128X392K QTY = 1	--
RESISTOR	RNC55H4022FM QTY = 2	--

591869-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-6-18		
DIMENSIONS: INCHES		CHK V.RAMOS 11-6-18		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD V.RAMOS 11-6-18	NAME	
0 PLC ± -		PRODUCT SPEC	FEEDBACK MODULE WITH RESISTORS AND CAPACITOR, SIZE 20,TJ	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		SIZE	CAGE CODE	DRAWING NO
3 PLC ± .005		A2	00779	C=591869
4 PLC ± -		WEIGHT	RESTRICTED TO	
ANGLES ± -		0.000000	-	
MATERIAL	FINISH	CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1
-	-			REV D