



The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, TE Connectivity (TE) makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, TE may change these requirements based on the results of additional testing and evaluation. Contact TE Engineering for further details.

025/060/110 HYB 25P CAP & PLUG ASSY

1. Scope

1.1 Content

This specification defines the test method for 025/060/110 HYB 25P CAP & PLUG ASSY.

1.2 Qualification

When testing the named products, the following specified specifications and standards shall be used.

All tests have to be done using the applicable inspection plan and product.

1.3 Applied Product

- 2109517 025/060/110 HYB 25P CAP ASSY
- 2109520 025/060/110 HYB 25P PLUG ASSY

2. Applicable Documents

The following documents, if they are referred inside this document, are part of this specification.

In case of conflict between the requirements of this specification and the product drawing or in conflict between the requirements of this specification and the referenced documents, this specification has precedence

2.1 TE Connectivity Documents

- A. 109-1: General Requirements for Test specifications.
- B. Customer Drawings
 - 2109517 025/060/110 HYB 25P CAP ASSY
 - 2109520 025/060/110 HYB 25P PLUG ASSY

2.2 HKMC specification

- ES-91500-00 HKMC Connector General Spec.
- MS300-08 HMC Combustibility Spec.
- MS300-34 HMC Smell Spec.
- MS201-02 HMC Material Spec.
- MS300-55 HMC VOCs Spec.

A1	LOCAL DOC TYPE Updated	SP/HM	09JAN2024
A	RELEASED	CI JEON	24. Mar '20
LTR	Revision Record	DR/CHK	Date

3. Requirements

No.	Items	Characteristics			Remarks
1	Appearance	No harmful crack, rust, burr, damage, deformation, discoloration etc.			
2	Connector engage and disengage force	7.6kgf or less			
3	Reverse insertion between housings	It shall not be incorrectly inserted by applying force of 20kgf			
4	Reverse insertion between terminal and housing	025: 3kgf or more / 060: 5kgf or more			
5	Engage force between terminal and housing	1.5kgf or less			
6	CONN Clip panel engage and retention force	Engage: Max 12kgf or less / Retention: Min 15kgf or more			
7	Housing locking strength	10kgf or more			
8	Lock release force	Force on release force point of lock part shall be 6kgf or less			
9	Terminal retention force	025: 6kgf or more / 060: 8kgf or more / 110: 10kgf or more at secondary locking condition			
10	Voltage drop	Division	Initial	After endurance	
		025	10 mV/A or less	10 mV/A or less	
		060	5 mV/A or less	10 mV/A or less	
		110	3 mV/A or less	20 mV/A or less	
11	Insulation resistance	Division	Initial	After endurance	
		Non-waterproof	100MΩ or more	100MΩ or more	
12	Leakage current	Division	Initial	After endurance	
		Non-waterproof	10 μA or less	10 μA or less	
13	High voltage test	There shall be no insulation break.			
14	Temperature rise	Division	Initial	After endurance	
		General Connector	30°C or less	40°C or less	
15	Instant short circuit	There shall be no 10μs or more instant short circuit.			

< Table 1 >

No.	Items	Characteristics	Remarks
16	engage and retention force between clip and housing	Engage: Max 6kgf or less / Retention: Min 11kgf or more	
17	Connector coupling sound	65 dB(A) or more	
18	Overcurrent cycle test	See Requirement No: 3.1 / 3.10 / 3.14 @ Basic current: 2.4A	
19	Cold temperature test	See Requirement No: 3.1 / 3.10 / 3.11 / 3.12 / 3.14	
20	Cold and hot temperature shock test	See Requirement No: 3.1 / 3.10	
21	High temperature test	See Requirement No: 3.1 / 3.10	
22	Temperature Humidity test	See Requirement No: 3.1 / 3.10 / 3.11 / 3.12	
23	Dust test	See Requirement No: 3.10	
24	Ozone test	See Requirement No: 3.1 / 3.10	
25	Sulfur gas test	See Requirement No: 3.1 / 3.10	
26	Complex environment endurance test	See Requirement No: 3.1 / 3.10 / 3.14 / 3.15	

< Table 2 >

4. Test conditions

4.1 Specimen

Unless there is specific mention, initial sample should use for the test specimen, and test specimen shall be 5EA or more for each cavity. However, if performance is expected to be clearly satisfactory ever by applying load to the same specimen in turn, it is possible to apply multiple test items to the same specimen. In such case, performance shall be satisfied with each item.

4.2 Laboratory condition

Perform each test at designated temperature and humidity. And control humidity at designated absorption ratio for the connector which uses absorbent resin housing.

Temperature: 25 ± 5 °C, Humidity: $60 \pm 20\%$