


Tyco Dwg 6-1532005-2  
Micro P/N 132-0508-0001



						DELETED			(11)
	1	1	1	1	003-0861-0001	SEALING SLEEVE	SILICONE RUBBER		(10)
(3)	1	1	1	1	003-0938-0002	MIDDLE SLEEVE	LEADED COPPER		(9)
(3)	1	1	1	1	003-0939-0002	INNER SLEEVE	BRASS, QD-B-626		(8)
	1	1	1	1	1000-0301-0164	CABLE INSULATOR	HALAR		(7)
						DELETED			(6)
(3)	1	1	1	1	003-0897-0002	PIN CONTACT	COPPER ALLOY		(5)
(5)	(3)	1			1003-1524-0001	HOUSING SUB-ASSY NUT-1/4" HEX W/WIRE HOLES			(4)
						DELETE			(3)
						DELETE			(2)
						DELETE			(1)
						COMPONENT No.	NOMENCLATURE	MAT'L & SPEC.	ITEM

(7) CABLE ACCOMMODATION DIMS:  
 JACKET DIA. ----- .110 MAX  
 DIELECTRIC DIA. ----- .057-.070  
 INNER CONDUCTOR DIA. --- .009-.019  
 FOR ENVIRONMENTAL SEAL USE EXTRUDED JACKET

6. FOR ELECTRICAL, MECHANICAL, & ENVIRONMENTAL SPECS. SEE MALCO CATALOG.

(5) .016 DIA. WIRE HOLE 3 PLACES

(4) DELETED

(3) GOLD PLATE PER MIL-G-45204, TYPE II, GR: C, CL: I

2. SEE REF ASMB-8 ASSY INSTRUCTIONS. SPECIAL TOOL REQ'D:  
 CONTACT CRIMP: 010-0134-0000 & LOCATOR 001-0104-0000  
 ALTERNATE TOOL 010-0065-0000 (NO LOCATOR REQUIRED)  
 HOUSING CRIMP: 010-0082-0000

1. THIS CONNECTOR MATES WITH ALL 50 Ω GOLDEN CRIMP, CRIMP SILVER & ALL S-50 JACKS & RECEPTACLES AS LISTED IN MALCO CATALOG

NOTES: UNLESS OTHERWISE SPECIFIED

ASSEMBLY NO REQ'D		A CUSTOMER USE DWG		STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. ± FRAC. ± ANGLES ± ECCENTRICITY MAX. T.I.R. HOLE DIA. ± SURFACE ROUGHNESS MICRO INCHES THREADS TO MIL-S-7742 COMMERCIAL TOLERANCES APPLY TO STOCK DIMENSIONS		<b>MALCO</b> A MICRODOT COMPANY, INC. 220 PASADENA AVE., SO. PASADENA,		SURFACE TREATMENT NOTED		APP APP CHECKED BY C.E.H. DRAWN BY D.D.	
NEXT ASSEMBLY		LET	ECO	REVISION DESCRIPTION	DATE	APP	MATERIAL NOTED		SCALE ∞	WT	DATE 3-3-78
PLUG ASSEMBLY ENVIRONMENTAL GOLDEN CRIMP 50 Ω (RG-188)							PROD CODE 941	DRAWING NUMBER 132-0508-000A		CD	