




CATALOGUE NUMBER: FAD1385-1445-6 SUITS CONDUCTOR

DEADEND

STRANDING/CONDUCTOR	COND. TYPE	DIAMETER	FITTING LAY
7/4.75	AAC/AAAC	14.25	RIGHT HAND
7/0.186	AAC/AAAC	14.17	RIGHT HAND
7/5.00 COMPACTED	AAC/AAAC	14.00	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD1385-1445-6
 DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
 MATERIAL: ALUMINIUM ALLOY
 NUMBER OF RODS: 6
 ROD DIAMETER: 3.65mm
 OVERAL LENGTH: 870mm
 END FINISH: CHAMFERED
 FITTING LAY DIRECTION: RIGHT HAND
 COLOUR CODED: BLUE

BOX LABEL

P/N: FAD1385-1445-6
 ID:
 DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
 7/4.75 AAC/AAAC
 7/0.186 AAC/AAAC
 7/5.00 COMPACTED AAC/AAAC
 RANGE: 13.85 - 14.45
 COLOUR-CODE: BLUE
 QTY: 20 WEIGHT: BATCH:

PRODUCT LABEL

FAD1385-1445-6
 7/4.75 AAC/AAAC
 7/0.186 AAC/AAAC
 7/5.00 COMPACTED AAC/AAAC

WEIGHT: 0.32kg
 BATCH NO:
 MONTH/YEAR:

LOC						IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5%. UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN -	TITLE FULL-TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø 13.85-Ø 14.45 7/4.75 & 7/0.186 AAC/AAAC 7/5.00 COMPACTED AAC/AAAC					
						PART Alias UTX/DUL FAD1385-1445-6			Cat No FAD1385-1445-6					
DIST	—	I	NEW RELEASE	15-05-2013	RN	AT	MATERIAL DESC ALUMINIUM ALLOY			DRAWN RN	DATE 15-05-2013	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
	POS	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO	CHECKED MN	APPROVED AT			DRAWING NO FAD1385-1445-6-C
								Format: generic_m03.au.rl.frm	Template: tec_generic_a3.metric.au.rl.drw		Deg No from P1 Mod Fam Tbl: 2	>AUXXXXX		