



Certificate of Compliance

Certificate: 1505185 **Master Contract:** 164196 (LR 7189)

Project: 80044741 **Date Issued:** 2021-02-17

Issued To: TE Connectivity Corporation
2901 Fulling Mill Road
Middletown, Pennsylvania, 17057-3163
United States

Attention: Steve Bolash

The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.



Michael Chung
Issued by: Michael Chung

PRODUCTS

CLASS 6233 01 - RECEPTACLES Attachment Plug Type and Plugs

CLASS 6233 81 - RECEPTACLES Attachment Plug Type and Plugs - Certified to US Standards

S-use "CPC" connectors 2XXXXX:

Series 1 (4 position), rated 22A (1-pole), 21A (2-poles), 16A (3 to 4-poles), 600V.

Series 1 (9 position), rated 22A (1-pole), 16A (2 to 5-poles), 12A (6 to 9-poles), 600V.

Series 1 (14 position), rated 22A (1-pole), 13A (2 to 8-poles), 10A (9 to 14-poles), 600V.

Series 1 (16 position), rated 22A (1-pole), 13A (2 to 8-poles), 10A (9 to 16-poles), 600V.

Series 1 (24 position), rated 22A (1-pole), 13A (2 to 12-poles), 10A (13 to 24-poles), 600V.

Series 1 (37 position), rated 22A (1-pole), 11A (2 to 19-poles), 8A (20 to 37-poles), 600V.

Series 2, rated 7.5A max, 250V.

Series 3, rated 35A max, 600V.

Series 4, rated 35A max, 600V.

Series 5, rated 50A max, 250V.

Series 6, rated 50A max, 600V.

APPLICABLE REQUIREMENTS

CSA Std. C22.2 No. 182.3-16, 2nd Ed - Special Use Attachment Plugs, Receptacles, and Connectors

UL Std. No. 1977, 3rd Ed - Component Connectors for Use in Data, Signal, Control and Power Applications