

TO BE SOLD
ONLY WITH
INSTALLATION
INSTRUCTIONS

Closed End Splice Pressure Type Wire Connectors
Type ECV Wire Combinations
Catalog No. 53891-1
CU

 424C
LISTED

 Circular Mil Range 19,500 to 42,700 — Use "18-6 ECV" Tooling
 Strip Length — 18.26 mm [.719 in.] Min
 19.84 mm [.781 in.] Max

 105°C [222°F]
Max

 UL Listed Wire Combinations Solid or Stranded Wire Sizes 18-6 AWG
 600 Volts Max Building Wiring 1000 Volts Max Fixture or Sign

WIRE SIZE (AWG)	NO. OF WIRES	NO. OF ADDITIONAL WIRES OF ONE WIRE SIZE						
		18	16	14	12	10	8	6
18	1	12-15	7-13	5-7	3-5	2-3	2	1
	2	11-14	7-12	4-7	3-5	2-3	1-2	1
	3	10-13	6-11	4-7	3-5	2-3	1-2	1
	4	9-12	6-10	4-6	2-5	2-3	1-2	1
	5	8-11	5-9	3-6	2-5	2-3	1-2	1
	6	7-10	4-9	3-5	2-4	1-3	1	1
	7	6-9	4-8	2-5	2-4	1-2	1	—
	8	5-8	3-7	2-4	1-4	1-2	1	—
	9	4-7	2-6	2-4	1-4	1	1	—
	10	3-6	2-5	1-3	1-3	1	1	—
	11	2-5	1-5	1-3	1-3	1	1	—
	12	1-4	1-4	1-2	1-2	1	—	—
	13	1-3	1-3	1	1	—	—	—
	14	1-2	1-2	1	—	—	—	—
	15	1	1	—	—	—	—	—
16	1	11-15	7-13	5-7	3-5	2-3	2	1
	2	9-14	6-12	4-7	3-5	2-3	1-2	1
	3	8-13	5-11	3-6	2-5	2-3	1-2	1
	4	6-12	4-10	3-6	2-4	1-3	1	1
	5	5-11	3-9	2-5	2-4	1-2	1	1
	6	3-9	2-8	1-5	1-3	1	1	—
	7	1-8	1-7	1-4	1-3	1	—	—
	8	1-7	1-6	1-3	1-2	1	—	—
	9	1-6	1-5	1-3	1-2	1	—	—
	10	1-4	1-4	1-2	1	—	—	—
	11	1-3	1-3	1	1	—	—	—
	12	1-2	1-2	1	—	—	—	—
	13	1	1	—	—	—	—	—
14	1	10-14	6-12	4-7	3-5	2-3	1-2	1
	2	7-12	5-10	3-6	2-5	2-3	1-2	1
	3	5-11	3-9	2-5	2-4	1-2	1	1
	4	2-9	2-7	1-4	1-3	1-2	1	—
	5	1-7	1-6	1-3	1-2	1	—	—
	6	1-5	1-4	1-2	1	1	—	—
	7	1-3	1-2	1	—	—	—	—
12	1	8-13	6-11	4-6	2-5	2-3	1	1
	2	4-12	3-9	2-5	1-4	1-2	1	1
	3	1-11	1-7	1-4	1-3	1-2	1	—
	4	1-9	1-5	1-3	1-2	1	—	—
	5	1-5	1-3	1-2	1	—	—	—
10	1	6-12	4-9	3-6	2-4	1-3	1	1
	2	1-8	1-5	1-4	1-3	1-2	1	—
	3	1-6	1-4	1-2	1	1	—	—
8	1	2-11	2-6	1-4	1-3	1-2	—	—
	2	1-5	1-2	1-2	—	—	—	—
	6	1	1-6	1-5	1-3	1-2	1	—

INSTRUCTIONS: Use as shown for OEM applications. For all field applications, twist wires together before crimping. Minimum loading is thirteen wires size 18 AWG.

CU

 TO BE SOLD
ONLY WITH
INSTALLATION
INSTRUCTIONS

Closed End Splice Pressure Type Wire Connectors
Type ECV Wire Combinations
Catalog No. 53891-1

 424C
LISTED

 Circular Mil Range 19,500 to 42,700 — Use "18-6 ECV" Tooling
 Strip Length — 18.26 mm [.719 in.] Min
 19.84 mm [.781 in.] Max

 105°C [222°F]
Max

 UL Listed Wire Combinations Solid or Stranded Wire Sizes 18-6 AWG
 600 Volts Max Building Wiring 1000 Volts Max Fixture or Sign

WIRE SIZE (AWG)	NO. OF WIRES	NO. OF ADDITIONAL WIRES OF ONE WIRE SIZE						
		18	16	14	12	10	8	6
18	1	12-15	7-13	5-7	3-5	2-3	2	1
	2	11-14	7-12	4-7	3-5	2-3	1-2	1
	3	10-13	6-11	4-7	3-5	2-3	1-2	1
	4	9-12	6-10	4-6	2-5	2-3	1-2	1
	5	8-11	5-9	3-6	2-5	2-3	1-2	1
	6	7-10	4-9	3-5	2-4	1-3	1	1
	7	6-9	4-8	2-5	2-4	1-2	1	—
	8	5-8	3-7	2-4	1-4	1-2	1	—
	9	4-7	2-6	2-4	1-4	1	1	—
	10	3-6	2-5	1-3	1	1	—	—
	11	2-5	1-5	1-3	1	1	—	—
	12	1-4	1-4	1-2	1-2	1	—	—
	13	1-3	1-3	1	1	—	—	—
	14	1-2	1-2	1	—	—	—	—
	15	1	1	—	—	—	—	—
16	1	11-15	7-13	5-7	3-5	2-3	2	1
	2	9-14	6-12	4-7	3-5	2-3	1-2	1
	3	8-13	5-11	3-6	2-5	2-3	1-2	1
	4	6-12	4-10	3-6	2-4	1-3	1	1
	5	5-11	3-9	2-5	2-4	1-2	1	1
	6	3-9	2-8	1-5	1-3	1	1	—
	7	1-8	1-7	1-4	1-3	1	—	—
	8	1-7	1-6	1-3	1-2	1	—	—
	9	1-6	1-5	1-3	1-2	1	—	—
	10	1-4	1-4	1-2	1	—	—	—
	11	1-3	1-3	1	1	—	—	—
	12	1-2	1-2	1	—	—	—	—
	13	1	1	—	—	—	—	—
14	1	10-14	6-12	4-7	3-5	2-3	1-2	1
	2	7-12	5-10	3-6	2-5	2-3	1-2	1
	3	5-11	3-9	2-5	2-4	1-2	1	1
	4	2-9	2-7	1-4	1-3	1-2	1	—
	5	1-7	1-6	1-3	1-2	1	—	—
	6	1-5	1-4	1-2	1	1	—	—
	7	1-3	1-2	1	—	—	—	—
12	1	8-13	6-11	4-6	2-5	2-3	1	1
	2	4-12	3-9	2-5	1-4	1-2	1	1
	3	1-11	1-7	1-4	1-3	1-2	1	—
	4	1-9	1-5	1-3	1-2	1	—	—
	5	1-5	1-3	1-2	1	—	—	—
10	1	6-12	4-9	3-6	2-4	1-3	1	1
	2	1-8	1-5	1-4	1-3	1-2	1	—
	3	1-6	1-4	1-2	1	1	—	—
8	1	2-11	2-6	1-4	1-2	1	—	—
	2	1-5	1-2	1-2	—	—	—	—
	6	1	1-6	1-5	1-3	1-2	1	—

INSTRUCTIONS: Use as shown for OEM applications. For all field applications, twist wires together before crimping. Minimum loading is thirteen wires size 18 AWG.