


**SPECIAL MANUFACTURING REQUIREMENTS  
RNF-100 4.5/1.9-CL  
Heat - Shrinkable Tubing**



**Table 1: Dimensions** Inches (MM)

As Supplied	Recovered	
<b>Inside Diameter Minimum (D)</b>	<b>Inside Diameter Maximum (d)</b>	<b>Wall Thickness Nominal (W)</b>
<b>0.179 ± 0.01 in.</b> (4.55 ± 0.25MM)	<b>0.075 ± 0.008 in.</b> (1.9 ± 0.20MM)	<b>0.16 ± 0.003 in.</b> (0.4 ± 0.08MM)

**Color:** Clear

**Longitudinal Change:** +0, -10%

**Spool Length:** 500 Feet per spool, No Splice

**Box Quantity:** 2 spools

**Physical Properties:** Except as specified above, RNF-100-4.5/1.9 shall meet all the requirements of RT-350.

<b>tyco</b> <i>Electronics</i>	Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA 94025 USA	<b>Raychem</b>	<b>Specification Control Drawing</b> Title: <b>Special Manufacturing Requirements RNF-100 4.5/1.9-CL Heat - Shrinkable Tubing</b>			
	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application		Document No : <b>RNF-100 4.5/1.9-CL</b>			
Cage Code: 06090	Scale: None	Size: A	Rev. Date: 7-Sep-99	Rev.: None	Sheet: 1 of 1	

If this document is printed it becomes uncontrolled. Check for the latest revision.