

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

- TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 1000V  
RATED CURRENT: 100A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 8KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE:  $10.0mm^2 \sim 35.0mm^2$   
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T20500020XX000)

注释:

- 技术参数:  
绝缘材料: PC  
额定电压: 1000V  
额定电流: 100A  
绝缘电阻:  $\geq 400M\Omega$   
脉冲电压: 8KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围:  $10.0mm^2 \sim 35.0mm^2$   
接线类型: 冷压接
- 端子需要单独订购.  
(订货号参考图面: T20500020XX000)

T2111028201-007	HMN-D2-FC	HMN-D2-FC FEMALE MODULE INSERT HMN-D2-FC 模块母插
-----------------	-----------	--

PART NUMBER  
料号PART DESCRIPTION  
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

FINISH

-

-

DWN 19SEP2017

YORK CHEN

CHK 19SEP2017

GINO YAO

APVD 19SEP2017

CHRIS WANG

PRODUCT SPEC

108-137058

APPLICATION SPEC

114-137058

WEIGHT

-

NAME

HMN-D2-FC

SIZE

A3

CAGE CODE

00779

DRAWING NO

T2111028201007

RESTRICTED TO

-

Customer Drawing

SCALE

1:1

SHEET

1 OF 1

REV

B

1470-19 (3/13)