

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 690V
RATED CURRENT: 40A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 1~6 mm² (18~10 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20400X10XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 690V
额定电流: 40A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 1~6 mm² (18~10 AWG)
接线类型: 冷压接
- 端子需要单独订购。
(订货号参考图面: T20400X10XX000)

T2111032101-007	HMN-003-M	HMN-003 MALE MODULE INSERT HMN-003 模块公插
-----------------	-----------	--

PART NUMBER
料号PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 19SEP2017

YORK CHEN

CHK 19SEP2017

GINO YAO

APVD 19SEP2017

CHRIS WANG

PRODUCT SPEC

108-137118

APPLICATION SPEC

114-137118

WEIGHT

-

CUSTOMER DRAWING

NAME

HMN-003-M

SIZE

A3

CAGE CODE

00779

DRAWING NO

G-T2111032101007

RESTRICTED TO

-

SCALE

3:2

SHEET

1 OF 1

REV

B

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

-

FINISH

-

-

TE Connectivity

1470-19 (3/13)