

A close-up photograph of a white, braided flexible wire. The wire is shown in a smooth, S-shaped curve, highlighting its flexibility. The background is a gradient of blue, from a darker shade at the top to a lighter shade at the bottom. The lighting is soft, creating subtle highlights and shadows on the wire's surface.

SHF-260 HIGHLY FLEXIBLE WIRE

EXCELLENT FLEXIBILITY FOR EASIER ROUTING IN
POWER FEEDER APPLICATIONS WITH A HIGH-TEMPERATURE
AND HIGH-PERFORMANCE WIRE

SHF-260 HIGHLY FLEXIBLE WIRE

Excellent Flexibility in a High-Performance wire



HIGHLY FLEXIBLE

- Down to 6x bending radius
- Tight routing and bending
- No wrinkling or cracking of insulation
- Reduces contact stress and mating/unmating forces

HIGH PERFORMANCE

- Outstanding chemical and fluid resistance
- Meets FAR Part 25 flammability requirements
- Excellent high temperature performance: 260°C (10,000 hours); 290°C (500 hours)

EXCELLENT ELECTRICAL PERFORMANCE

- Arc track resistant
- All extruded single or dual wall fluoropolymer insulation system

SHF-260 highly flexible wire satisfies the need for high temperature and high performance in large-diameter power feeder applications where easy routing and durability are key.

The cable's high flexibility allows it to be routed in extremely tight spaces—often shortening the required run—with no wrinkling or cracking of the insulation.

Flexibility of the SHF-260 wire serves to reduce stress on the contact and to reduce the mating and unmating forces normally associated with large circular connectors, such as MIL-DTL-5015 and MIL-DTL-83723 connectors.

The ability to route the cable in tight spaces may allow you to increase gauge size and eliminate the need to split power.

Available in 24 AWG to 4/0 AWG sizes, typical uses for SHF-260 wire include both primary and secondary power distribution applications where high current is needed and where routing in tight spaces is essential.

In addition to excellent flexibility and routability, SHF-260 wire provides outstanding chemical and fluid resistance, excellent electrical properties, and high-temperature performance to 260°C.

TE Components . . . TE Technology . . . TE Know-how . . .

AMP | Agastat | CII | Hartman | Kilovac | Microdot | Nanonics | Polamco | Raychem | Rochester | DEUTSCH
SEACON Phoenix | L.L. Rowe | Phoenix Optix | AFP | SEACON

Get your product to market faster with a smarter, better solution.



MATERIALS

- **Insulation:** Modified PFA
- **Conductors:** Nickel-coat copper

ENVIRONMENTAL/MECHANICAL PERFORMANCE

- **Temperature Range:** -65°C to +260°C
- **Life Cycle:** 290°C for 500 hours
- **Cold Bend:** -65°C for 4 hours
- **Thermal Shock Resistance:** AS22759 using an oven temperature of 260°C
- **Insulation Elongation:** 150% min.
- **Tensile Strength:** 2000 psi min.
- **Min. Bend Radius:** 290°C for 500 hours around a mandrel
- **Wrap Test:** Accordance with AS22759 using an oven temperature of 290°C
- **Flammability, 60° Flame:** Exceeds test requirements
- **Smoke:** Smoke resistance test specified in AS22759 using an oven temperature of 290°C

ELECTRICAL PERFORMANCE

- **Voltage Range:** 1000 V_{rms}
- **Insulation Resistance:** 50,000 MΩ/1000 ft min.
- **Corona Resistance:** ASTM D1868
- **Arc Track Resistance:** SAE AS22759

WIRE PRINTING

- **UV Laser Marking:** Excellent mark contrast (available in 10 AWG and smaller only)

SPECIFICATIONS

- **Product Specification:** WCD3111

Part Numbering/Ordering Information

Contact TE Connectivity.



LET'S CONNECT

We make it easy to connect with our experts and are ready to provide all the support you need. Just call your local support number or visit www.te.com/industrial to chat with a Product Information Specialist.

Technical Support

te.com/support-center

North America	+1 800 522 6752	Asia Pacific	+86 400 820 6015
North America (Toll)	+1 717 986 7777	Japan	044 844 8180
EMEA/South Africa	+800 0440 5100	Australia	+61 2 9554 2695
EMEA (Toll)	+31 73 624 6999	New Zealand	+64 (0) 9 634 4580
India (Toll-Free)	+800 440 5100		

te.com/power-cables

TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

1773455-9 04/16